

fluorescent dimming with Hi-lume®, Compact SE™, Eco-10®, EcoSystem® ballasts, and Hi-lume® LED



- use with Lutron® 3-wire line-voltage control electronic dimming ballasts
- please refer to the Lutron® Fluorescent Dimming Systems Selection Guide (P/N 366-002) for more information
- no derating if ganged

fluorescent*

single pole	120V	8A	SF-10P-
single pole	277V	6A	SF-12P-277-
3-way	120V	8A	SF-103P-
3-way	277V	6A	SF-12P-277-3-

LED (with Hi-lume® LED driver only)*

NEW

single pole	120V	8A	SF-10P-
single pole	277V	6A	SF-12P-277-
3-way	120V	8A	SF-103P-
3-way	277V	6A	SF-12P-277-3-

LED (with GRX-TVI 0-10 VDC sink control)*

NEW

single pole	16A load 30 mA control 120/277V	SF-10P-
3-way	16A load 30 mA control 120/277V	SF-103P-

* requires neutral wire connection

fluorescent dimming with Tu-Wire® ballasts



- use with Lutron® Tu-Wire® line-voltage control electronic dimming ballasts
- for information on using Lutron® dimmers to control Advance® Mark 10® dimming ballasts, visit the Lutron® website at www.lutron.com/advance
- must be derated if ganged

fluorescent Tu-Wire®

single pole/3-way 5A **SFTU-5A3P-**

compact fluorescent dimming with Philips® DIMMABLE Energy Saver CFL

NEW



- use **only** with **PHILIPS®** models:
EL/A
R30 DIM
R40 DIM
PAR38 DIM
- includes locator light
- no derating if ganged
- always turn on, regardless of slider setting
- isolates bulb from unstable line voltage

screw base dimmable compact fluorescent

single pole/3-way 200W **SPDC-203P-**†

Standard incandescent/halogen dimmers are not UL listed for screw base dimmable compact fluorescent (CFL) lamps.

† Available in white, ivory, almond, and light almond.

See page 77 for available colors.

To order, add color suffix to model number.

Example: **SF-10P- WH**



Shown actual size: Skylark® preset dimmer and 1-gang Claro® wallplate in almond (AL)

SKYLARK® dimmers

product family features

- rocker switch returns light to your favorite light level
- slide up to brighten, down to dim (adjust light to suit any activity)
- coordinating Claro® wallplates available separately (including stainless steel)
- eco-dim® model available

available models

source type

- incandescent/halogen lighting
- magnetic low-voltage lighting
- electronic low-voltage lighting
- fluorescent lighting
- LED lighting
- dimnable compact fluorescent
- quiet 3-speed fan controls
- quiet 3-speed fan/light controls
- fully variable fan controls

control locations

- single pole (one location)
- 3-way (two locations)

available colors (see page 12 for color swatches)

colors (gloss finish)

- | | |
|------------------------|-----------------|
| WH white | GR gray |
| IV ivory | BR brown |
| AL almond | BL black |
| LA light almond | |

Questions on installation or selection?
Call Lutron® 24 hours/7 days a week at
1.800.523.9466 or visit www.lutron.com