



FOREST LIGHTING

Sustainable illumination

A19 Dimmable LED Lamps

Forest Lighting A19 LED Lamps are the most affordable, standard LED light bulbs on the market today. They are dimmable, and can be used with approved dimmers from all leading lighting control manufacturers. Forest Lighting A19 lamps offer a variety of colors from warm white to bright white.

PERFORMANCE & PARAMETERS

CCT	3000K / 4000K / 5000K
Beam Angle	290°
CRI	> 80 Ra
Efficacy	≥ 75 lm/W
Rated Average Life	30,000 Hrs
Input Voltage	120V
Power Frequency	60 Hz
Power Tolerance	+/-10%

	6 WATT	9 WATT
Luminous Flux	450 lm	800 lm
Input Current	0.05A	0.073A
Incandescent Equivalent	40W	60W

Operating Temperature	-4 to +104 °F, -20 to +40 °C
Operating Humidity	10 to 85% RH
Operating Frequency	> 120 Hz
Base	E26



FEATURES & BENEFITS

- Lasts 27 years
- Cool to the touch
- High efficiency

WARRANTY

5 Year Warranty

LISTINGS AND CERTIFICATIONS





A19 Dimmable LED Lamps

ORDERING INFORMATION

Single Pack

Product	Wattage	CCT	Model No.	Factory Model No.
A19	6W	3000K	A19-6W30KD-ES-MA4S05-6	MA4S05-6
		4000K*	A19-6W40KD-ES-MA4N05-6	MA4N05-6
		5000K	A19-6W50KD-ES-MA4Z05-6	MA4Z05-6
A19	9W	3000K	A19-9W30KD-ES-MA4S06-9	MA4S06-9
		4000K*	A19-9W40KD-ES-MA4N06-9	MA4N06-9
		5000K	A19-9W50KD-ES-MA4Z06-9	MA4Z06-9

*Non Stock Item

4-Pack

Product	Wattage	CCT	Model No.	Factory Model No.
A19	6W	3000K	A19-6W30KD-ES-4-MA4S05-6	MA4S05-6
		4000K	A19-6W40KD-ES-4-MA4N05-6	MA4N05-6
		5000K	A19-6W50KD-ES-4-MA4Z05-6	MA4Z05-6
A19	9W	3000K	A19-9W30KD-ES-4-MA4S06-9	MA4S06-9
		4000K	A19-9W40KD-ES-4-MA4N06-9	MA4N06-9
		5000K	A19-9W50KD-ES-4-MA4Z06-9	MA4Z06-9



FOREST LIGHTING

Sustainable illumination

A19 Non-Dimmable LED Lamps

Forest Lighting A19 LED Lamps are the most affordable, standard LED light bulb on the market today. Forest Lighting A19 lamps offer a variety of colors from warm white to bright white.

PERFORMANCE & PARAMETERS

CCT	3000K / 4000K / 5000K
Beam Angle	290°
CRI	> 80 Ra
Efficacy	≥ 75 lm/W
Rated Average Life	30,000 Hrs
Input Voltage	120V
Power Frequency	60 Hz
Power Tolerance	+/-10%

	6 WATT	9 WATT
Luminous Flux	450 lm	800 lm
Input Current	0.05A	0.073A
Incandescent Equivalent	40W	60W

Operating Temperature	-4 to +104 °F, -20 to +40 °C
Operating Humidity	10 to 85% RH
Operating Frequency	> 120 Hz
Base	E26



FEATURES & BENEFITS

- Lasts 27 years
- Cool to the touch
- High efficiency

WARRANTY

5 Year Warranty

LISTINGS AND CERTIFICATIONS





FOREST LIGHTING

Sustainable illumination

A19 Non-Dimmable LED Lamps

ORDERING INFORMATION

Product	Wattage	CCT	Model No.	Factory Model No.
A19	6W	3000K	A19-6W30KND-ES-MA2S05-6	MA2S05-6
		4000K*	A19-6W40KND-ES-MA2N05-6	MA2N05-6
		5000K	A19-6W50KND-ES-MA2Z05-6	MA2Z05-6
A19	9W	3000K	A19-9W30KND-ES-MA2S05-9	MA2S05-9
		4000K*	A19-9W40KND-ES-MA2N05-9	MA2N05-9
		5000K	A19-9W50KND-ES-MA2Z05-9	MA2Z05-9

*Non Stock Item