EBPLED7W/EBPLED14W Battery Pack



Product Feature	Customer Benefit
Field installable	Meet emergency code with no aesthetic impact
Satisfies all wiring configurations as conduit and test button are included	Design ease; less SKU's to stock
7 watt or 14 watt output creates 600 to 2500 lumens in emergency mode	Design flexibility; superior egress coverage
Laser test feature enables simplified NFPA testing	Labor savings on NFPA/OSHA required testing

Certifi	ication / Warranty
UL 924 installa	Classified for field ation
NFPA/ compli	NEC/OSHA/CEC code ant
	nteed compatibility w/ Fixtures
5 year	product warranty

APX/APX7H Polycarbonate Exit



Product Feature	Customer Benefit
LED source with nickel cadmium battery	Up to 10 years with no maintenance
Red or Green LED illumination	Design flexibility
Universal mount; single or double sided	Design flexibility
Optional remote capacity to drive 2 or 4 LED heads (H version)	Design flexibility; labor and material savings

Certification / Warranty
UL 924 damp location listed
NFPA/NEC/OSHA/CEC code compliant
5 year product warranty
7 year prorated battery warranty

APC7/APC7H Polycarbonate LED Combo



Product Feature	Customer Benefit
LED source with nickel cadmium battery	Up to 10 years with no maintenance
Red or Green LED illumination	Design flexibility
Universal mount; single or double sided	Design flexibility
LED emergency heads	Design flexibility; labor and material savings
Optional remote capacity to drive 2 LED heads (H version)	Design flexibility; labor and material savings

Certification / Warranty	
UL 924 damp location listed	
NFPA/NEC/OSHA/CEC code compliant	
5 year product warranty	
7 year prorated battery warra	nty

APEL/APELH2 Polycarbonate LED Emergency



Product Feature	Customer Benefit
LED source with nickel cadmium battery	Up to 10 years with no maintenance
Adjustable heads	Design flexibility
Optional remote capacity to drive 2 LED heads (H2 version)	Design flexibility; labor and material savings

Certification / Warranty
UL 924 damp location listed
NFPA/NEC/OSHA/CEC code compliant
5 year product warranty
7 year prorated battery warranty

APWR1/APWR2 Indoor/Outdoor Polycarbonate LED Remote



Product Feature	Customer Benefit
LED source	Up to 10 years with no maintenance
Adjustable heads	Design Flexibility
Outdoor rated	Design flexibility; less SKU's to stock

Certification / Warranty
UL 924 wet location listed
NFPA/NEC/OSHA/CEC code compliant
5 year product warranty



SEL Polycarbonate LED Emergency



Product Feature	Customer Benefit
Up to 60 feet of egress coverage	Up to \$300 savings on installation
LED source with Nickel cadmium battery	Up to ten years with no maintenance
Optional remote capacity (SRP/SRM remotes)	Indoor, outdoor design flexibility
Self diagnostics w/laser test option	Labor savings on NFPA/OSHA required testing

Certification / Warranty
UL924 damp location
NFPA/NEC/OSHA/CEC code compliant
5-year product warranty
7-year prorated battery warranty


SELW Polycarbonate Outdoor LED Emergency



Product Feature	Customer Benefit
LED source with Nickel cadmium battery	Up to ten years with no maintenance
Forward throw optic	Maximum design flexibility
Up to 29 feet of egress coverage	Design flexibility; superior egress coverage
Self diagnostics w/laser test option	Labor savings on NFPA/OSHA required

Certification / Warranty
UL924 wet location
NFPA/NEC/OSHA/CEC code compliant
5-year product warranty
7-year prorated battery warranty

LPX Polycarbonate / CX Die Cast Exit



Product Feature	Customer Benefit
LED source with Nickel cadmium battery	Up to ten years with no maintenance
Field adjustable for red or green / universal mount	Maximum design flexibility; less SKU's to stock
Optional remote capacity (SRP/SRM remotes)	Indoor/outdoor design flexibility
Self diagnostics with laser test option	Labor savings on NFPA/OSHA required testing

Certification / Warranty
UL924 damp location listed
NFPA/NEC/OSHA/CEC code compliant
5-year product warranty
7-year prorated battery warranty

SELDW Industrial LED Emergency



Product Feature	Customer Benefit
LED source with Nickel cadmium battery	Up to ten years with no maintenance
Up to 60 feet of egress coverage	Fixture cost savings - less fixtures required
Self diagnostics with laser test standard	Labor savings on NFPA/OSHA required testing
NEMA 4X; IP66; - 30° C to 50° C temp range	Maximum design flexibility; less SKU's to stock

Certification / Warranty	
UL924 wet location listed	
NEMA 4X/IP66/NSF	
NFPA/NEC/OSHA/CEC code compliant	
HAZ (class 1, Div 2) option	
5-year product warranty	
7-year prorated battery warranty	

UX Industrial Exit



Product Feature	Customer Benefit
LED source with Nickel cadmium battery	Up to ten years with no maintenance
Field adjustable for red or green/universal mount	Maximum design flexibility; less SKU's to stock
Self diagnostics with laser test standard	Labor savings on NFPA/OSHA required testing
NEMA 4X; IP66; - 30° C to 50° C temp range	Maximum design flexibility; less SKU's to stock

Certification / Warranty	
UL924 wet location listed	
NEMA 4X/IP66/NSF	
NFPA/NEC/OSHA/CEC code compliant	
HAZ (class 1, Div 2) option	
5-year product warranty	
7-year prorated battery warranty	

Eaton

1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.eaton.com/lighting

Canada Sales 5925 McLaughlin Road Mississauga, Ontario L5R 1B8 P: 905-501-3000 F: 905-501-3172

© 2017 Eaton All Rights Reserved Printed in USA Publication No. SA518019EN June 14, 2017 8:33 AM Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.

