SLD surface LED downlight

Technical bulletin

Halo SLD Surface LED Downlight luminaires incorporate WaveStream™ LED technology to create an ultra-low profile, surface-mounting luminaire with the performance and look of traditional downlights. The SLD Series offers unparalleled design freedom with mainstream value.

The SLD4 and SLD6 luminaires are designed for installation in many 3-1/2" and 4" electrical junction boxes, and may be retrofit in 4", 5", or 6" aperture IC and Non-IC recessed housings.



Junction Box Installation

Using the Slot-N-Lock quick installation system, the SLD can be installed into many 3-1/2' and 4" square, octagon, and round electrical junction boxes. Slot-N-Lock bracket included.

Recessed Housing Installation

Friction blades allow for installation into 4", 5" or 6" recessed housings without torsion spring mounting tabs Torsion springs allow for installation into 5" or 6" recessed housings with torsion spring mounting tabs.

Dimming

Dimmable to 5% with many 120V leading-edge and trailingedge phase control dimmers. Universal voltage also dimmable to 10% with many 0-10V DC low voltage dimmers.

Construction

- 4" and 6" ultra-low profile surface mounting
- Die cast aluminum trim ring and die formed aluminum frame
- Plug-in LED connector for easy installation
 - Supply wire adapter connection for junction box wiring
 - Screwbase adapter for recessed housing retrofit

Code Compliance

- cULus Listed for Halo housings
- UL Classified for other housings
- Damp Location Listed for walls
- Wet Location Listed for showers and outdoor protected ceilings

Warranty

• Five-year warranty

Stock Ordering Information

SLD4 Series

| Model Number | Description | Lumens | Wattage | Voltage |
|-----------------------------------------------------|-----------------------------------------------------|--------|---------|----------------|
| SLD405827WH | 4" Surface LED Downlight, 80 CRI, 2700K | 720 | 12.2W | 120V, 50/60 Hz |
| SLD405830WH | WH 4" Surface LED Downlight, 80 CRI, 3000K | | 12.2W | 120V, 50/60 Hz |
| SLD405835WH | 4" Surface LED Downlight, 80 CRI, 3500K | 780 | 12.2W | 120V, 50/60 Hz |
| SLD405840WH | SLD405840WH 4" Surface LED Downlight, 80 CRI, 4000K | | 12.2W | 120V, 50/60 Hz |
| SLD405927WH 4" Surface LED Downlight, 90 CRI, 2700K | | 650 | 12W | 120V, 50/60 Hz |
| SLD405930WH | 4" Surface LED Downlight, 90 CRI, 3000K | 670 | 12W | 120V, 50/60 Hz |
| SLD405935WH 4" Surface LED Downlight, 90 CRI, 3500K | | 690 | 12W | 120V, 50/60 Hz |
| SLD405940WH | 4" Surface LED Downlight, 90 CRI, 4000K | 710 | 12W | 120V, 50/60 Hz |

SLD4 Series - J-box Only Kits

| Model Number Description | | Lumens | Wattage | Voltage |
|--------------------------|-----------------------------------------------------------------|--------|---------|----------------|
| SLD405827WHJB | .D405827WHJB 4" Surface LED Downlight, J-box kit, 80 CRI, 2700K | | 12.2W | 120V, 50/60 Hz |
| SLD405830WHJB | 4" Surface LED Downlight, J-box kit, 80 CRI, 3000K | 750 | 12.2W | 120V, 50/60 Hz |
| SLD405835WHJB | 4" Surface LED Downlight, J-box kit, 80 CRI, 3500K | 780 | 12.2W | 120V, 50/60 Hz |
| SLD405840WHJB | 4" Surface LED Downlight, J-box kit, 80 CRI, 4000K | 800 | 12.2W | 120V, 50/60 Hz |
| SLD405927WHJB | 4" Surface LED Downlight, J-box kit, 90 CRI, 2700K | 650 | 12W | 120V, 50/60 Hz |
| SLD405930WHJB | 4" Surface LED Downlight, J-box kit, 90 CRI, 3000K | 670 | 12W | 120V, 50/60 Hz |
| SLD405935WHJB | 4" Surface LED Downlight, J-box kit, 90 CRI, 3500K | 690 | 12W | 120V, 50/60 Hz |
| SLD405940WHJB | 4" Surface LED Downlight, J-box kit, 90 CRI, 4000K | 710 | 12W | 120V, 50/60 Hz |

continued



Eaton

1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.eaton.com/lighting

Canada Sales

5925 McLaughlin Road Mississauga, Ontario L5R 1B8 F: 905-501-3172

© 2015 Eaton All Rights Reserved Printed in USA Publication No. SA518006EN December 7, 2015 9:26 AM

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.

Stock Ordering Information

SLD6 600 Series

| Model Number | Model Number Description | | Wattage | Voltage |
|---------------------------------------------------------------|-----------------------------------------------------------|-----|---------|----------------|
| SLD606827WH | 5"/6" Surface LED Downlight, 80 CRI, 2700K | 727 | 12.2W | 120V, 50/60 Hz |
| SLD606830WH | 5"/6" Surface LED Downlight, 80 CRI, 3000K | 760 | 12.2W | 120V, 50/60 Hz |
| SLD606835WH | 5835WH 5"/6" Surface LED Downlight, 80 CRI, 3500K | | 12.2W | 120V, 50/60 Hz |
| SLD606840WH | 06840WH 5"/6" Surface LED Downlight, 80 CRI, 4000K | | 12.2W | 120V, 50/60 Hz |
| SLD606927WH | D6927WH 5"/6" Surface LED Downlight, 90 CRI, 2700K | | 13.2W | 120V, 50/60 Hz |
| SLD606930WH | 5"/6" Surface LED Downlight, 90 CRI, 3000K | 735 | 13.2W | 120V, 50/60 Hz |
| SLD606935WH 5"/6" Surface LED Downlight, 90 CRI, 3500K | | 760 | 13.2W | 120V, 50/60 Hz |
| SLD606940WH | 5"/6" Surface LED Downlight, 90 CRI, 4000K | 780 | 13.2W | 120V, 50/60 Hz |

SLD6 600 Series - J-box Only Kits

| Model Number | per Description | | Wattage | Voltage |
|---------------------------------------------------------------------|--------------------------------------------------------------------|-----|---------|----------------|
| SLD606827WHJB | 5"/6" Surface LED Downlight, J-box kit, 80 CRI, 2700K | 727 | 12.2W | 120V, 50/60 Hz |
| SLD606830WHJB | 5"/6" Surface LED Downlight, J-box kit, 80 CRI, 3000K | 760 | 12.2W | 120V, 50/60 Hz |
| SLD606835WHJB | 5"/6" Surface LED Downlight, J-box kit, 80 CRI, 3500K | 780 | 12.2W | 120V, 50/60 Hz |
| SLD606840WHJB | LD606840WHJB 5"/6" Surface LED Downlight, J-box kit, 80 CRI, 4000K | | 12.2W | 120V, 50/60 Hz |
| SLD606927WHJB 5"/6" Surface LED Downlight, J-box kit, 90 CRI, 2700K | | 710 | 13.2W | 120V, 50/60 Hz |
| SLD606930WHJB | 5"/6" Surface LED Downlight, J-box kit, 90 CRI, 3000K | 735 | 13.2W | 120V, 50/60 Hz |
| SLD606935WHJB 5"/6" Surface LED Downlight, J-box kit, 90 CRI, 3500K | | 760 | 13.2W | 120V, 50/60 Hz |
| SLD606940WHJB | 5"/6" Surface LED Downlight, J-box kit, 90 CRI, 4000K | 780 | 13.2W | 120V, 50/60 Hz |

SLD6 1200 Series

| Model Number Description | | Lumens | Wattage | Voltage |
|--------------------------------------------------------|----------------------------------------------------------|--------|---------|----------------|
| SLD612827WH | 2827WH 5"/6" Surface LED Downlight, 80 CRI, 2700K | | 14.8W | 120V, 50/60 Hz |
| SLD612830WH | 5"/6" Surface LED Downlight, 80 CRI, 3000K | 1150 | 14.8W | 120V, 50/60 Hz |
| SLD612835WH | SLD612835WH 5"/6" Surface LED Downlight, 80 CRI, 3500K | | 14.8W | 120V, 50/60 Hz |
| SLD612840WH 5"/6" Surface LED Downlight, 80 CRI, 4000K | | 1215 | 14.8W | 120V, 50/60 Hz |
| SLD612927WH 5"/6" Surface LED Downlight, 90 CRI, 2700K | | 880 | 14.8W | 120V, 50/60 Hz |
| SLD612930WH | 5"/6" Surface LED Downlight, 90 CRI, 3000K | 925 | 14.8W | 120V, 50/60 Hz |
| SLD612935WH | 5"/6" Surface LED Downlight, 90 CRI, 3500K | 965 | 14.8W | 120V, 50/60 Hz |
| SLD612940WH | 5"/6" Surface LED Downlight, 90 CRI, 4000K | 1000 | 14.8W | 120V, 50/60 Hz |

SLD6 1200 Series - Universal Voltage, J-box Only Kits

| Model Number | Description | Lumens | Wattage | Voltage |
|------------------------------------------------------------------------|-------------------------------------------------------|--------|---------|---------------------|
| SLD612827WHUNVJB | 5"/6" Surface LED Downlight, J-box kit, 80 CRI, 2700K | 1100 | 14.8W | 120V-277V, 50/60 Hz |
| SLD612830WHUNVJB | 5"/6" Surface LED Downlight, J-box kit, 80 CRI, 3000K | 1150 | 14.8W | 120V-277V, 50/60 Hz |
| SLD612835WHUNVJB | 5"/6" Surface LED Downlight, J-box kit, 80 CRI, 3500K | 1200 | 14.8W | 120V-277V, 50/60 Hz |
| SLD612840WHUNVJB | 5"/6" Surface LED Downlight, J-box kit, 80 CRI, 4000K | 1215 | 14.8W | 120V-277V, 50/60 Hz |
| SLD612927WHUNVJB 5"/6" Surface LED Downlight, J-box kit, 90 CRI, 2700K | | 880 | 14.8W | 120V-277V, 50/60 Hz |
| SLD612930WHUNVJB | 5"/6" Surface LED Downlight, J-box kit, 90 CRI, 3000K | 925 | 14.8W | 120V-277V, 50/60 Hz |
| SLD612935WHUNVJB | 5"/6" Surface LED Downlight, J-box kit, 90 CRI, 3500K | 965 | 14.8W | 120V-277V, 50/60 Hz |
| SLD612940WHUNVJB | 5"/6" Surface LED Downlight, J-box kit, 90 CRI, 4000K | 1000 | 14.8W | 120V-277V, 50/60 Hz |

SLD4 Accessories

| Model Number | Description |
|---------------------------------------------------|---------------------------------------------------------------------------------------------|
| SLD4EXT 4" Surface LED J-Box Extender, 7.75" O.D. | |
| SLD4RAD | 4" SLD Round Surface J-Box Adapter, 6.15" O.D. (For 4-inch round or octagon junction boxes) |
| SLD4ACCKIT | 4" Accessory Parts Replacement Kit (Screwbase adapter, torsion springs, friction blades) |
| SLD4BRKT | 4" Junction Box Bracket & Screws |

SLD6 Accessories

| 00.00000000 | |
|--------------|-------------------------------------------------------------------------------------------------|
| Model Number | Description |
| SLD6EXT | 6" Surface LED J-Box Extender, 9.5" O.D. |
| SLD6RAD | 6" SLD Round Surface J-Box Adapter, 7.92" O.D. (for 4-inch round or octagon junction boxes.) |
| SLD6SADPLT | 6" SLD Square Surface J-Box Adapter Plate (For 4-inch square junction boxes, use with SLD6RAD.) |
| SLD6ACCKIT | 6" Accessory Parts Replacement Kit (Screwbase adapter, torsion springs, friction blades) |
| SLD6BRKT | 6" Junction Box Bracket & Screws |







Designer Trims (order separately)

| Stock Number | Description | Finishes | | |
|--------------|---------------------------|--------------------------|---------------------|------------------------|
| SLD4TRM | 4" Designer Trim for SLD4 | | | |
| SLD6TRM | 6" Designer Trim for SLD6 | SN = Satin Nickel | TBZ = Tuscan Bronze | WH = White (Paintable) |