

NEW

M18™ FORCE LOGIC™



2678-22BG
(2) M18™ REDLITHIUM™ 2.0 compact batteries, M18™ 6T fixed BG crimping jaw, carabineer and utility bucket bag.



2678-22O
(2) M18™ REDLITHIUM™ 2.0 compact batteries, M18™ 6T fixed O crimping jaw, carabineer and utility bucket bag.



2678-22
(2) M18™ REDLITHIUM™ 2.0 compact batteries, M18™ 6T snub nose crimping jaw, carabineer and utility bucket bag.

M18™ FORCE LOGIC™ 6T CRIMPERS THE MOST RELIABLE WAY TO CRIMP

- Fully balanced design provides ultimate control and accuracy with class 3 gloves, simplifying the alignment process.
- PFM™ (Predictive Force Monitoring): Automatically modifies output based on connector, ensuring optimal pressure every time. Delivers the fastest, most accurate crimps.
- Receive instant pressure verification with green light.
- Weather protected electronics keep dirt, dust & moisture out.
- Hydraulic System is optimized for consistent performance from 0°F - 122°F.
- POWERSTATE™ brushless motor delivers up to 4x longer life.
- In-Line design and 350° head rotation for easy access anywhere.
- Tool records & stores every crimp made. One-Key enabled for professional report building.



2672-21S
M18™ REDLITHIUM™ 2.0 compact batteries, multi-voltage charger, M18™ 477 ACSR jaw, Allen key and utility bucket bag.



2672-21
M18™ REDLITHIUM™ 2.0 compact batteries, multi-voltage charger, M18™ 750 MCM cable cutting jaw, Allen key and utility bucket bag.

M18™ FORCE LOGIC™ CABLE CUTTERS THE FASTEST WAY TO CUT

- Powerful 6T hydraulic pump effortlessly cuts through 477 in seconds.
- Fully balanced design delivers easiest alignment wearing class 3 gloves.
- Optimized blade geometry delivers up to 1000 cuts per blade.
- Patented anti-spreading jaw design provides the best power to size ratio in the industry.
- Hydraulic system is optimized for consistent performance from 0°F - 122°F.
- POWERSTATE™ brushless motor delivers up to 4x longer life.
- Jaws automatically open when cut is complete.



Lineman's Crimper w/Fixed BG 49-16-2601

Contoured rubberized grip is optimized for use while wearing PPE and is excellent at absorbing vibration. Integrated carabineer loops to safely pass up a handline or hang from a bucket. Extremely durable fiberglass core. Die labeled tips for fast tool identification. Accepts W style crimping dies.

NEW

M18™ FORCE LOGIC™



2679-22

(2) M18™ REDLITHIUM™ 2.0 compact batteries, M18™ 600 MCM U style crimping jaw, multi-voltage charger and carrying case

ONE KEY
UNLOCKING THE DIGITAL JOBSITE.

M18™ FORCE LOGIC™ 600 MCM CRIMPER THE MOST ACCURATE WAY TO CRIMP

- Proprietary jaw alignment system: holds connector for instant alignment.
- PFM™ (Predictive Force Monitoring): Ensures optimal pressure every time. Delivers fastest crimp time in the industry.
- Receive instant pressure verification with green light.
- Tool records & stores every crimp made. One-Key enabled for professional report building.
- In-Line design and 350° head rotation for easy access in the tightest panels.
- Weather protected electronics keep dirt, dust & moisture out.
- Hydraulic System is optimized for consistent performance from 0°F - 122°F.
- POWERSTATE™ brushless motor delivers up to 4x longer life.

M18™ FORCE LOGIC™ KNOCKOUT THE EASIEST WAY TO PUNCH!



M18™ FORCE LOGIC™ 10T 1/2" - 2" Knockout Tool Kit

2676-22 Includes 1/2" to 2" EXACT™ punches and dies, 3/4" and 7/16" draw stud, (2) M18™ REDLITHIUM™ XC batteries, multi-voltage charger, ball stud, coupler, quick connect collar and carrying case.

- Powerful enough to punch 4" holes in 12 gauge stainless steel.
- Quick connect alignment system allows for easy set-up without the tool and speeds up repetitive punching.
- Compact right angle design for easy access to tight spaces.
- EXACT™ punches and dies with cross-hairs deliver the clearest alignment in both mild and stainless steel for accurate holmaking.
- Compatible with competitive accessories.

M18™ FORCE LOGIC™ 6T 1/2" - 2" Knockout Tool Kit

2677-21 Includes M18™ REDLITHIUM™ 2.0 compact batteries, multi-voltage charger, M18™ 477 ACSR jaw, Allen key and utility bucket bag.

- Punches up to 4" holes in 14 gauge mild steel.
- Quick Connect Alignment System speeds up alignment by delivering the easiest set-up and enabling the clearest view of the work surface.
- Ideal for Service: 40% lighter weight and compact size deliver the best clearance in tight spaces.
- EXACT™ Punches and Dies are rated for both mild and stainless steel punching.
- EXACT™ Dies feature vivid red cross hairs for clearest alignment.

M18™ FORCE LOGIC™ 10T 1/2" - 4" Knockout Tool Kit

2676-23

EXACT™ 2-1/2" - 4" Knockout Set

49-16-2695

EXACT™ 1/2" - 2" Hand Ratchet Knockout Set

49-16-2694 Includes 3/8" and 3/4" ball bearing draw stud, 1/2"-2" punches and dies, grease tube, hand ratchet and case.

- 20% longer length delivers greater leverage versus the competition.
- 5° ratcheting angle allows the contractor to punch in tighter clearances.

