

# Rhino™ 4200

## Compact, Time-Saving Label Maker for On-The-Go Pros

- Familiar computer-style QWERTY keyboard for fast and easy text entry
- One-Touch “Hot Keys” provide shortcuts for creating and formatting wire/cable wraps, flags, Code 39 and Code 128 bar codes, fixed-length, general and breaker labels
- “Favorites” key provides single-key access to your most commonly used labels, symbols and terms
- Avoid repeated steps with the “Custom” key – customize and save settings for individual label formats
- Pre-programmed library with 150 symbols and terms for security, electrical, pro A/V, and facilities management
- Integrated rubber bumpers help prevent damage from accidental drops and falls
- Large back-lit display is easy to read, even in dimly-lit work areas
- Prints 57% faster than the competition\*

*\*Based on independent testing of Rhino 4200 vs. Brother PT-1400 and Brother PT-7100 in default settings*



### Single Unit Includes:

- Rhino 4200 Label Maker
- 1/2" White Vinyl Label Cartridge
- Quick Reference Guide



### Kit Includes everything in single unit, plus:

- Carry Case
- Rechargeable Lithium-ion Battery
- AC Adapter



### Quick Specs

Unit Dimensions (H x W x L)	8.46" x 4.06" x 2.24"
Weight (excluding battery)	14.63 oz
Mac®/PC Compatible	No
Accepts Label Sizes	1/4", 3/8", 1/2", 3/4"
Tape Platform	IND
Resolution	180 dpi
Printing System	Thermal Transfer
Print Speed	0.6 in/sec
Barcodes	Yes, Code 39 & Code 128
Cutter Type	Manual
Batteries	6 AA or Rechargeable (not included)
AC Adapter	Yes (not included)
Networking	No
Country of Origin	China

Item Number	Description	List Price U.S. (ea)	ECCN Number	ISV Playbook Merch Options		Length (in)	Width (in)	Height (in)	Weight (lbs)	QTY	Ti	Hi	UPC
1801611	Rhino 4200	\$124.44	EAR99	1856901	Unit	8.7	3.1	10.8	1.2	1	12	4	000 71701 059598
					Shelf	-	-	-	-	-	-	-	-
					Case	12.4	12.0	11.8	3.7	3	-	-	500 71701 05959 3
					Pallet	48.0	40.0	52.2	171.4	144	-	-	700 71701 05959 7
1835374	Rhino 4200 Soft Case Kit	\$216.67	EAR99	Requires Custom Display	Unit	10.8	10.4	3.6	2.5	1	12	4	000 71701 00013 2
					Shelf	-	-	-	-	-	-	-	-
					Case	11.4	11.0	11.4	7.5	3	-	-	500 71701 00013 7
					Pallet	48.0	40.0	50.7	360.0	144	-	-	700 71701 00013 1
<b>Accessories</b>													
1835375	Rhino 4200 Case	\$34.00	-	Requires Custom Display	Unit	10.8	10.4	3.6	0.5	1	12	4	000 71701 00014 9
15519	Rhino AC Adapter	\$33.33	EAR99	Requires Custom Display	Unit	4.1	2.4	3.1	0.4	1	0	0	000 71701 15519 1
1759398	Rechargeable battery	\$40.00	EAR99	Requires Custom Display	Unit	3.4	1.3	3.5	0.5	1	13	7	100 71701 05707 2

# Rhino™ 4200 | Compatible Labels



## IND Vinyl

Ideal for both indoor and outdoor applications. Available in the widest range of colors that meet OSHA, ANSI and ISO color standards.

- UL recognized component to UL 969
- RoHS compliant
- Temperature rating: -40° F to 176°F

## IND Flexible Nylon

Specifically designed for curved surfaces and wire and cable marking.

- UL recognized component to UL 969
- RoHS compliant
- Temperature rating: 14° F to 176°F

## IND Permanent Polyester

Professional, polished finish ideal for panels, blocks, faceplates, shelves, bins, beams and more.

- UL recognized component to UL 969
- RoHS compliant
- For flat surfaces only
- Temperature rating: -40° F to 302°F

## IND Heat-Shrink Tube

For high-end cable identification. A 3:1 shrink ratio helps ensure a secure fit on wires and cables.

- Meets MIL-M-81531, MIL-STD-202G, SAE-DTL-23053/5 (Class 1 & 3)
- UL recognized as a component to UL 224
- RoHS compliant
- Temperature rating: -67° F to 275°F

### IND Compatible Labels

Width	Length	List Price	A	A	A	A	A	A	A	A	A	A	A
<b>IND VINYL</b>													
3/8"	18'	\$19.49	18443	-	-	-	-	-	1805437	-	-	-	-
1/2"	18'	\$19.49	18444	-	18432	18435	1805413	1805416	1805435	1805414	1805243	1805415	1805412
3/4"	18'	\$21.82	18445	-	18433	18436	1805419	1805422	1805436	1805420	1805417	1805421	1805418
<b>IND PERMANENT POLYESTER</b>													
1/4"	18'	\$17.22	1805442	1805440	-	-	1805441	-	-	-	-	-	-
3/8"	18'	\$19.49	18482	18508	-	-	18485	-	-	-	-	-	-
1/2"	18'	\$19.49	18483	622289	-	-	18486	-	-	-	-	-	-
3/4"	18'	\$21.82	18484	622290	-	-	18487	-	-	-	-	-	-
<b>IND FLEXIBLE NYLON</b>													
1/2"	11.5'	\$22.59	18488	-	18490	-	-	-	-	-	-	-	-
3/4"	11.5'	\$24.96	18489	-	18491	-	-	-	-	-	-	-	-
<b>IND HEAT-SHRINK TUBE</b>													
1/4"	5'	\$43.27	18051	-	18052	-	-	-	-	-	-	-	-
3/8"	5'	\$46.61	18053	-	18054	-	-	-	-	-	-	-	-
1/2"	5'	\$49.94	18055	-	18056	-	-	-	-	-	-	-	-
3/4"	5'	\$53.26	18057	-	18058	-	-	-	-	-	-	-	-

Country of Origin: Belgium

**DISTRIBUTED BY:**  
 DYMO, ATLANTA, GA 30328  
 800-426-7827: WWW.DYMO.COM

INTERNAL USE ONLY. NOT FOR DISTRIBUTION.



A *NewellRubbermaid* Brand