

LED 4W DECORATIVE CANDLE



An LED dimmable decorative candle for multi-socket ornamental fixtures and decorative chandeliers, the four-watt LED Decorative Candle in a flame-tip envelope replaces up to a 25-watt incandescent bulb. This results in up to 80 percent savings in energy throughout the L70 25,000 hour life.

FEATURES:

- 4 watts
- CRI: >80
- 25,000 hour life (L70)
- Candelabra base (E12)
- Aluminum housing for thermal heat protection
- Five year limited warranty
- Power factor: .6
- Dimmable down to 10 percent
- Suitable for damp locations
- Not for use in enclosed luminaires

CONSTRUCTION:

LEDs: All LEDs are matched for color and CRI. The stated 25,000 hour life is based on functional light quality. After 30 percent lumen depreciation, MaxLite considers the functionality of the lamp to be ended (end of life), even though the lamp is still at 70 percent of initial lumens.

Housing: The body of each lamp is solid aluminum, which acts as a heat-sink to provide heat conductivity. This keeps the LED junction temperature well below the manufacturer's specification. The lamps stay cool and the lumens are maintained for longer life.

PROJECT NAME
CATALOG NUMBER
NOTES
FIXTURE TYPE



Lamp Ordering Information:

Watts	Order Number	Model Number	Incandescent Equivalent	Lumens	Lamp Life (Hrs.)	Dimensions (W"xH")	CCT	Shape
4.0	71638	SKCC4.0DLED30F	25	240	25,000	1.5" x 4.6"	3000K	Clear flame tip
4.0	71145	SKCC4.0DLED27	25	230	25,000	1.5" x 3.9"	2700K	Clear torpedob

MAX12161



LED 4W DECORATIVE CANDLE



COMPATIBLE DIMMERS:

Brand	Model
Lutron	S-600
Lutron	LGCL-153PL
Lutron	LG-600P
Lutron	CTCL-153PD
Lutron	SELVB-300P
Arctic Lighting	PH3-A
Smart Home	2876D
Leviton	IPL06

