

2017 EXPANDED

LED Program

...see what's new inside!



Westinghouse

INNOVATION YOU CAN BE SURE OF

NEW LED Lamps!

LED SLOPED CEILING RECESSED DOWNLIGHTS

Our assortment of LED retrofit kits has further expanded to include new adjustable angle kits ideal for sloped ceiling applications. Gimbal ring rotates 355 degrees and angles up to 45 degrees for completely customizable and adaptable illumination. Ideal for lighting artwork or for general illumination in rooms with sloped ceilings.



CHOOSE YOUR COLOR TEMPERATURE

Even more Omni A19 lamps now available in a variety of color temperatures, ranging from 2700K to 5000K. Looking to create a cozy, calm ambience? Try a 2700K or 3000K lamp. If crisp and invigorating is your goal, a 5000K lamp will transform your space.



2016 TITLE 24 BUILDING CODE LED LAMPS

Lamps that meet JA8 of the Title 24 Building Code are certified to the California Energy Commission (CEC).



Visit www.westinghouselighting.com for our complete assortment of LED lamps, light fixtures, ceiling fans and accessories.



All LED lamps in this brochure are approved for use in damp locations.

DECORATIVE LAMPS



Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL
DECORATIVE														
03211	3	Cand.	3B10/LED/DIM/CL/CB/30 1CD	Card	25	Warm White	Clear	3000	80	250	25000	22.8	\$0.36	3.85"
33045	3	Cand.	3B10/LED/DIM/CL/CB/30	Hanging Box	25	Warm White	Clear	3000	80	250	25000	22.8	\$0.36	3.85"
03212	3	Med.	3B10/LED/DIM/CL/30 1CD	Card	25	Warm White	Clear	3000	80	250	25000	22.8	\$0.36	3.67"
33046	3	Med.	3B10/LED/DIM/CL/30	Hanging Box	25	Warm White	Clear	3000	80	250	25000	22.8	\$0.36	3.67"
53141 ▲	4.5	Cand.	4.5B11/LED/DIM/CL/CB/27	Hanging Box	40	Warm White	Clear	2700	80	300	25000	22.8	\$0.54	3.78"
53204 ▲	4.5	Cand.	4.5B11/LED/DIM/CL/CB/27 1CD	Card	40	Warm White	Clear	2700	80	300	25000	22.8	\$0.54	3.78"
53205 ▲	4.5	Med.	4.5B11/LED/DIM/CL/27 1CD	Card	40	Warm White	Clear	2700	80	300	25000	22.8	\$0.54	3.78"
53144 ▲	4.5	Med.	4.5B11/LED/DIM/CL/27	Hanging Box	40	Warm White	Clear	2700	80	300	25000	22.8	\$0.54	3.78"
24 50700 ▲	5	Med.	5B11/LED/DIM/CL/27	Box	40	Warm White	Clear	2700	90	325	25000	22.8	\$0.60	3.78"
24 50690 ▲	5	Cand.	5B11/LED/DIM/CL/CB/27	Box	40	Warm White	Clear	2700	90	325	25000	22.8	\$0.60	3.78"
35121	5	Med.	5C11/LED/SW/27 2CD	Card (2)	40	Warm White	Soft White	2700	80	300	15000	13.6	\$0.60	4.01"
35122	5	Cand.	5C11/LED/SW/CB/27 2CD	Card (2)	40	Warm White	Soft White	2700	80	300	15000	13.6	\$0.60	4.01"
35123	5	Med.	5C11/LED/CL/27 2CD	Card (2)	40	Warm White	Clear	2700	80	300	15000	13.6	\$0.60	4.01"
35124	5	Cand.	5C11/LED/CL/CB/27 2CD	Card (2)	40	Warm White	Clear	2700	80	300	15000	13.6	\$0.60	4.01"
53206 ▲	4	Cand.	4CA11/LED/DIM/CL/CB/27 1CD	Card	40	Warm White	Clear	2700	80	300	25000	22.8	\$0.48	4.00"
43145	4.5	Cand.	4.5CA11/LED/DIM/CL/CB/27	Hanging Box	40	Warm White	Clear	2700	80	300	25000	22.8	\$0.54	3.98"
33207	5	Med.	5CA11/LED/DIM/CL/27 1CD	Card	40	Warm White	Clear	2700	80	300	25000	22.8	\$0.60	3.94"
33146	5	Med.	5CA11/LED/DIM/CL/27	Hanging Box	40	Warm White	Clear	2700	80	300	25000	22.8	\$0.60	3.94"
53200	6.5	Cand.	6.5B13/LED/DIM/CL/CB/27 1CD	Card	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.78	4.49"
53130 ▲	6.5	Cand.	6.5B13/LED/DIM/CL/CB/27	Hanging Box	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.78	4.49"
53132 ▲	6.5	Med.	6.5B13/LED/DIM/CL/27	Hanging Box	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.78	4.61"
53201 ▲	6.5	Med.	6.5B13/LED/DIM/CL/27 1CD	Card	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.78	4.61"
05125	7	Med.	7C13/LED/SW/27 2CD	Card (2)	60	Warm White	Soft White	2700	80	500	12000	10.9	\$0.84	4.48"
35127	7	Cand.	7C13/LED/SW/CB/27 2CD	Card (2)	60	Warm White	Soft White	2700	80	500	15000	13.6	\$0.84	4.48"
35128	7	Med.	7C13/LED/CL/27 2CD	Card (2)	60	Warm White	Clear	2700	80	500	15000	13.6	\$0.84	4.48"
45129 ▲	7	Cand.	7C13/LED/CL/CB/27 2CD	Card (2)	60	Warm White	Clear	2700	80	500	15000	13.6	\$0.84	4.49"
53202 ▲	7	Cand.	7CA13/LED/DIM/CL/CB/27 1CD	Card	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	4.49"
53138 ▲	7	Cand.	7CA13/LED/DIM/CL/CB/27	Hanging Box	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	4.49"
43203	7	Med.	7CA13/LED/DIM/CL/27 1CD	Card	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	4.45"
43139	7	Med.	7CA13/LED/DIM/CL/27	Hanging Box	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	4.45"

▲ Approved for use in totally enclosed fixtures

*Based on 3 hrs./day

**Based on 3 hrs./day 11¢/kWh

24 These lamps can be used to comply with the 2016 Title 24, Part 6, high efficacy light source requirements in the state of California.

NEW!

Visit www.westinghouselighting.com for our latest energy-saving LED products, dimmer compatibilities and individual product specification sheets.

GENERAL PURPOSE LAMPS



Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL
OMNI A15														
45134 ▲	5	Med.	50MNIA15/LED/SW/27 1CD	Card	40	Warm White	Soft White	2700	80	450	15000	13.6	\$0.60	3.54"
45136 ▲	5.5	Med.	5.50MNIA15/LED/SW/27 1CD	Card	60	Warm White	Soft White	2700	80	600	15000	13.6	\$0.66	3.55"
33191 ▲	5.5	Med.	5.50MNIA15/LED/DIM/SW/27 1CD	Card	40	Warm White	Soft White	2700	80	450	25000	22.8	\$0.66	3.54"
05135	7	Med.	70MNIA15/LED/CL/27 1CD	Card	40	Warm White	Clear	2700	80	450	12000	10.9	\$0.84	3.50"
A19														
43798 ▲	14	Med.	14A19/LED/SW/30	Box	100	Warm White	Soft White	3000	80	1500	15000	13.6	\$1.69	4.21"
45158 ▲	14	Med.	14A19/LED/SW/30 2PK	Box (2)	100	Warm White	Soft White	3000	80	1500	15000	13.6	\$1.69	4.21"
45142 ▲	14	Med.	14A19/LED/SW/50	Box	100	Daylight	Soft White	5000	80	1500	15000	13.6	\$1.69	4.21"
OMNI A19														
43425 ▲	6	Med.	60MNIA19/LED/DIM/SW/27	Box	40	Warm White	Soft White	2700	80	480	25000	22.8	\$0.72	4.33"
33464 ▲	6	Med.	60MNIA19/LED/SW/27	Box	40	Warm White	Soft White	2700	80	450	25000	22.8	\$0.72	4.33"
53098 ▲	6	Med.	60MNIA19/LED/DIM/SW/30	Box	40	Warm White	Soft White	3000	80	480	25000	22.8	\$0.72	4.33"
43189 ▲	6	Med.	60MNIA19/LED/SW/30	Box	40	Warm White	Soft White	3000	80	480	15000	13.6	\$0.72	4.33"
35156 ▲	6	Med.	60MNIA19/LED/SW/30 4PK	Box (4)	40	Warm White	Soft White	3000	80	480	15000	13.6	\$0.72	4.33"
05144 ▲	6	Med.	60MNIA19/LED/DIM/SW/50	Box	40	Daylight	Soft White	5000	80	470	25000	22.8	\$0.72	4.33"
35138 ▲	6	Med.	60MNIA19/LED/SW/50	Box	40	Daylight	Soft White	5000	80	480	15000	13.6	\$0.72	4.33"
24 50710 ▲	6.5	Med.	6.50MNIA19/LED/DIM/SW/27	Box	40	Warm White	Soft White	2700	90	470	25000	22.8	\$0.78	4.25"
24 50730 ▲	6.5	Med.	6.50MNIA19/LED/DIM/SW/30	Box	40	Warm White	Soft White	3000	90	470	25000	22.8	\$0.78	4.25"
05137	7	Med.	70MNIA19/LED/CL/27	Box	40	Warm White	Clear	2700	80	480	12000	10.9	\$0.84	4.41"
05143	7	Med.	70MNIA19/LED/DIM/CL/27	Box	40	Warm White	Clear	2700	80	480	25000	22.8	\$0.84	4.41"
43697 ▲	9	Med.	90MNIA19/LED/SW/27	Box	60	Warm White	Soft White	2700	80	800	25000	22.8	\$1.08	4.33"
03697 ▲	9	Med.	90MNIA19/LED/SW/27	Box	60	Warm White	Soft White	2700	80	790	40000	36.5	\$1.08	4.33"
43696 ▲	9	Med.	90MNIA19/LED/DIM/SW/27	Box	60	Warm White	Soft White	2700	80	800	25000	22.8	\$1.08	4.33"
05173 ▲	9	Med.	90MNIA19/LED/SW/27 12PK	Box (12)	60	Warm White	Soft White	2700	80	800	15000	13.6	\$1.08	4.33"
43440 ▲	9	Med.	90MNIA19/LED/SW/30 1CD	Card	60	Warm White	Soft White	3000	80	800	25000	22.8	\$1.08	4.33"
03440 ▲	9	Med.	90MNIA19/LED/SW/30 1CD	Card	60	Warm White	Soft White	3000	80	800	40000	36.5	\$1.08	4.33"
43127 ▲	9	Med.	90MNIA19/LED/SW/30	Box	60	Warm White	Soft White	3000	80	800	15000	13.6	\$1.08	4.33"
35160 ▲	9	Med.	90MNIA19/LED/SW/30 4PK	Box (4)	60	Warm White	Soft White	3000	80	800	15000	13.6	\$1.08	4.33"
43439 ▲	9	Med.	90MNIA19/LED/DIM/SW/30 1CD	Card	60	Warm White	Soft White	3000	80	800	25000	22.8	\$1.08	4.33"
53094 ▲	9	Med.	90MNIA19/LED/DIM/SW/30	Box	60	Warm White	Soft White	3000	80	800	25000	22.8	\$1.08	4.33"
35140 ▲	9	Med.	90MNIA19/LED/SW/50	Box	60	Daylight	Soft White	5000	80	800	15000	13.6	\$1.08	4.33"
53097 ▲	9	Med.	90MNIA19/LED/DIM/SW/50	Box	60	Daylight	Soft White	5000	80	800	25000	22.8	\$1.08	4.33"
43158 ▲	9.5	GU24	9.50MNIA19/LED/DIM/SW/GU24/27	Box	60	Warm White	Soft White	2700	80	800	25000	22.8	\$1.14	4.33"
50770 ▲	9.8	Med.	9.80MNIA19/LED/DIM/SW/40	Box	60	Warm White	Soft White	4000	80	800	25000	22.8	\$1.18	4.33"
05139	10	Med.	100MNIA19/LED/CL/27	Box	60	Warm White	Clear	2700	80	800	12000	10.9	\$1.20	4.41"
03696 ▲	10	Med.	100MNIA19/LED/DIM/SW/27	Box	60	Warm White	Soft White	2700	80	790	40000	36.5	\$1.20	4.33"
24 50720 ▲	10	Med.	100MNIA19/LED/DIM/SW/27	Box	60	Warm White	Soft White	2700	90	800	25000	22.8	\$1.20	4.25"
03439 ▲	10	Med.	100MNIA19/LED/DIM/SW/30 1CD	Card	60	Warm White	Soft White	3000	80	800	40000	36.5	\$1.20	4.33"
24 50740 ▲	10	Med.	100MNIA19/LED/DIM/SW/30	Box	60	Warm White	Soft White	3000	90	800	25000	22.8	\$1.20	4.25"
50780 ▲	10	Med.	100MNIA19/LED/SW/40	Box	60	Cool White	Soft White	4000	80	800	15000	13.6	\$1.20	4.33"
45145 ▲	11	Med.	110MNIA19/LED/DIM/SW/50	Box	75	Daylight	Soft White	5000	80	1100	25000	22.8	\$1.32	4.49"
53190 ▲	11	Med.	110MNIA19/LED/SW/30	Box	75	Warm White	Soft White	3000	80	1100	15000	13.6	\$1.32	4.49"
53140	3/9/12	Med.	3/9/120MNIA19/LED/3WAY/SW/27	Box	30/70/100	Warm White	Soft White	2700	80	280/950/1200	25000	22.8	\$1.45	4.65"
53136 ▲	15	Med.	150MNIA19/LED/DIM/SW/27	Box	100	Warm White	Soft White	2700	80	1600	25000	22.8	\$1.81	4.92"
50750 ▲	15	Med.	150MNIA19/LED/DIM/SW/40	Box	100	Cool White	Soft White	4000	80	1600	25000	22.8	\$1.81	4.64"
50760 ▲	15.5	Med.	15.50MNIA19/LED/SW/40	Box	100	Cool White	Soft White	4000	80	1600	15000	13.6	\$1.87	4.64"
50790 ▲	15.5	Med.	15.50MNIA19/LED/SW/50	Box	100	Daylight	Soft White	5000	80	1600	15000	13.6	\$1.87	4.64"

▲ Approved for use in totally enclosed fixtures

*Based on 3 hrs./day

**Based on 3 hrs./day 11¢/kWh

24 These lamps can be used to comply with the 2016 Title 24, Part 6, high efficacy light source requirements in the state of California.

NEW!

COLOR GENERAL PURPOSE LAMPS



COLOR OMNI A19

Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL
SPECIALTY - COLOR OMNI A19														
03153 ▲	5	Med.	50MNIA19/LED/R	Box	40	—	Red	—	—	—	25000	22.8	\$0.60	4.33"
03154 ▲	6	Med.	60MNIA19/LED/B	Box	40	—	Blue	—	—	—	25000	22.8	\$0.72	4.33"
03152 ▲	6	Med.	60MNIA19/LED/G	Box	40	—	Green	—	—	—	25000	22.8	\$0.72	4.33"

◆ Wet Location Approved

▲ Approved for use in totally enclosed fixtures

*Based on 3 hrs./day

**Based on 3 hrs./day 11¢/kWh

OMNI A21 LAMPS



OMNI A21

Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL
OMNI A21														
53053 ▲	11	Med.	11OMNIA21/LED/DIM/SW/30	Box	75	Warm White	Soft White	3000	80	1100	25000	22.8	\$1.32	4.80"
35157 ▲	11	Med.	11OMNIA21/LED/SW/30 2PK	Box (2)	75	Warm White	Soft White	3000	80	1100	15000	13.6	\$1.32	4.80"
35141 ▲	11	Med.	11OMNIA21/LED/SW/50	Box	75	Daylight	Soft White	5000	80	1100	15000	13.6	\$1.32	4.80"

▲ Approved for use in totally enclosed fixtures

*Based on 3 hrs./day

**Based on 3 hrs./day 11¢/kWh

GLOBE LAMPS



G16½

G19

G25

Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL
GLOBE														
53213 ▲	7	Cand.	7G16.5/LED/DIM/CL/CB/27 1CD	Card	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	2.76"
53128 ▲	7	Cand.	7G16.5/LED/DIM/CL/CB/27	Box	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	2.76"
43214	7	Med.	7G16.5/LED/DIM/CL/27 1CD	Card	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	3.02"
43129	7	Med.	7G16.5/LED/DIM/CL/27	Box	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	2.83"
45131 ▲	7	Cand.	7G16.5/LED/DIM/SW/CB/27 1CD	Card	60	Warm White	Soft White	2700	80	500	25000	22.8	\$0.84	2.75"
05130	7	Med.	7G16.5/LED/DIM/SW/27 1CD	Card	60	Warm White	Soft White	2700	80	500	25000	22.8	\$0.84	3.10"
03192	7	Med.	7G19/LED/DIM/SW/27 1CD	Card	60	Warm White	Soft White	2700	80	500	25000	22.8	\$0.84	3.52"
53011 ▲	6	Med.	6G25/LED/DIM/SW/30	Box	75	Warm White	Soft White	3000	80	590	25000	22.8	\$0.72	4.33"
35149	7	Med.	7G25/LED/DIM/CL/27	Box	60	Warm White	Clear	2700	80	500	25000	22.8	\$0.84	4.42"

▲ Approved for use in totally enclosed fixtures

*Based on 3 hrs./day

**Based on 3 hrs./day 11¢/kWh

NEW!

Visit www.westinghouselighting.com for our latest energy-saving LED products, dimmer compatibilities and individual product specification sheets.

FILAMENT LAMPS

LAMPS SHOWN UNLIT



Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL
A TYPE														
33166 ▲	4.5	Med.	4.5A15/FilamentLED/DIM/CL/27	Box	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.54	3.30"
50190 ▲	4.5	Med.	4.5A15/FilamentLED/DIM/SW/27	Box	40	Warm White	Soft White	2700	80	420	15000	13.6	\$0.54	3.30"
33164 ▲	4.5	Med.	4.5A19/FilamentLED/DIM/CL/27	Box	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.54	4.13"
50150 ▲	4.5	Med.	4.5A19/FilamentLED/DIM/SW/27	Box	40	Warm White	Soft White	2700	80	420	15000	13.6	\$0.54	4.13"
05151 ▲	5	Med.	5A19/FilamentLED/DIM/A/20 1CD	Card	40	Warm White	Amber	2000	80	420	15000	13.6	\$0.60	3.97"
33165 ▲	6.5	Med.	6.5A19/FilamentLED/DIM/CL/27	Box	60	Warm White	Clear	2700	80	810	15000	13.6	\$0.78	4.13"
50160 ▲	6.5	Med.	6.5A19/FilamentLED/DIM/SW/27	Box	60	Warm White	Soft White	2700	80	720	15000	13.6	\$0.78	4.13"
BT15														
33167 ▲	4.5	Med.	4.5BT15/FilamentLED/DIM/CL/27	Box	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.54	4.05"
B11 DECORATIVE														
50470 ▲	2.5	Med.	2.5B11/FilamentLED/DIM/SW/27 2CD	Card (2)	40	Warm White	Soft White	2700	80	200	15000	13.6	\$0.30	3.58"
50340 ▲	2.5	Med.	2.5B11/FilamentLED/DIM/SW/27	Box	40	Warm White	Soft White	2700	80	200	15000	13.6	\$0.30	3.58"
50630 ▲	3	Cand.	3B11/FilamentLED/DIM/CL/CB/27 2CD	Card (2)	25	Warm White	Clear	2700	80	200	15000	13.6	\$0.36	3.82"
50590 ▲	3	Cand.	3B11/FilamentLED/DIM/CL/CB/27	Box	25	Warm White	Clear	2700	80	200	15000	13.6	\$0.36	3.82"
50640 ▲	3	Cand.	3B11/FilamentLED/DIM/SW/CB/27 2CD	Card (2)	25	Warm White	Soft White	2700	80	180	15000	13.6	\$0.36	3.82"
50600 ▲	3	Cand.	3B11/FilamentLED/DIM/SW/CB/27	Box	25	Warm White	Soft White	2700	80	180	15000	13.6	\$0.36	3.82"
50610 ▲	4.5	Cand.	4.5B11/FilamentLED/DIM/CL/CB/27 2CD	Card (2)	40	Warm White	Clear	2700	80	300	15000	13.6	\$0.54	3.82"
05171 ▲	4.5	Cand.	4.5B11/FilaLED/DIM/CL/CB/27	Box	40	Warm White	Clear	2700	80	300	15000	13.6	\$0.54	3.82"
50670 ▲	4.5	Med.	4.5B11/FilamentLED/DIM/CL/27 2CD	Card (2)	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.54	3.58"
33169 ▲	4.5	Med.	4.5B11/FilamentLED/DIM/CL/27	Box	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.54	3.58"
50510 ▲	4.5	Cand.	4.5B11/FilamentLED/DIM/SW/CB/27 2CD	Card (2)	40	Warm White	Soft White	2700	80	250	15000	13.6	\$0.54	3.54"
50210 ▲	4.5	Cand.	4.5B11/FilamentLED/DIM/SW/CB/27	Box	40	Warm White	Soft White	2700	80	250	15000	13.6	\$0.54	3.54"
50480 ▲	4.5	Med.	4.5B11/FilamentLED/DIM/SW/27 2CD	Card (2)	60	Warm White	Soft White	2700	80	420	15000	13.6	\$0.54	3.58"
50200 ▲	4.5	Med.	4.5B11/FilamentLED/DIM/SW/27	Box	60	Warm White	Soft White	2700	80	420	15000	13.6	\$0.54	3.58"
50620	6	Cand.	6B11/FilamentLED/DIM/CL/CB/27 2CD	Card (2)	60	Warm White	Clear	2700	80	500	15000	13.6	\$0.72	3.82"
33168	6	Cand.	6B11/FilaLED/DIM/CL/CB/27	Box	60	Warm White	Clear	2700	80	500	15000	13.6	\$0.72	3.82"
50520 ▲	6	Cand.	6B11/FilamentLED/DIM/SW/CB/27 2CD	Card (2)	60	Warm White	Soft White	2700	80	450	15000	13.6	\$0.72	3.54"
50220 ▲	6	Cand.	6B11/FilamentLED/DIM/SW/CB/27	Box	60	Warm White	Soft White	2700	80	450	15000	13.6	\$0.72	3.54"
CA10 DECORATIVE														
50680 ▲	4.5	Med.	4.5CA10/FilamentLED/DIM/CL/27 2CD	Card (2)	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.54	4.37"
33171 ▲	4.5	Med.	4.5CA10/FilamentLED/DIM/CL/27	Box	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.54	4.37"
05132 ▲	5	Cand.	5CA10/FilLED/DIM/A/CB/20 1CD	Card	40	Warm White	Amber	2000	80	400	15000	13.6	\$0.60	4.52"
CA11 DECORATIVE														
50650 ▲	4.5	Cand.	4.5CA11/FilamentLED/DIM/CL/CB/27 2CD	Card (2)	40	Warm White	Clear	2700	80	300	15000	13.6	\$0.54	4.37"
05172 ▲	4.5	Cand.	4.5CA11/FilaLED/DIM/CL/CB/27	Box	40	Warm White	Clear	2700	80	300	15000	13.6	\$0.54	3.82"
50660	6	Cand.	6CA11/FilamentLED/DIM/CL/CB/27 2CD	Card (2)	60	Warm White	Clear	2700	80	500	15000	13.6	\$0.72	4.37"
33170	6	Cand.	6CA11/FilaLED/DIM/CL/CB/27	Box	60	Warm White	Clear	2700	80	500	15000	13.6	\$0.72	4.37"

▲ Approved for use in totally enclosed fixtures

*Based on 3 hrs./day

**Based on 3 hrs./day 11¢/kWh

Visit www.westinghouselighting.com for our latest energy-saving LED products, dimmer compatibilities and individual product specification sheets.

FILAMENT LAMPS

LAMPS SHOWN UNLIT



Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL
F15														
03193 ▲	2.5	Med.	2.5F15/FilamentLED/DIM/CL/27 1CD	Card	25	Warm White	Clear	2700	80	250	15000	13.6	\$0.30	4.33"
03195 ▲	2.5	Med.	2.5F15/FilaLED/DIM/A/20 1CD	Card	25	Warm White	Amber	2000	80	190	15000	13.6	\$0.30	4.33"
03194 ▲	5	Med.	5F15/FilamentLED/DIM/CL/27 1CD	Card	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.60	4.33"
03196 ▲	5	Med.	5F15/FilamentLED/DIM/A/20 1CD	Card	40	Warm White	Amber	2000	80	400	15000	13.6	\$0.60	4.33"
G16.5 GLOBE														
50490 ▲	4.5	Cand.	4.5G16.5/FilamentLED/DIM/CL/CB/27 2CD	Card (2)	40	Warm White	Clear	2700	80	300	15000	13.6	\$0.54	3.23"
50230 ▲	4.5	Cand.	4.5G16.5/FilamentLED/DIM/CL/CB/27	Box	40	Warm White	Clear	2700	80	300	15000	13.6	\$0.54	3.23"
50500 ▲	6	Cand.	6G16.5/FilamentLED/DIM/CL/CB/27 2CD	Card (2)	60	Warm White	Clear	2700	80	500	15000	13.6	\$0.72	3.23"
50240 ▲	6	Cand.	6G16.5/FilamentLED/DIM/CL/CB/27	Box	60	Warm White	Clear	2700	80	500	15000	13.6	\$0.72	3.23"
G25 GLOBE														
33172 ▲	4.5	Med.	4.5G25/FilamentLED/DIM/CL/27	Box	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.54	4.52"
50170 ▲	4.5	Med.	4.5G25/FilamentLED/DIM/SW/27	Box	40	Warm White	Soft White	2700	80	420	15000	13.6	\$0.54	4.52"
50180 ▲	5.5	Med.	5.5G25/FilamentLED/DIM/SW/27	Box	60	Warm White	Soft White	2700	80	500	15000	13.6	\$0.66	4.52"
33173 ▲	6.5	Med.	6.5G25/FilamentLED/DIM/CL/27	Box	60	Warm White	Clear	2700	80	810	15000	13.6	\$0.78	4.52"
G40 GLOBE														
33174 ▲	4.5	Med.	4.5G40/FilamentLED/DIM/CL/27	Box	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.54	6.57"
33175 ▲	6.5	Med.	6.5G40/FilamentLED/DIM/CL/27	Box	60	Warm White	Clear	2700	80	810	15000	13.6	\$0.78	6.57"
ST15														
05186 ▲	4.5	Med.	4.5ST15/FilamentLED/DIM/CL/27	Box	40	Warm White	Clear	2700	80	470	15000	13.6	\$0.54	4.65"
05187 ▲	6.5	Med.	6.5ST15/FilamentLED/DIM/CL/27	Box	60	Warm White	Clear	2700	80	800	15000	13.6	\$0.78	4.65"
ST20														
33176 ▲	2.5	Med.	2.5ST20/FilamentLED/DIM/A/22	Box	25	Warm White	Amber	2200	80	230	15000	13.6	\$0.30	5.50"
05182 ▲	4.5	Med.	4.5ST20/FilamentLED/DIM/CL/27	Box	40	Warm White	Clear	2700	80	500	15000	13.6	\$0.54	5.43"
33177 ▲	4.5	Med.	4.5ST20/FilamentLED/DIM/A/22	Box	40	Warm White	Amber	2200	80	420	15000	13.6	\$0.54	5.50"
05133 ▲	5	Med.	5ST20/FilamentLED/DIM/A/20 1CD	Card	40	Warm White	Amber	2000	80	400	15000	13.6	\$0.60	5.39"
33178 ▲	6.5	Med.	6.5ST20/FilamentLED/DIM/A/22	Box	60	Warm White	Amber	2200	80	600	15000	13.6	\$0.78	5.50"
05183 ▲	7	Med.	7ST20/FilamentLED/DIM/CL/27	Box	60	Warm White	Clear	2700	80	800	15000	13.6	\$0.84	5.43"
T9														
05184 ▲	4.5	Med.	4.5T9/FilamentLED/DIM/CL/27 1CD	Card	60	Warm White	Clear	2700	80	450	15000	13.6	\$0.54	7.10"
05188 ▲	6.5	Med.	6.5T9/FilamentLED/DIM/CL/27 1CD	Card	75	Warm White	Clear	2700	80	800	15000	13.6	\$0.78	11.97"
T10														
05185 ▲	3.2	Med.	3.2T10/FilamentLED/DIM/CL/27 1CD	Card	60	Warm White	Clear	2700	80	320	15000	13.6	\$0.39	4.92"

▲ Approved for use in totally enclosed fixtures

*Based on 3 hrs./day

**Based on 3 hrs./day 11¢/kWh

REFLECTOR LAMPS



Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL
MR11														
05152	4	GU4	4MR11/LED/FL/GU4/30 1CD	Card	30	Warm White	White	3000	80	250	25000	22.8	\$0.48	1.52"
05153	4	GU10	4MR11/LED/DIM/FL/GU10/30 1CD	Card	25	Warm White	White	3000	80	250	25000	22.8	\$0.48	1.89"
MR16														
33209 ▲	4.5	GU5.3	4.5MR16/LED/DIM/FL/30 1CD	Card	35	Warm White	Clear	3000	80	360	25000	22.8	\$0.54	1.85"
33638 ▲	4.5	GU5.3	4.5MR16/LED/DIM/FL/30	Hanging Box	35	Warm White	Clear	3000	80	360	25000	22.8	\$0.54	1.85"
05179 ▲	4.5	GU10	4.5MR16/LED/DIM/FL/GU10/30	Hanging Box	35	Warm White	Frost	3000	80	360	25000	22.8	\$0.54	2.16"
33491 ▲	6.5	GU5.3	6.5MR16/LED/DIM/FL/30	Hanging Box	50	Warm White	Clear	3000	80	500	25000	22.8	\$0.78	1.85"
33208 ▲	6.5	GU5.3	6.5MR16/LED/DIM/FL/30 1CD	Card	50	Warm White	Clear	3000	80	500	25000	22.8	\$0.78	1.85"
43210 ▲	6.5	GU10	6.5MR16/LED/DIM/FL/GU10/30 1CD	Card	50	Warm White	Frost	3000	80	500	25000	22.8	\$0.78	2.16"
53032 ▲	6.5	GU10	6.5MR16/LED/DIM/FL/GU10/30	Box	50	Warm White	Frost	3000	80	500	25000	22.8	\$0.78	2.16"
REFLECTOR														
45154 ▲	4	Inter.	4R14/LED/DIM/FL/IN/27 1CD	Card	25	Warm White	Soft White	2700	80	280	25000	22.8	\$0.48	2.55"
45155 ▲	6	Med.	6R16/LED/DIM/FL/27 1CD	Card	45	Warm White	Frost	2700	80	450	25000	22.8	\$0.72	3.23"
53050 ▲	6.5	Med.	6.5R20/LED/DIM/FL/27	Box	50	Warm White	Frost	2700	80	525	25000	22.8	\$0.78	3.93"
53161 ▲	6.5	Med.	6.5R20/LED/DIM/FL/30	Box	50	Warm White	Frost	3000	80	525	25000	22.8	\$0.78	3.93"
50110 ▲	6.5	Med.	6.5R20/LED/DIM/FL/40	Box	50	Cool White	Frost	4000	80	525	25000	22.8	\$0.78	3.93"
50120 ▲	6.5	Med.	6.5R20/LED/DIM/FL/50	Box	50	Daylight	Frost	5000	80	525	25000	22.8	\$0.78	3.93"
53000	8	Med.	8R30/LED/DIM/FL/27	Box	65	Warm White	Frost	2700	80	650	25000	22.8	\$0.96	5.16"
33159	8	GU24	8R30/LED/DIM/FL/GU24/27	Box	65	Warm White	Frost	2700	80	650	25000	22.8	\$0.96	4.96"
05174 ▲	9	Med.	9BR30/LED/DIM/FL/27 12PK	Box (12)	65	Warm White	Frost	2700	80	750	25000	22.8	\$1.08	5.24"
53055 ▲	9	Med.	9BR30/LED/DIM/FL/27	Box	65	Warm White	Frost	2700	80	750	25000	22.8	\$1.08	5.24"
53010 ▲	9	Med.	9BR30/LED/DIM/FL/30	Box	65	Warm White	Frost	3000	80	750	25000	22.8	\$1.08	5.24"
50080 ▲	9	Med.	9BR30/LED/DIM/FL/40	Box	65	Cool White	Frost	4000	80	750	25000	22.8	\$1.08	5.24"
35148 ▲	9	Med.	9BR30/LED/DIM/FL/50	Box	65	Daylight	Frost	5000	80	750	25000	22.8	\$1.08	5.16"
43063	11.5	Med.	11.5R40/LED/DIM/FL/27	Box	75	Warm White	Frost	2700	80	940	25000	22.8	\$1.39	6.46"
43162	11.5	Med.	11.5R40/LED/DIM/FL/30	Box	75	Warm White	Frost	3000	80	940	25000	22.8	\$1.39	6.46"
33163	16.5	Med.	16.5R40/LED/DIM/FL/27	Box	85	Warm White	Frost	2700	80	1200	25000	22.8	\$1.99	6.46"
53064	16.5	Med.	16.5R40/LED/DIM/FL/30	Box	85	Warm White	Frost	3000	80	1200	25000	22.8	\$1.99	6.46"
50130	16.5	Med.	16.5R40/LED/DIM/FL/40	Box	85	Cool White	Frost	4000	80	1200	25000	22.8	\$1.99	6.46"
50140	16.5	Med.	16.5R40/LED/DIM/FL/50	Box	85	Daylight	Frost	5000	80	1200	25000	22.8	\$1.99	6.46"

▲ Approved for use in totally enclosed fixtures

*Based on 3 hrs./day

**Based on 3 hrs./day 11¢/kWh

REFLECTOR LAMPS



Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL
PAR16 REFLECTOR														
33067 ▲	6	Med.	6PAR16/LED/DIM/FL/30	Box	45	Warm White	Clear	3000	80	470	25000	22.8	\$0.72	3.50"
PAR20 REFLECTOR														
43012 ▲	7	Med.	7PAR20/LED/DIM/FL/30	Box	50	Warm White	Clear	3000	80	490	25000	22.8	\$0.84	3.50"
50000 ▲	7	Med.	7PAR20/LED/DIM/FL/40	Box	50	Cool White	Clear	4000	80	490	25000	22.8	\$0.84	3.50"
50010 ▲	7	Med.	7PAR20/LED/DIM/FL/50	Box	50	Daylight	Clear	5000	80	490	25000	22.8	\$0.84	3.50"
PAR30 REFLECTOR														
43160 ▲	10	Med.	10PAR30S/LED/DIM/FL/30	Box	75	Warm White	Clear	3000	80	840	25000	22.8	\$1.20	3.58"
50040 ▲	10	Med.	10PAR30S/LED/DIM/FL/40	Box	75	Cool White	Clear	4000	80	840	25000	22.8	\$1.20	3.58"
50050 ▲	10	Med.	10PAR30S/LED/DIM/FL/50	Box	75	Daylight	Clear	5000	80	840	25000	22.8	\$1.20	3.58"
53013 ▲	10	Med.	10PAR30/LED/DIM/FL/30	Box	75	Warm White	Clear	3000	80	840	25000	22.8	\$1.20	4.57"
50020 ▲	10	Med.	10PAR30/LED/DIM/FL/40	Box	75	Cool White	Clear	4000	80	840	25000	22.8	\$1.20	4.57"
50030 ▲	10	Med.	10PAR30/LED/DIM/FL/50	Box	75	Daylight	Clear	5000	80	840	25000	22.8	\$1.20	4.57"
PAR38 REFLECTOR														
33110 ◆▲	15	Med.	15PAR38/LED/OutdoorFL/30	Box	90	Warm White	Clear	3000	80	1310	25000	22.8	\$1.81	5.32"
33114 ◆▲	15	Med.	15PAR38/LED/OutdoorFL/30 2PK	Box (2)	90	Warm White	Clear	3000	80	1310	25000	22.8	\$1.81	5.32"
50090 ◆▲	15	Med.	15PAR38/LED/OutdoorFL/40	Box	90	Cool White	Clear	4000	80	1310	25000	22.8	\$1.81	5.32"
50101 ◆▲	15	Med.	15PAR38/LED/OutdoorFL/50	Box	90	Daylight	Clear	5000	80	1310	25000	22.8	\$1.81	5.32"
53014 ▲	15	Med.	15PAR38/LED/DIM/FL/30	Box	90	Warm White	Clear	3000	80	1350	25000	22.8	\$1.81	5.24"
50060 ▲	15	Med.	15PAR38/LED/DIM/FL/40	Box	90	Cool White	Clear	4000	80	1350	25000	22.8	\$1.81	5.24"
50070 ▲	15	Med.	15PAR38/LED/DIM/FL/50	Box	90	Daylight	Clear	5000	80	1350	25000	22.8	\$1.81	5.24"

◆ Wet Location Approved

▲ Approved for use in totally enclosed fixtures

*Based on 3 hrs./day

**Based on 3 hrs./day 11¢/kWh

COLOR REFLECTOR LAMPS



COLOR PAR38

Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL
SPECIALTY - COLOR PAR38 REFLECTOR														
33147 ◆▲	15	Med.	15PAR38/LED/FL/R	Box	100	—	Red	—	—	—	25000	22.8	\$1.81	5.32"
33149 ◆▲	15	Med.	15PAR38/LED/FL/G	Box	100	—	Green	—	—	—	25000	22.8	\$1.81	5.32"
33151 ◆▲	15	Med.	15PAR38/LED/FL/B	Box	100	—	Blue	—	—	—	25000	22.8	\$1.81	5.32"

◆ Wet Location Approved

▲ Approved for use in totally enclosed fixtures

*Based on 3 hrs./day

**Based on 3 hrs./day 11¢/kWh

GENERAL PURPOSE SPECIALTY LAMPS



Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL
C7														
35108	0.6	Cand.	0.6C7/LED/F/CB/27 2CD	Card (2)	4	Warm White	Frost	2700	80	20	15000	13.6	\$0.07	2.05"
35110	0.6	Cand.	0.6C7/LED/CL/CB/27 2CD	Card (2)	4	Warm White	Clear	2700	80	20	15000	13.6	\$0.07	2.05"
35109	1	Cand.	1C7/LED/F/CB/27 2CD	Card (2)	7	Warm White	Frost	2700	80	50	15000	13.6	\$0.12	2.05"
35111	1	Cand.	1C7/LED/CL/CB/27 2CD	Card (2)	7	Warm White	Clear	2700	80	50	15000	13.6	\$0.12	2.05"
S6														
35117	0.6	Cand.	0.6S6/LED/CL/CB/27 1CD	Card	6	Warm White	Clear	2700	80	32	15000	13.6	\$0.07	1.77"
S11														
35113	1	Med.	1S11/LED/CL/27 1CD	Card	7.5	Warm White	Clear	2700	80	50	15000	13.6	\$0.12	1.99"
45112 ▲	1	Med.	1S11/LED/W/27 1CD	Card	7.5	Warm White	White	2700	80	40	15000	13.6	\$0.12	2.08"
35114	1.5	Inter.	1.5S11/LED/CL/IN/27 1CD	Card	10	Warm White	Clear	2700	80	80	15000	13.6	\$0.18	2.09"
S14														
45115 ▲	1	Med.	1S14/LED/F/27 1CD	Card	11	Warm White	Frost	2700	80	60	15000	13.6	\$0.12	3.23"
35116	1	Med.	1S14/LED/CL/27 1CD	Card	11	Warm White	Clear	2700	80	65	15000	13.6	\$0.12	3.23"
T7														
35118	1	Cand.	1T7/LED/CL/CB/27 1CD	Card	10	Warm White	Clear	2700	80	50	15000	13.6	\$0.12	2.09"
45119 ▲	1.5	Inter.	1.5T7/LED/CL/IN/27 1CD	Card	15	Warm White	Clear	2700	80	80	15000	13.6	\$0.18	2.09"
35120	1.5	D.C. Bay.	1.5T7/LED/CL/DC/27 1CD	Card	15	Warm White	Clear	2700	80	80	15000	13.6	\$0.18	2.09"
33199 ▲	8	Med.	8T7/LED/F/30 1CD	Card	60	Warm White	Frost	3000	80	800	15000	13.6	\$0.96	4.22"
05161 ▲	8	Med.	8T7/LED/DIM/F/30 1CD	Card	60	Warm White	Frost	3000	80	800	25000	22.8	\$0.96	4.22"
UTILITY														
03197 ▲	15	Med.	15DLR46E26/LED/F/27	Box	75	Warm White	Frost	2700	80	1200	25000	22.8	\$1.81	4.41"
03198 ▲	20	Med.	20DLR64E26/LED/F/27	Box	100	Warm White	Frost	2700	80	1800	25000	22.8	\$2.41	6.06"

▲ Approved for use in totally enclosed fixtures.

*Based on 3 hrs./day

**Based on 3 hrs./day 11¢/kWh

Visit www.westinghouselighting.com for our latest energy-saving LED products, dimmer compatibilities and individual product specification sheets.

HALOGEN ALTERNATIVE SPECIALTY LAMPS



Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Volt	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL
JC															
03184 ▲	1.3	G4	13G4/LED/F/30 1CD	12	Card	10	Warm White	Frost	3000	80	100	25000	22.8	\$0.16	1.46"
JCD															
03185 ▲	2.5	G9	25G9/LED/F/30 1CD	120	Card	25	Warm White	Frost	3000	80	220	25000	22.8	\$0.30	2.05"
DOUBLE-ENDED SHORT															
03186 ▲	5	RSC	5R7S/LED/CL/27 1CD	120	Card	40	Warm White	Clear	2700	80	450	25000	22.8	\$0.60	3.07"
DOUBLE-ENDED LONG															
03187 ▲	9	RSC	9R7S/LED/CL/27 1CD	120	Card	75	Warm White	Clear	2700	80	900	25000	22.8	\$1.08	4.65"
33188 ▲	25	RSC	25R7S/LED/CL/27	120	Box	150	Warm White	Clear	2700	80	2300	25000	22.8	\$3.01	4.65"

▲ Approved for use in totally enclosed fixtures.

*Based on 3 hrs./day

**Based on 3 hrs./day 11¢/kWh

ADJUSTABLE RECESSED DOWNLIGHTS

All Adjustable Recessed LED Downlights are UL Classified.



Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL	MOD
SMOOTH BAFFLE															
31051 •	7	Med.	7R/4"/LED/DIM/ADJ/FL/27	Box	50	Warm White	Frost	2700	80	550	25000	22.8	\$0.84	5.32"	5.31"
31049 •	7	Med.	7R/4"/LED/DIM/ADJ/FL/30	Box	50	Warm White	Frost	3000	80	550	25000	22.8	\$0.84	5.32"	5.31"
31052 •	10	Med.	10R/6"/LED/DIM/ADJ/FL/27	Box	75	Warm White	Frost	2700	80	800	25000	22.8	\$1.20	7.28"	7.28"
31050 •	10	Med.	10R/6"/LED/DIM/ADJ/FL/30	Box	75	Warm White	Frost	3000	80	800	25000	22.8	\$1.20	7.28"	7.28"

• Damp Location Approved *Based on 3 hrs./day **Based on 3 hrs./day 11¢/kWh



RECESSED DOWNLIGHTS

All Recessed LED Downlight Kits are UL or ETL Classified.

Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**	MOL	MOD
STEP BAFFLE															
51047 ♦♦	10	Med.	10R/4"/LED/DIM/FL/30	Retail Box	65	Warm White	Frost	3000	90	670	50000	45.6	\$1.20	2.88"	5.52"
50530 ♦♦	10	Med.	10R/4"/LED/DIM/FL/40	Retail Box	65	Cool White	Frost	4000	90	670	50000	45.6	\$1.20	2.88"	5.52"
50540 ♦♦	10	Med.	10R/4"/LED/DIM/FL/50	Retail Box	65	Daylight	Frost	5000	90	670	50000	45.6	\$1.20	2.88"	5.52"
51048 ♦♦	11	Med.	11R/5-6"/LED/DIM/FL/30	Retail Box	65	Warm White	Frost	3000	90	750	50000	45.6	\$1.32	2.13"	7.48"
50550 ♦♦	11	Med.	11R/5-6"/LED/DIM/FL/40	Retail Box	65	Cool White	Frost	4000	90	750	50000	45.6	\$1.32	2.13"	7.48"
50560 ♦♦	11	Med.	11R/5-6"/LED/DIM/FL/50	Retail Box	65	Daylight	Frost	5000	90	750	50000	45.6	\$1.32	2.13"	7.48"
SMOOTH BAFFLE															
31043 ♦♦	8	Med.	8R/4"/LED/DIM/FL/27	Contractor Box	65	Warm White	Frost	2700	80	650	50000	45.6	\$0.96	3.50"	5.04"
41041 ♦♦	8	Med.	8R/4"/LED/DIM/FL/30	Contractor Box	65	Warm White	Frost	3000	80	650	50000	45.6	\$0.96	3.50"	5.04"
41040 ♦♦	14	Med.	14R/5"/LED/DIM/FL/27	Contractor Box	80	Warm White	Frost	2700	80	1000	50000	45.6	\$1.69	3.54"	6.30"
41044 ♦♦	14	Med.	14R/5"/LED/DIM/FL/30	Contractor Box	80	Warm White	Frost	3000	80	1000	50000	45.6	\$1.69	3.54"	6.30"
41045 ♦♦	14	Med.	14R/6"/LED/DIM/FL/27	Contractor Box	80	Warm White	Frost	2700	80	950	50000	45.6	\$1.69	3.40"	7.24"
41046 ♦♦	14	Med.	14R/6"/LED/DIM/FL/30	Contractor Box	80	Warm White	Frost	3000	80	950	50000	45.6	\$1.69	3.40"	7.24"
SQUARE STEP BAFFLE															
31053 ♦♦	10	Med.	10R/4"/LED/DIM/SQ/FL/30	Retail Box	60	Warm White	Frost	3000	90	650	50000	45.6	\$1.20	1.89"	4.00"
31054 ♦♦	10	Med.	10R/4"/LED/DIM/SQ/FL/40	Retail Box	60	Cool White	Frost	4000	90	650	50000	45.6	\$1.20	1.89"	4.00"
31055 ♦♦	15	Med.	15R/6"/LED/DIM/SQ/FL/30	Retail Box	100	Warm White	Frost	3000	90	1100	50000	45.6	\$1.81	2.48"	6.00"
31056 ♦♦	15	Med.	15R/6"/LED/DIM/SQ/FL/40	Retail Box	100	Cool White	Frost	4000	90	1100	50000	45.6	\$1.81	2.48"	6.00"
SLOPED STEP BAFFLE															
50820 ♦♦	10	Med.	10R/4"/LED/DIM/SLP/FL/27	Contractor Box	65	Warm White	Frost	2700	90	650	35000	31.9	\$1.20	3.35"	5.15"
50830 ♦♦	10	Med.	10R/4"/LED/DIM/SLP/FL/30	Contractor Box	65	Warm White	Frost	3000	90	650	35000	31.9	\$1.20	3.35"	5.15"
50840 ♦♦	13	Med.	13R/6"/LED/DIM/SLP/FL/27	Contractor Box	80	Warm White	Frost	2700	90	900	35000	31.9	\$1.57	3.50"	7.28"
50850 ♦♦	13	Med.	13R/6"/LED/DIM/SLP/FL/30	Contractor Box	80	Warm White	Frost	3000	90	900	35000	31.9	\$1.57	3.50"	7.28"

♦ Optional accessory GU24 base adapter sold separately (Item# 22000)

♦ Wet Location Approved • Damp Location Approved

*Based on 3 hrs./day

**Based on 3 hrs./day 11¢/kWh



Visit www.westinghouselighting.com for our latest energy-saving LED products, dimmer compatibilities and individual product specification sheets.

NEW!



HIGH BAY LAMP

This High Bay LED Lamp is 120-277V.



50570

Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. HID Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	MOL
50570◆▲	115	Mogul	115HB/LED/HL/E39/50	Box	400	Daylight	Clear	5000	80	15500	50000	8.11"

◆ DLC qualified

▲ Approved for use in totally enclosed fixtures.



HIGH LUMEN LAMPS

All High Lumen LED Lamps are 120-277V.



05181

05165

05162

05163

05164

05166

35167

05180

Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Equiv. Incand. Wattage	Equiv. CFL Wattage	Equiv. HID Wattage	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	MOL
05181▲	16	Med.	16T24/LED/HL/50	Box	100	32	50	Daylight	Clear	5000	80	2400	40000	6.52"
05165▲	24	Med.	24T23/LED/HL/50	Box	150	55	100	Daylight	Clear	5000	80	2880	40000	8.58"
05162▲	36	Med.	36T28/LED/HL/50	Box	200	65	150	Daylight	Clear	5000	80	4320	40000	8.46"
05163▲	45	Med.	45T28/LED/HL/50	Box	300	85	175	Daylight	Clear	5000	80	5400	40000	9.53"
05164◆▲	45	Mogul	45T28/LED/HL/E39/50	Box	300	85	175	Daylight	Clear	5000	80	5400	40000	9.92"
05166◆▲	54	Mogul	54T28/LED/HL/E39/50	Box	400	105	250	Daylight	Clear	5000	80	6480	40000	10.55"
35167◆▲	100	Mogul	100T44/LED/HL/E39/50	Box	750	150	400	Daylight	Clear	5000	80	15000	40000	9.65"
05180◆▲	120	Mogul	120T44/LED/HL/E39/50	Box	1000	250	800	Daylight	Clear	5000	80	18000	40000	10.43"

◆ DLC qualified

▲ Approved for use in totally enclosed fixtures.

YouTube Videos



Visit Our YouTube Channel for Educational Videos

www.youtube.com/user/Gwestinghouse

In just a few minutes, learn more about these LEDs by watching our brief videos.



HID to High Lumen LED Conversion Video



This informative tutorial includes the conversion of a parking lot light from a metal halide HID to an energy-efficient high lumen LED lamp.



LINEAR LAMPS

All Linear LED Lamps are UL Classified and NSF Certified.

Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Lamp Type Replacement	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	MOL
T5 46 inch (DesignLights Consortium® qualified product)												
33788 ◆▲■	25	Mini BiPin	LED 25T5/46"/40 Direct Install	Sleeve	T5	Cool White	Frost	4000	82	3500	50000	46"
33789 ◆▲■	25	Mini BiPin	LED 25T5/46"/50 Direct Install	Sleeve	T5	Daylight	Frost	5000	82	3500	50000	46"
T8 24 inch (DesignLights Consortium® qualified product)												
50390 ◆▲	8	Med. BiPin	LED 8T8/24"/35 Direct Install	Sleeve	T8	Cool White	Frost	3500	82	1200	50000	24"
50250 ◆▲	8	Med. BiPin	LED 8T8/24"/40 Direct Install	Sleeve	T8	Cool White	Frost	4000	82	1250	50000	24"
50400 ◆▲	8	Med. BiPin	LED 8T8/24"/50 Direct Install	Sleeve	T8	Daylight	Frost	5000	82	1250	50000	24"
50430 ◆▲	9	Med. BiPin	LED 9T8/24"/35 Ballast Bypass	Sleeve	T8 & T12	Cool White	Frost	3500	82	1100	50000	24"
50260 ◆▲	9	Med. BiPin	LED 9T8/24"/40 Ballast Bypass	Sleeve	T8 & T12	Cool White	Frost	4000	82	1150	50000	24"
50440 ◆▲	9	Med. BiPin	LED 9T8/24"/50 Ballast Bypass	Sleeve	T8 & T12	Daylight	Frost	5000	82	1150	50000	24"
T8 36 inch												
50410▲	10.5	Med. BiPin	LED 10.5T8/36"/35 Direct Install	Sleeve	T8	Cool White	Frost	3500	82	1400	50000	36"
50270▲	10.5	Med. BiPin	LED 10.5T8/36"/40 Direct Install	Sleeve	T8	Cool White	Frost	4000	82	1450	50000	36"
50420▲	10.5	Med. BiPin	LED 10.5T8/36"/50 Direct Install	Sleeve	T8	Daylight	Frost	5000	82	1450	50000	36"
50450▲	12	Med. BiPin	LED 12T8/36"/35 Ballast Bypass	Sleeve	T8 & T12	Cool White	Frost	3500	82	1400	50000	36"
50280▲	12	Med. BiPin	LED 12T8/36"/40 Ballast Bypass	Sleeve	T8 & T12	Cool White	Frost	4000	82	1450	50000	36"
50460▲	12	Med. BiPin	LED 12T8/36"/50 Ballast Bypass	Sleeve	T8 & T12	Daylight	Frost	5000	82	1450	50000	36"
T8 48 inch (DesignLights Consortium® qualified product)												
33851 ◆▲	11.5	Med. BiPin	LED 11.5T8/48"/35 Direct Install	Sleeve	T8	Cool White	Frost	3500	82	1700	50000	48"
33739 ◆▲	11.5	Med. BiPin	LED 11.5T8/48"/40 Direct Install	Sleeve	T8	Cool White	Frost	4000	82	1800	50000	48"
33852 ◆▲	11.5	Med. BiPin	LED 11.5T8/48"/50 Direct Install	Sleeve	T8	Daylight	Frost	5000	82	1800	50000	48"
03860 ◆▲	15	Med. BiPin	LED 15T8/48"/35 Ballast Bypass	Sleeve	T8 & T12	Cool White	Frost	3500	82	1700	50000	48"
03861 ◆▲	15	Med. BiPin	LED 15T8/48"/40 Ballast Bypass	Sleeve	T8 & T12	Cool White	Frost	4000	82	1800	50000	48"
03854 ◆▲	15	Med. BiPin	LED 15T8/48"/50 Ballast Bypass	Sleeve	T8 & T12	Daylight	Frost	5000	82	1800	50000	48"
43652 ◆▲	15	Med. BiPin	LED 15T8/48"/35 Direct Install	Sleeve	T8	Cool White	Frost	3500	82	2100	50000	48"
43653 ◆▲	15	Med. BiPin	LED 15T8/48"/40 Direct Install	Sleeve	T8	Cool White	Frost	4000	82	2200	50000	48"
43655 ◆▲	15	Med. BiPin	LED 15T8/48"/50 Direct Install	Sleeve	T8	Daylight	Frost	5000	82	2200	50000	48"
33660 ◆▲	18	Med. BiPin	LED 18T8/48"/35 Ballast Bypass	Sleeve	T8 & T12	Cool White	Frost	3500	82	2200	50000	48"
33672 ◆▲	18	Med. BiPin	LED 18T8/48"/40 Ballast Bypass	Sleeve	T8 & T12	Cool White	Frost	4000	82	2200	50000	48"
33676 ◆▲	18	Med. BiPin	LED 18T8/48"/50 Ballast Bypass	Sleeve	T8 & T12	Daylight	Frost	5000	82	2200	50000	48"
T8 48 inch Dual-End Powered (DesignLights Consortium® qualified product)												
50310 ◆▲	17	Med. BiPin	LED 17T8/48"/35 DE Ballast Bypass	Sleeve	T8 & T12	Cool White	Frost	3500	82	2100	50000	48"
50320 ◆▲	17	Med. BiPin	LED 17T8/48"/40 DE Ballast Bypass	Sleeve	T8 & T12	Cool White	Frost	4000	82	2200	50000	48"
50330 ◆▲	17	Med. BiPin	LED 17T8/48"/50 DE Ballast Bypass	Sleeve	T8 & T12	Daylight	Frost	5000	82	2200	50000	48"
T8 96 inch (P.E.T. Coated)												
04049 ▲	33	Single Pin	LED 33T8/96"/40 Direct Install	Sleeve	T8	Cool White	Frost	4000	82	4400	50000	96"
04050 ▲	33	Single Pin	LED 33T8/96"/50 Direct Install	Sleeve	T8	Daylight	Frost	5000	82	4400	50000	96"
04051 ▲	43	Single Pin	LED 43T8/96"/40 Ballast Bypass	Sleeve	T8 & T12	Cool White	Frost	4000	82	5500	50000	96"
04052 ▲	43	Single Pin	LED 43T8/96"/50 Ballast Bypass	Sleeve	T8 & T12	Daylight	Frost	5000	82	5500	50000	96"

◆ DLC qualified

▲ Approved for use in totally enclosed fixtures.

■ Replace F54T5HO linear fluorescent lamps.

Visit www.westinghouselighting.com for our latest energy-saving LED products, dimmer compatibilities and individual product specification sheets.



U-BENT LINEAR LAMPS

All Linear LED Lamps are UL Classified and NSF Certified.



T8 U-BENT

Item No.	Energy Used (Watts)	Lamp Base	Domestic Code	Package Type	Lamp Type Replacement	Color Designation	Finish	Light Appearance (Kelvin)	CRI	Brightness (Lumens)	Avg. Rated Hours	MOL
T8 U-Bent												
50350 ♦▲	15	Med. BiPin	LED 15T8/UB6/35 Direct Install	Box	T86U	Cool White	Frost	3500	82	2100	50000	22.84"
50290 ♦▲	15	Med. BiPin	LED 15T8/UB6/40 Direct Install	Box	T86U	Cool White	Frost	4000	82	2200	50000	22.84"
50360 ♦▲	15	Med. BiPin	LED 15T8/UB6/50 Direct Install	Box	T86U	Daylight	Frost	5000	82	2200	50000	22.84"
50370 ♦▲	18	Med. BiPin	LED 18T8/UB6/35 Ballast Bypass	Box	T86U	Cool White	Frost	3500	82	2100	50000	22.84"
50300 ♦▲	18	Med. BiPin	LED 18T8/UB6/40 Ballast Bypass	Box	T86U	Cool White	Frost	4000	82	2200	50000	22.84"
50380 ♦▲	18	Med. BiPin	LED 18T8/UB6/50 Ballast Bypass	Box	T86U	Daylight	Frost	5000	82	2200	50000	22.84"

♦ DLC qualified

▲ Approved for use in totally enclosed fixtures.

YouTube Videos



Visit Our YouTube Channel for TLED Educational Videos

www.youtube.com/user/Gwestinghouse

In just a few minutes, learn more about these LEDs by watching our brief videos.



4 ft T8 LED Direct Install Installation Overview Educational Video



Westinghouse T8 Direct Install LEDs can easily replace traditional fluorescent T8 lamps.



8 ft T8 LED Ballast Bypass Installation Overview Educational Video



General overview of a ballast bypass installation for use with Westinghouse ballast bypass 8 ft T8 LEDs.



4 ft T8 LED Ballast Bypass Installation Overview Educational Video



T8 Ballast Bypass LEDs can replace traditional fluorescent T8 lamps but installation requires knowledge of fluorescent lighting fixtures and electrical systems.



8 ft T8 LED Informational Video



General information for replacing fluorescent linear bulbs with Westinghouse direct install or ballast bypass 8 ft T8 LEDs.



4 ft TLED Informational Video



General information about Westinghouse TLED linear direct install and ballast bypass lamps.

LEDs for every lighting application!

Recessed Lighting

Perfect for providing overhead lighting for commercial and residential applications. A variety of reflector lamps, recessed downlight kits and adjustable recessed downlights provide multiple options.



Decorative Fixtures

Perfect for balancing function and design, as well as creating a personalized style in the home or workplace.



Ceiling Fans

Ideal for use in ceiling fans in both residential and commercial applications. Provide ample downward illumination for added ambience in dining rooms, bedrooms, and home entertainment areas.



Outdoor Lighting

Perfect for transforming outdoor areas into inviting spaces, as well as illuminating areas to ensure safety.



Specialty Color Lighting

Perfect for commercial or residential outdoor accent lighting. Ideal for holiday lighting, parties and special events. Weatherproof for indoor and outdoor use.



Office & Work Area Lighting

Ideal for both residential and commercial applications. Easily replace 4 foot medium bi-pin or 8 foot single pin linear fluorescent lamps with energy-saving LED alternatives. Dimmable options available.



Commercial Lighting

Perfect for applications where high lumens are desired, including barn/shop lighting, outdoor post top lanterns, wall pack lighting, bay lighting, street lights, parking lot lights and outdoor flood lighting.



Westinghouse

INNOVATION YOU CAN BE SURE OF



Call 1-800-999-2226 or visit www.westinghouselighting.com.

®, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.

Contact your Westinghouse Sales Representative for more information.