

MECHANICAL CONNECTORS
Aluminum Dual Rated
Transformer Connectors
2 HOLE NEMA PAD MOUNT
STL SERIES



FEATURES

- Made from 6061T-6 aluminum alloy.
- Electro-tin plated for low contact resistance.
- Two NEMA ½" holes for easy attachment.

RATINGS

VOLTAGE:
 600V max.

All dimensional data is listed in inches.

CAT. NO.	WIRE RANGE
STL250-4	250 MCM-6 AWG
STL250-6	250 MCM-6 AWG
STL250-8	250 MCM-6 AWG
STL350-4	350 MCM-6 AWG
STL350-6	350 MCM-6 AWG
STL350-8	350 MCM-6 AWG
STL500-4	500 MCM-4 AWG
STL500-6	500 MCM-4 AWG
STL500-8	500 MCM-4 AWG
STL750-4	750-250 MCM
STL750-6	750-250 MCM
STL750-8	750-250 MCM



NO. OF CONDUCTORS	MTG. HOLE DIA.	MTG. HOLE SPACING	TORQUE VALUE (IN./LBS.)	MTG. BOLT SIZE	WRENCH SIZE	LENGTH (L)	WIDTH (W)	HEIGHT (H)	STD. CTN. QTY.
4	0.560	1.750	330	1/2	5/16	6.240	0.875	1.125	6
6	0.560	1.750	330	1/2	5/16	7.960	0.875	1.125	6
8	0.560	1.750	330	1/2	5/16	9.680	0.875	1.125	6
4	0.560	1.750	400	1/2	5/16	6.960	1.000	1.440	6
6	0.560	1.750	400	1/2	5/16	9.060	1.000	1.440	6
8	0.560	1.750	400	1/2	5/16	11.160	1.000	1.440	6
4	0.560	1.750	550	1/2	5/16	7.500	1.130	1.630	6
6	0.560	1.750	550	1/2	5/16	9.740	1.130	1.630	6
8	0.560	1.750	550	1/2	5/16	12.030	1.130	1.630	6
4	0.560	1.750	550	1/2	3/8	8.570	1.440	2.000	3
6	0.560	1.750	550	1/2	3/8	11.420	1.440	2.000	3
8	0.560	1.750	550	1/2	3/8	14.280	1.440	2.000	3

