


- Flat Hanger Screws
- Tool Not Included
- TK - With Drill Pt.

- Flat Hanger Tool w/ Safety Sleeve
- Heavy Duty Steel Construction
- Installs Hanger Screws Quickly



CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
631	18135	1/4 x 3"	100	1000	2.38#	C
631TK	18136	1/4 x 2"	100	1000	2.38#	C
HBT	28950	Installation Tool	1	6	0.11#	Ea

Hanger Bolts • E-Z Hanger Bolt Tool | PC 4940

- Hanger Bolts
- Lag/Machine Screw Threads
- Tool Not Included
- EZ Hanger Bolt Tool

- Heavy Duty Steel Construction
- Threads On For Quick Installation
- Improved: With Ball Bearing Release To Reduce Hanger Bolt Lockup



CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
HB14	18100	1/4 x 3"	100	1000	2.78#	C
HB38	18105	3/8 x 3"	100	1000	6.82#	C
EZ14	28953	Installation Tool 1/4" For HB14	1	6	0.11#	Ea
EZ38	28956	3/8" For HB38	1	6	1.17#	Ea

Drive Screws | PC 4960


- Steel
- Hammer Drive



CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
216	18120	2 x 16	100	1000	2.66#	C

Fluorescent Fixture Hangers | PC 4970

- Top-Mount or Side Mount
- Fluorescent Fixture Hangers
- Steel
- For Use With 2, 3 or 4 Light Fixtures



CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
629	18125	Side-Mount 10 GA	100	500	6.18#	C
630	18130	Top-Mount 10 GA	100	500	6.18#	C