

Handi-Foam Expanding Sealant | PC 6190

- UL Classified
- ICBO Approved
- Polyurethane
- Pressurized Can
- Quick Drying

Handi-Foam is an expanding sealant which is a moisture-cure polyurethane foam. It is used to seal, bond, retrofit, insulate and deaden sound in electrical, plumbing, air-conditioning and refrigeration applications. It expands 2 to 3 times its extruded bead, and is rated R-5 for each inch of foam. Specifically designed to be dispensed as a bead for filling cracks. Substrate must be clean, firm, free of loose particles and dust.



CAT NO	UPC	CONTENTS	STD	MSTR	WT/STD	UNIT
HF340	90980	12 oz.	12	12	12.12#	Ea

RTV Silicone Sealant | PC 6200

- UL Classified
- Clear / White
- Neutral Cure Silicone
- Non Acetic & Non Corrosive
- Low Odor

- Flexible, Non Sagging, Watertight
- Withstands temperatures to 450° F



CAT NO	UPC	COLOR	CONTENTS	DESCRIPTION	STD	MSTR	WT/STD	UNIT
RTV3	17360	Clear	3 oz.	Tube	12	12	3.60#	Ea
RTV8	17366	Clear	7.25 oz.	Pressurized Can	12	12	4.53#	Ea
RTV10	17365	Clear	10.1 oz.	Cartridges	12	12	9.48#	Ea
RTV8W	10921	White	7.25 oz.	Pressurized Can	12	12	4.53#	Ea
RTV10W	17367	White	10.1 oz.	Cartridges	12	12	9.48#	Ea



100% RTV Silicone Sealant contains no solvents or fillers. It is provided in a pressurized can, 3 oz. tube or as a 10 oz. caulk. It is perfect for exterior and interior sealing and caulking, and adheres to metal, glass, marble, tile, ceramic, porcelain, painted surfaces, non oily woods, plastic and rubber. RTV is mildew resistant and can be used as an adhesive for bonding surfaces together.

Roof Mastic | PC 6210

- UL Classified
- Asbestos Free
- Meets ASTM 4586, ASTM D2822
- Meets Federal Specs SS-C-153

Premium grade roof mastic can be used in wet or dry locations to patch cracks & breaks, repair seams & joints and for sealing flashings. It adheres to all surfaces, wet or dry and forms a tight, strong weathertight seal which stays soft and pliable. Applied with a trowel or putty knife, it will cure to be a durable, resilient coating of excellent adhesion and unsurpassed weathering.



CAT NO	UPC	CONTENTS	STD	MSTR	WT/STD	UNIT
RKM1	30605	1 Quart	12	12	30.60#	Ea
RKM4	30610	1 Gallon	4	4	38.52#	Ea
RKM20	30615	5 Gallon	1	1	43.94#	Ea
RKM10	10920	10 oz.	12	12	9.48#	Ea

Dark Cutting Oil | PC 6220

- Petroleum Mineral Oil
- Chlorinated Additive

Dark Cutting Oil is specifically designed for threading steel and cast iron, and is recommended for cutting ferrous materials and ferrous alloys. It has been fortified with a chlorinated additive which works as an extreme pressure agent to allow an increased tolerance of alloyed or hard-grained pipe. Caution: Dark cutting oil contains active sulphur which will stain non-ferrous materials including copper, brass, stainless.



CAT NO	UPC	CONTENTS	STD	MSTR	WT/STD	UNIT
CO1	27525	1 Quart	12	12	24.96#	Ea
CO4	27530	1 Gallon	4	4	32.04#	Ea

See new products at www.lhdottie.com

UPC Vendor ID Code: 78-1002

