


ERT403LV**Reflector**

- "Cat's paw" retention spring

ET400LVAT	12V 50W MR16
ET400LVRAT	
EI400LVAT	



Height: 1-1/4" [31mm]
Outside Diameter: 5" [127mm]

**ERT403LV**

High Gloss Appliance White Trim
with Clear Specular Reflector


ERT403LVG

High Gloss Appliance White Trim
with Gold Reflector

ERT401LV**Baffle**

- "Cat's paw" retention spring

ET400LVAT	12V 50W MR16
ET400LVRAT	
EI400LVAT	



Height: 1-1/4" [31mm]
Outside Diameter: 5" [127mm]

**ERT401LVW**

High Gloss Appliance White Trim
Ring with White Baffle


ERT401LV

High Gloss Appliance White Trim
Ring with Black Baffle

ERT402LV**Eyeball - 30° Tilt**

- "Cat's paw" retention spring

ET400LVAT	12V 50W MR16
ET400LVRAT	
EI400LVAT	



Aperture: 2" [51mm]
Outside Diameter: 5" [127mm]


**ERT402LV**

High Gloss Appliance White Trim
Ring with White Eyeball

ERT404LV**Slot Aperture**

- "Cat's paw" retention spring

ET400LVAT	12V 50W MR16
ET400LVRAT	
EI400LVAT	



Slot: 1-3/8" x 2-1/8" [35mm x 54mm]
OD: 5" [127mm]

**ERT404LV**

High Gloss Appliance White Trim
and Slot