

## Insulpads PC 6120

- Polymers and Butyl Rubber
- Gray
- 100% Solid
- Low Odor
- Temperature Range: -20° F. to 180° F.
- Sound Barrier
- Non Hardening
- Flexible
- Forms Watertight Seal

| CAT NO | UPC   | SIZE           | STD | MSTR | WT/STD | UNIT |
|--------|-------|----------------|-----|------|--------|------|
| 68     | 15250 | 1/8" x 6" x 8" | 100 | 100  | 33.80# | C    |

## Duct Seal PC 6130

- UL Listed
- Adheres to Most Clean Surfaces
- Non Toxic / Asbestos Free

Duct Seal (Prest "O" Seal) is used to seal around junction box flashings, service masts, etc. It is heavy mastic, which is flexible and can be pressed into any shape to form a water and airtight seal.

| CAT NO | UPC   | SIZE | STD | MSTR | WT/STD | UNIT |
|--------|-------|------|-----|------|--------|------|
| LHD1   | 17230 | 1 lb | 50  | 50   | 50.00# | Ea   |
| LHD5   | 17235 | 5 lb | 10  | 10   | 50.00# | Ea   |

## Handi-Foam Expanding Sealant PC 6190

- Seals To Prevent Air And Moisture Infiltration
- Seals The Building Envelope
- Improves Building Efficiencies By Sealing Penetrations
- Improves Indoor Air Quality

Handi-Foam is an expanding sealant which is a moisture-cure polyurethane foam. It is used to seal, bond, retrofit, insulate and deaden sound in electrical, plumbing, air-conditioning and refrigeration applications. It expands 2 to 3 times its extruded bead, and is rated R-5 for each inch of foam. Specifically designed to be dispensed as a bead for filling cracks. Substrate must be clean, firm, free of loose particles and dust.

| CAT NO | UPC   | CONTENTS | STD | MSTR | WT/STD | UNIT |
|--------|-------|----------|-----|------|--------|------|
| HF340  | 90980 | 12 oz.   | 12  | 12   | 12.12# | Ea   |

## RTV Silicone Sealant PC 6200

- UL Classified
- Clear / White
- Neutral Cure Silicone
- Non Acetic & Non Corrosive
- Low Odor
- Flexible, Non Sagging, Watertight
- Withstands Temperatures to 450° F

| CAT NO | UPC   | COLOR | CONTENTS | DESCRIPTION     | STD | MSTR | WT/STD | UNIT |
|--------|-------|-------|----------|-----------------|-----|------|--------|------|
| RTV3   | 17360 | Clear | 3 oz.    | Tube            | 12  | 12   | 3.60#  | Ea   |
| RTV8   | 17366 | Clear | 8 oz.    | Pressurized Can | 12  | 12   | 4.53#  | Ea   |
| RTV10  | 17365 | Clear | 10.1 oz. | Cartridges      | 12  | 12   | 9.48#  | Ea   |
| RTV8W  | 10921 | White | 8 oz.    | Pressurized Can | 12  | 12   | 4.53#  | Ea   |
| RTV10W | 17367 | White | 10.1 oz. | Cartridges      | 12  | 12   | 9.48#  | Ea   |

## Caulking Gun PC 6600

- Double Friction Rod
- Long Trigger Leverage
- Thumb Pressure Release
- Standard Cartridge Size

For use with all types of caulks, sealants and adhesives.

| CAT NO | UPC   | DESCRIPTION  | STD | MSTR | WT/STD | UNIT |
|--------|-------|--------------|-----|------|--------|------|
| CG10   | 40770 | Caulking Gun | 1   | 24   | 0.940# | Ea   |

See new products at [Ihdottie.com](http://Ihdottie.com)

Dottie

D11