



**(Combo) Square/Slotted**



**(Combo) Slotted/Phillips**



**Slotted**

*Light to medium duty anchors for use in hollow walls. Mushroom head provides a large bearing surface.*

- Toggle Bolts
- Mushroom Head
- Slotted, Combo Slotted/Phillips or Combo Square/Slotted
- Zinc Plated Steel

CAT NO	UPC	SIZE	DESCRIPTION	STD	MSTR	WT/STD	UNIT
TBC82	16848	1/8 x 2	Slotted/Phillips (Combo)	50	500	0.75#	C
TB82DS	15392	1/8 x 2	Square/Slotted (Combo)	50	500	0.75#	C
TBC83	16846	1/8 x 3	Slotted/Phillips (Combo)	50	500	0.88#	C
TB83DS	15397	1/8 x 3	Square/Slotted (Combo)	50	500	1.00#	C
TBC84	16847	1/8 x 4	Slotted/Phillips (Combo)	50	500	1.02#	C
TB84DS	15402	1/8 x 4	Square/Slotted (Combo)	50	500	1.00#	C
TBC362	16849	3/16 x 2	Slotted/Phillips (Combo)	50	500	1.63#	C
TB362DS	16792	3/16 x 2	Square/Slotted (Combo)	50	500	1.63#	C
TBC363	16850	3/16 x 3	Slotted/Phillips (Combo)	50	500	1.84#	C
TB363DS	16797	3/16 x 3	Square/Slotted (Combo)	50	500	2.25#	C
TBC364	16855	3/16 x 4	Slotted/Phillips (Combo)	50	500	2.16#	C
TB364DS	16802	3/16 x 4	Square/Slotted (Combo)	50	500	2.50#	C
TB366	16810	3/16 x 6	Slotted	50	500	3.28#	C
TBC42	16859	1/4 x 2	Slotted/Phillips (Combo)	50	500	2.65#	C
TBC43	16860	1/4 x 3	Slotted/Phillips (Combo)	50	500	3.22#	C
TB43DS	15197	1/4 x 3	Square/Slotted (Combo)	50	500	3.25#	C
TBC44	16865	1/4 x 4	Slotted/Phillips (Combo)	50	500	3.80#	C
TB44DS	15202	1/4 x 4	Square/Slotted (Combo)	50	500	3.50#	C
TB45	15205	1/4 x 5	Slotted	50	500	3.98#	C
TB46	15210	1/4 x 6	Slotted	50	500	4.50#	C
TB383	16815	3/8 x 3	Slotted	50	250	6.68#	C
TB384	16820	3/8 x 4	Slotted	50	250	8.47#	C
TB385	16825	3/8 x 5	Slotted	50	250	8.00#	C
TB386	16830	3/8 x 6	Slotted	25	125	8.89#	C
TB124	16835	1/2 x 4	Slotted	25	125	11.12#	C
TB125	16840	1/2 x 5	Slotted	25	125	11.09#	C
TB126	16845	1/2 x 6	Slotted	25	125	11.06#	C

TOGGLE & STOVE BOLTS



### Zinc Chromate & Stainless Steel

**Zinc Chromate** plating is the most widely used plating, and is designated in our catalog as Zinc plated. It has good to excellent corrosion resistance and is relatively non-toxic.

**Stainless Steel** is provided in **18-8** unless other grade/s are requested. 18-8 is durable, non-magnetic and highly corrosion resistant. It is the most popular and readily available.

