


Jack chain is used for suspending fixtures.

- Jack Chain
- Steel
- Used For Suspending Fixtures

9)	CAT NO	UPC	GAUGE	DIAMETER	WORK LOAD	BREAK LOAD	SIZE	STD	MSTR	WT/STD	UNIT	
	CH1010 CH10P (Pail)	27475 27405	#10 #10	.135 .135	43 lbs 43 lbs	170 lbs 170 lbs	#10 #10	100' 300'	500' 300'	14.95# 43.90#	C	
	CH1212 CH12P (Pail)	27485 27415	#12 #12	.105 .105	29 lbs 29 lbs	115 lbs 115 lbs	#12 #12	100' 300'	1000' 300'	8.78# 27.00#	C	
	CH1414	27495	#14	.080	16 lbs	65 lbs	#14	100'	1000'	5.18#	С	
	CH1616	27490	#16	.080	10 lbs	40 lbs	#16	100'	1000'	3.00#	С	

## Double Loop Chain • Bright Galvanized | PC 5010



Double loop is a locked link chain with higher load ratings than jack chain. Because the links cannot be opened it requires the use of the S hook.

- Double Loop Jack Chain
- Locked Link
- Steel

4	CAT NO	UPC	GAUGE	DIAMETER	WORK LOAD	BREAK LOAD	SIZE	STD	MSTR	WT/STD	UNIT	
	DL2/0 DL1/0	28055 28050	#10 #11	.135 .120	255 lbs 200 lbs	1020 lbs 800 lbs	#2/0 #1/0	100 100	500 500	17.43# 13.32#	C	
	DL1 DL2 DL3	28060 28065 28070	#12 #13 #14	.105 .091 .080	155 lbs 115 lbs 90 lbs	620 lbs 460 lbs 360 lbs	#1 #2 #3	100 100 100	500 500 500	10.22# 8.25# 6.40#	CCC	

**WORKING LOAD LIMIT** designates the maximum stress in pounds which should ever be applied to chain. This refers also to chain in the best condition, when new and when the load is applied uniformly to a straight, untwisted length of chain.

BREAK TEST LOAD is the minimum load in pounds at which new chain has been found by experience to break, under tests in which the load is applied in direct tension to a straight length of chain with a uniform rate of speed on a standard chain testing machine.

**STANDARD FINISH: BRIGHT GALV** Our chain is made from quality, silver bright, galvanized steel wire. Tests have shown chain made from galvanized wire to be superior in rust resistance to chain which is zinc plated after forming.

## U Bolts • Zinc Plated | PC 4870



U Bolts are generally used to support conduit from strut. Provided with straps and nuts. Pipe sizes are inside diameters.

- U Bolts
- Zinc Plated
- Sizes Thru 4" Incl. Hex Nuts & Plate

CAT NO	UPC	PIPE SIZE	Α	В	С	Т	STD	MSTR	WT/STD	UNIT
U50 U75 U100	17910 17915 17920	1/2" 3/4" 1"	1/4" 1/4" 1/4"	1" 1-1/8" 1-3/8"	1-3/4" 2" 2-3/4"	7/8" 1" 1-1/8"	25 25 25	25 25 25	2.22# 2.42# 2.91#	C C C
U125 U150 U200	17925 17930 17935	1-1/4" 1 1/2" 2"	5/16" 5/16" 5/16"	1-3/4" 2" 2-1/2"	3" 3" 3-1/2"	1-3/8" 1-3/8" 1-3/8"	25 25 25	25 25 25	4.59# 4.84# 5.54#	CCC
U250 U300 U350 U400	17940 17945 17950 17955	2-1/2" 3" 3-1/2" 4"	3/8" 3/8" 1/2" 1/2"	3" 3-1/2" 4" 4-1/2"	4" 4-1/2" 5-1/2" 6-1/2"	1-1/4" 1-5/8" 1-1/2" 2-1/4"	10 10 10 10	10 10 10 10	3.71# 4.17# 9.61# 10.16#	CCCC

