

- MT SeriesAvailable up to 1200 Watts
- CTS SeriesAvailable up to 1200 Watts
- HP SeriesAvailable up to 1200 Watts

- vPro SeriesAvailable up to 300 Watts



	OUTPUT VOLTAGE	CERTIFICATION	AVAILABLE WATTAGE
MT Series	» 11 Volts » 12 Volts » 13 Volts » 14 Volts » 15 Volts	» UL Listed to U.S. and Canadian safety standards for landscape lighting transformers (UL 1838)	» 300 W » 600 W » 900 W » 1200 W
			HOUSING » 304 Domestic stainless steel » 20 gauge
CTS Series	» 12 Volts » High/low setting	» UL Listed to U.S. and Canadian safety standards for landscape lighting transformers (UL 1838)	DIMENSIONS » 17" h. x 9" w. x 5½" d.
			PRIMARY PROTECTION » Grounded and isolated with encapsulated core and coil » Auto thermal shut-off
HP Series	» 12 Volts » 13 Volts » 14 Volts » 15 Volts » 16 Volts » 17 Volts » 19 Volts » 22 Volts	» UL Listed to U.S. and Canadian safety standards for general purpose transformers (UL 506)	SECONDARY PROTECTION » Magnetic circuit breaker » Resettable » Toggle switch may be used for manual on/off switching
			ADDITIONAL FEATURES » LED on/off indicators » Removable swing-down enclosure bottom » Adjustable Cable Raceway Feeder (ACRF) » 2" and multiple ½"–¾" knockouts for conduit mounting » Large terminal strip for multiple low voltage cable connections » Accessory terminal strip for installation of external switching devices » 120-volt terminal strip for hardwiring » 120-volt accessory receptical » Removable door with weather-resistant seal » Easy to read operating instructions inside door » Louvered vents for maintaining a cool operating temperature » Lockable stainless steel latch » HP Series only: Extended terminal leads with dead front covers for hard wiring alternatives



AVAILABLE WATTAGE	
» 75 W » 75 × 2 W » 150 W » 150 × 2 W	
OUTPUT VOLTAGE	
» User adjustable to 15V Max.	
HOUSING	DIMENSIONS
» 304 Domestic stainless steel » 20 gauge	» 19¼" h. x 6⅝" w. x 3⅛" d.
PRIMARY PROTECTION	SECONDARY PROTECTION
» Built in slow start, microprocessor controlled primary overload	» Microprocessor controlled automatic output power limit
ADDITIONAL FEATURES	
» Low profile, light weight, stainless-steel enclosure » Ease of handling and installation flexibility » Solid-state technology » Downloadable app allows control by any Bluetooth enabled Apple or Android device » User-friendly interface for fast, easy set up » Astronomic programming with multiple on/off and dimming » Smooth dimming from full bright to 0% without stepping » On-the-fly override for all control aspects » Self-adjusting to protect against overload » Available in single or double circuits; double circuit dimming individually addressable » Multiple wattage options from 75 to 500 » Can be used with halogen and LED systems » Outdoor/indoor rated » Password protected	
CERTIFICATION	
» UL Listed to U.S. and Canadian safety standards for landscape lighting transformers (UL 1838)	

ORDERING INFORMATION <i>Select appropriate choice from each column</i>					example: MT-900-RP
Model	Wattage	Finish <i>(Clear Coat finish is standard)</i>		Control Option	
CTS	300	B	Black	GT	Granite
MT	600	Z	Architectural Bronze	TC	Terracotta
HP	900	DZ	Dark Bronze	R	Rust
	1200	LZ	Light Bronze	HG	Hunter Green
VP	75	SB	Special Bronze	M	Mocha
	75×2	G	Verde	WB	Weathered Bronze
	150	P	Pewter	WI	Weathered Iron
	150×2	BR	Architectural Brick	W	White

