



# RAB Lighting LED Quick Reference Sheet

	Product Part Number	Description	Voltage	Lumen Output	Mounting	DLC Listed
Area Lights / Shoebox Fixtures	ALED2T78	78W LED Area light / Equal to 250W MH / Type II Distribution	120-277	7,716	square pole	YES
	ALED3T78	78W LED Area light / Equal to 250W MH / Type III Distribution	120-277	6,911	straight square pole	YES
	ALED4T78	78W LED Area light / Equal to 250W MH / Type IV Distribution	120-277	7,564	straight square pole	YES
	ALED2T150	150W LED Area light / Equal to 400W MH / Type II Distribution	120-277	14,038	straight square pole	YES
	ALED3T150	150W LED Area light / Equal to 400W MH / Type III Distribution	120-277	12,526	straight square pole	YES
	ALED4T150	150W LED Area light / Equal to 400W MH / Type IV Distribution	120-277	14,349	straight square pole	YES
Wallpacks	SLIM57	57W Wallpack / Equal to 250W MH / Semi Cutoff	120-277	4,312	Mounts Direct to wall	YES
	SLIM62	62W Wallpack / Equal up to 400W MH / Semi Cutoff	120-277	4,775	Mounts Direct to wall	YES
	WP2LED37	37W Wallpack / Equal up to 250W MH / Traditional Non-Cutoff	120-277	4,329	Mounts Direct to wall	YES
	WP3LED55	55W Wallpack / Equal to 400W MH / Traditional Non-Cutoff	120-277	6,645	Mounts Direct to wall	YES
Smaller Floodlights	FFLED18	18W Square flood / Equal up to 150W MH	120-277	1,681	1/2" Threaded Male adapter	YES
	FFLED39	39W Square flood / Equal up to 175W MH	120-277	4,596	1/2" Threaded Male adapter	YES
	FFLED39T	39W Square flood / Equal up to 175W MH	120-277	4,596	Trunnion Mount	YES
	FFLED39SF	39W Square flood / Equal up to 175W MH	120-277	4,596	Slipfitter Mount	YES
	FFLED80	80W Square flood / Equal up to 250W MH	120-277	9,672	1/2" Threaded Male adapter	YES
	FFLED80T	80W Square flood / Equal up to 250W MH	120-277	9,672	Trunnion Mount	YES
	FFLED80SF	80W Square flood / Equal up to 250W MH	120-277	9,672	Slipfitter Mount	YES
Larger Floodlights	FXLED78T	78W Square flood Curved back / Equal up to 320W MH	120-277	7,597	Trunnion Mount	YES
	FXLED78SF	78W Square flood Curved back / Equal up to 320W MH	120-277	7,597	Slipfitter Mount	YES
	FXLED150T	150W Square flood Curved back / Equal up to 400W MH	120-277	14,440	Trunnion Mount	YES
	FXLED150SF	150W Square flood Curved back / Equal up to 400W MH	120-277	14,440	Slipfitter Mount	YES
Extra Large Floodlights	FXLED200T	200W Square flood Curved back / Equal 400W+ MH	120-277	27,005	Trunnion Mount	NO
	FXLED200SF	200W Square flood Curved back / Equal 400W+ MH	120-277	27,005	Slipfitter Mount	NO
	FXLED300T	300W Square flood Curved back / Equal 1000W MH	120-277	38,292	Trunnion Mount	YES
	FXLED300SF	300W Square flood Curved back / Equal 1000W MH	120-277	38,292	Slipfitter Mount	YES
Drill Mounted Steel Poles	PS4-07-20D2 / ABK4-07	4" Straight Square Steel - 7 gauge 20' - Drilled Pole	-	-	Anchor bolts	-
	PS4-11-20D2 / ABK4-11	4" Straight Square Steel - 11 gauge 20' - Drilled Pole	-	-	Anchor bolts	-
	PS4-07-25D2 / ABK4-07	4" Straight Square Steel - 7 gauge 25' - Drilled Pole	-	-	Anchor bolts	-
	PS4-11-25D2 / ABK4-11	4" Straight Square Steel - 11 gauge 25' - Drilled Pole	-	-	Anchor bolts	-
Tennon Mounted Steel Poles	PS4-07-30D2 / ABK4-07	4" Straight Square Steel - 7 gauge 30' - Drilled Pole	-	-	Anchor bolts	-
	PS5-07-30D2 / ABK5	5" Straight Square Steel - 7 gauge 30' - Drilled Pole	-	-	Anchor bolts	-
	PS5-11-30D2 / ABK5	5" Straight Square Steel - 11 gauge 30' - Drilled Pole	-	-	Anchor bolts	-
	PS4-07-20WT / ABK4-07	4" Straight Square Steel - 7 gauge 20' - Tennon Mount	-	-	Anchor bolts	-
	PS4-11-20WT / ABK4-11	4" Straight Square Steel - 11 gauge 20' - Tennon Mount	-	-	Anchor bolts	-
	PS4-07-25WT / ABK4-07	4" Straight Square Steel - 7 gauge 25' - Tennon Mount	-	-	Anchor bolts	-
	PS4-11-25WT / ABK4-11	4" Straight Square Steel - 11 gauge 25' - Tennon Mount	-	-	Anchor bolts	-
	PS4-07-30WT / ABK4-07	4" Straight Square Steel - 7 gauge 30' - Tennon Mount	-	-	Anchor bolts	-
	PS5-07-30WT / ABK5	5" Straight Square Steel - 7 gauge 30' - Tennon Mount	-	-	Anchor bolts	-
	PS5-11-30WT / ABK5	5" Straight Square Steel - 11 gauge 30' - Tennon Mount	-	-	Anchor bolts	-
Pole Accessories	BAD4	4" Internal tenon adapter	-	-	-	-
	BAD5	5" Internal tenon adapter	-	-	-	-
	BULL2	2 light bullhorn	-	-	-	-
	BULL3	3 light bullhorn	-	-	-	-
	MCB	Curved wall bracket single bullhorn	-	-	-	-

# RAB Lighting LED Quick Reference Sheet

	Product Part Number	Description	Voltage	Lumen Output	Mounting	DLC Listed
Parking Garage Fixtures	PRT30	30W LED Garage Light / Equal to 100W MH	120-277	3,455	Surface / Pendant	YES
	PRT42	42W LED Garage Light / Equal to 150W MH	120-277	4,833	Surface / Pendant	YES
	PRT55	55W LED Garage Light / Equal to 175W MH	120-277	6,085	Surface / Pendant	YES
Linear Washdown	SHARK2-25W/D10*	2' LED Impact-resistant linear washdown - IP66 Rating	120-277	2,697	Surface	NO
	SHARK2-25W/D10*	2' LED Impact-resistant linear washdown - IP66 Rating	120-277	2,697	Surface	NO
	SHARK4-36W/D10*	4' LED Impact-resistant linear washdown - IP66 Rating	120-277	4,192	Surface	NO
	SHARK4-50W/D10*	4' LED Impact-resistant linear washdown - IP66 Rating	120-277	5,161	Surface	NO
Vandal-Resistant Canopy Light	VANLED10	10W LED Square Canopy Mount / Equal to 50W MH	120-277	1,462	Surface mount	NO
	VANLED20	20W LED Square Canopy Mount / Equal to 70W MH	120-277	2,366	Surface mount	YES
	VANLED40	40W LED Square Canopy Mount / Equal to 100W MH	120-277	4,475	Surface mount	YES
	VANLED52	52W LED Square Canopy Mount / Equal to 150W MH	120-277	5,494	Surface mount	YES
	VANLED65	65W LED Square Canopy Mount / Equal to 175W MH	120-277	6,054	Surface mount	YES
	VANLED75	75W LED Square Canopy Mount / Equal to 200W MH	120-277	6,818	Surface mount	YES
High Bay Rail	RAIL95W	20" LED HIGH BAY / Equal to 200W MH	120-277	11,657	Others Aircraft Cable / Chain	YES
	RAIL150W	20" LED HIGH BAY / Equal to 250W MH	120-277	17,964	Others Aircraft Cable / Chain	YES
	RAIL185W	30" LED HIGH BAY / Equal to 320W MH	120-277	23,503	Others Aircraft Cable / Chain	YES
	RAIL225W	30" LED HIGH BAY / Equal to 400W MH	120-277	27,279	Others Aircraft Cable / Chain	YES
Troffers	TRLED2X2-37N/D10*	2X2 37W LED Troffer	120-277	3,370	Grid Ceiling	YES
	TRLED2X2-50N/D10*	2X2 50W LED Troffer	120-277	4,230	Grid Ceiling	YES
	TRLED2X4-37N/D10*	2X4 37W LED Troffer	120-277	3,451	Grid Ceiling	YES
	TRLED2X4-50N/D10*	2X4 50W LED Troffer	120-277	4,233	Grid Ceiling	YES
Panels	PANEL1X4-34N	1X4 34W LED PANEL	120-277	2,980	Grid Ceiling	YES
	PANEL1X4-41N	1X4 41W LED PANEL	120-277	3,238	Grid Ceiling	YES
	PANEL1X4-52N	1X4 52W LED PANEL	120-277	4,083	Grid Ceiling	NO
	PANEL2X2-34N	2X2 34W LED PANEL	120-277	3,392	Grid Ceiling	YES
	PANEL2X2-41N	2X2 41W LED PANEL	120-277	3,753	Grid Ceiling	YES
	PANEL2X2-52N	2X2 52W LED PANEL	120-277	4,679	Grid Ceiling	YES
	PANEL2X4-44N	2X4 44W LED PANEL	120-277	4,778	Grid Ceiling	YES
	PANEL2X4-59N	2X4 59W LED PANEL	120-277	6,227	Grid Ceiling	YES
2" Downlights New Construction	RDLED2R8-30-YN-TW/ND2T	2" Round 8W LED 3500K White, IC Rated, dimming	120V Only		Recessed	Energy Star
	RDLED2S8-30-YN-TW/ND2T	2" Square 8W LED 3500K White, IC Rated, dimming	120V Only		Recessed	Energy Star
2" Downlights Remodeler	RDLED2R8-30-YN-TW	2" Round 8W LED 3500K White, IC Rated, dimming	120V Only		Recessed	Energy Star
	RDLED2S8-30-YN-TW	2" Square 8W LED 3500K White, IC Rated, dimming	120V Only		Recessed	Energy Star
4" Downlights New Construction	NDIC4R12F / NDLED4R-50YN-S-S	4" Round 12W LED 3500K Specular Silver Trim & Cone	120V Only		Recessed	-
	NDIC4S12F / NDLED4S-50YN-S-S	4" Square 12W LED 3500K Specular Silver Trim & Cone	120V Only		Recessed	-
4" Downlights Remodeler	RDLED4R12F-50YN-S-S	4" Round 12W LED 3500K Specular Silver Trim & Cone	120V Only		Recessed	-
	RDLED4S12F-50YN-S-S	4" Square 12W LED 3500K Specular Silver Trim & Cone	120V Only		Recessed	-
6" Downlights New Construction	NDIC6R26F / NDLED6R-50YN-S-S	6" Round 26W LED 3500K Specular Silver Trim & Cone	120-277V		Recessed	-
	NDIC6S26F / NDLED6S-50YN-S-S	6" Square 26W LED 3500K Specular Silver Trim & Cone	120-277V		Recessed	-
6" Downlights Remodeler	RDLED6R26F-50YN-S-S	6" Round 26W LED 3500K Specular Silver Trim & Cone	120-277V		Recessed	-
	RDLED6S26F-50YN-S-S	6" Square 26W LED 3500K Specular Silver Trim & Cone	120-277V		Recessed	-

\* Dimming Capability

Note: Performance above based on 5000K color temperature. Other color temperatures offered. Photocell, 480V and bi-level dimming options are available on most products.