

© COMMERCIAL S FANS

1/4 HP AIR CIRCULATORS Pedestal & Wall Mount

MOTOR: 1/4 HP, 3 Speed, 120V, 1 Phase, ball-bearing, open ventilated, permanently lubricated, permanent split capacitor SWITCH: Pull Chain

- CORD: 9' long SJT type 3 conductor
- GUARD: Coated steel with retaining clips

Adjusts center of fan from 43" to 60" POLE:

ALL FAN COMPONENTS SHIPPED IN ONE UPS-ABLE CARTON

WALL MOUNT

נ(∬ך

PEDESTAL MOUNT

US

MODELS	BLADE SIZE	MOTOR TYPE	FAN TYPE	FAN MOUNT	MOTOR HP	CFM MAX VELOCITY	AMPS (HIGH)	PRICE EACH
CACU 24-P	24"		Non- Oscillating	Dedeetel		5,400	2.3	\$210.65
CACU 30-P	30"			Non- Pedestal		6,700	2.4	\$232.65
CACU 24-W	24"				Wall] [5,400	2.3
CACU 30-W	30"	Open		vvan	1/4	6,700	2.4	\$187.00
CACU 24-PO	24"	Ventilated	entilated Oscillating	Pedestal		5,400	1.5	\$249.15
CACU 30-PO	30"	1				6,700	2.0	\$261.25
CACU 24-WO	24"			Wall] [5,400	1.5	\$212.85
CACU 30-WO	30"			vvan		6,700	2.0	\$231.00

Meets Federal OSHA Requirements / 1 Year LIMITED WARRANTY

1/3 HP HEAVY DUTY AIR CIRCULATORS Pedestal

MOTOR: 1/3 HP, 3 speed, 120V, 1 Phase, ball-bearing, open ventilated, permanently lubricated, permanent split capacitor SWITCH: Pull Chain

CORD:

- 9' long SJT type 3 conductor GUARD: Coated steel with retaining clips
- POLE: Adjusts center of fan from 43" to 60"

ALL FAN COMPONENTS SHIPPED IN ONE UPS-ABLE CARTON

MODELS	BLADE SIZE	MOTOR TYPE	FAN TYPE	FAN MOUNT	MOTOR HP		AMPS (HIGH)	PRICE EACH
CACU 30-P-HD	00"	Open Ventilated	Non-Oscillating	Dodootol	1/3	7,000	3.6	\$270.60
CACU 30-PO-HD	30"		Oscillating	Pedestal			2.9	\$334.40

Meets Federal OSHA Requirements / 1 Year LIMITED WARRANTY

c(UL)us

DIRECT DRIVE PORTABLE BLOWERS

MOTOR:	1/3 HP, 2 speed, 120V, 3.6 amp, ball-bearing, ventilated, lubricated
BLADE:	Aluminum
CORD:	6' long SJT type 3 conductor
GUARD:	Spiral Wire (front & rear)
WHEELS:	5" rubber
HOUSING:	20 gauge steel powder coated

MODEL #	CFM MAX VELOCITY	CORD LENGTH	SWITCH	WT (LBS)	PRICE EACH
CPBS 30-D	6,700	6'	ROCKER	60	\$317.35
CPB 30-D	6,700	6'	ROCKER	52	\$278.85
CPB 36-D	8,500	10'	ROTARY	70	\$345.40

Meets Federal OSHA Requirements / 1 Year LIMITED WARRANTY

BELT DRIVE PORTABLE BLOWERS

MOTOR:	2 speed, 120V, 3.6 amp, ball-bearing, ventilated, permanently lubricated
BLADE:	Aluminum
SWITCH:	Rocker
CORD:	8' long SJT type 3 conductor
GUARD:	Spiral Wire (front & rear)
WHEELS:	8" rubber
HOUSING:	20 gauge steel powder coated

MODEL #	SIZE	MOTOR HP	CFM MAX VELOCITY	MAX AMPS	WT (LBS)	PRICE EACH
CPB 36-B	36"	1/3	8,600	4.8	82	\$376.20
CPB 42-B	42"	1/2	12,000	4.3	93	\$482.90
CPB 48-B	48"	3/4	14,000	9.0	129	\$652.85

Meets Federal OSHA Requirements / 1 Year LIMITED WARRANTY



COMMERCIAL FLOOR FANS

MOTOR: 1/5 HP, 3 speed, sleeve-bearing, ventilated, permanently lubricated SWITCH: Rotary

US

CORD: 7' long, SJT type 3 conductor GUARD: Coated steel with retaining clips



CFM PRICE EACH MAX AMPS WT (LBS) MODEL # HIGH MEDIUM LOW 1,050 CF-12 875 750 0.6 10 \$48.95 CF-18 1,600 1.4 16 1,480 1,380 \$60.50 CF-20 1,725 1,600 1,480 1.9 17 \$83.60

Meets Federal OSHA Requirements / 1 Year LIMITED WARRANTY



SWIVEL MODEL (CPBS 30-D)



STANDARD MODEL (CPB 36-D)



DISTRIBUTED BY:

© Copyright 2018; TPI Corporation | 1-800-682-3398 | 1-423-477-4131 | www.tpicorp.com | answers@tpicorp.com