

Bulb Shape	Base	Watts	Nominal Length (in)	Order Code	Description	Case Qty	Rated Life (hrs)	Initial Lumens	Mean Lumens	Color Temp K	CRI	High Color Rendering	Energy Savings	Reduced Wattage	Meets Federal Minimum Efficiency Standards	Footnotes	Warning and Caution Notices	Additional Information
Other T8 Lengths (continued)																		
5' T8 w/Starcoat®																		
T8	Medium Bi-Pin (G13)	40	60.0	15950	F40T8/SP30	24	20000	3600	3240	3000	75	☞					101	
		40	60.0	15951	F40T8/SP35	24	20000	3600	3240	3500	75	☞					101	
		40	60.0	15952	F40T8/SP41	24	20000	3600	3240	4100	75	☞					101	
		40	60.0	22660	F40T8/SPX30	24	20000	3725	3350	3000	84	☞					101	
		40	60.0	22661	F40T8/SPX35	24	20000	3725	3350	3500	84	☞					101	
		40	60.0	22662	F40T8/SPX41	24	20000	3725	3350	4100	84	☞					101	
6' T8 Instant Start																		
T8	Single Pin (Fa8)	35	72.0	10829	F72T8/CW	24	7500	3000	2730	4100	60						101	
		35	72.0	10835	F72T8/WW 6PK	6	7500	3100	2820	3000	52						101	Warm White
T8 PolyLux																		
2' T8 PolyLux																		
T8	Medium Bi-Pin (G13)	18	24.0	93311	F18T8/835/XLR	25	20000	1350	1280	3500	85	☞					101	
		18	24.0	93317	F18T8/841/XLR	25	20000	1350	1280	4100	85	☞					101	
4' T8 PolyLux																		
T8	Medium Bi-Pin (G13)	36	48.0	19991	F36WT8/835/XLR	25	20000	3350	3180	3500	85	☞					101	
		36	48.0	16856	F36WT8/841/XLR	25	20000	3350	3180	3500	85	☞					101	
5' T8 PolyLux																		
T8	Medium Bi-Pin (G13)	58	60.0	40120	F58T8/835PLYXLR	25	20000	5200	4940	3500	85	☞					101	
		58	60.0	40081	F58T8/841PLYXLR	25	20000	5200	4940	4000	85	☞					101	
6' T8 PolyLux																		
T8	Medium Bi-Pin (G13)	70	70.0	42792	F70T8/835PLYUX	25	20000	6300	5985	3500	85	☞					101	
		70	70.0	42793	F70T8/840PLYUX	25	20000	6300	5985	4100	85	☞					101	
T8 Preheat																		
12" T8																		
T8	Medium Bi-Pin (G13)	13	12.0	10098	F13T8/CW	24	7500	565	480	4100	60						101	
15" T8																		
T8	Medium Bi-Pin (G13)	14	15.0	10104	F14T8/CW	24	7500	685	580	4100	60						101	
18" T8																		
T8	Medium Bi-Pin (G13)	15	18.0	17911	F15T8/SP35	24	7500	940	850	3500	75	☞					101	
		15	18.0	19643	F15T8/SP41	24	7500	940	850	4100	72	☞					101	
		15	18.0	19644	F15T8/SPX30	24	7500	1000	900	3000	82	☞					101	
		15	18.0	19645	F15T8/SPX35	24	7500	1000	900	3500	82	☞					101	
		15	18.0	10142	F15T8/CW	24	7500	825	725	4100	60						101	
		15	18.0	10143	F15T8/CW 6PK	24	7500	825	725	4100	60						101	
		15	18.0	10134	F15T8/D	24	7500	700	615	6500	75	☞					101	Daylight
		15	18.0	21326	F15T8/K8 6PK	24	7500	940	850	3000	70	☞					104	Kitchen & Bath
		15	18.0	13968	F15T8/SUN 6PK	24	7500	620	525	5000	90	☞					101	Sunlight
		15	18.0	10147	F15T8/WW	24	7500	845	745	3000	52						101	Warm White
36" T8																		
T8	Medium Bi-Pin (G13)	30	36.0	16323	F30T8/SPX30	24	7500	2300	2140	3000	82	☞					101	
		30	36.0	10316	F30T8/CW 6PK	24	7500	2150	1980	4100	60						101	
		30	36.0	10310	F30T8/D	24	7500	1850	1625	6500	75	☞					101	Daylight
		30	36.0	22747	F30T8/K8 6PK	24	7500	2125	1910	3000	70	☞					104	Kitchen & Bath
		30	36.0	10318	F30T8/WW	24	7500	2150	1880	3000	52						101	Warm White
T12 Lamps																		
3' T12 Ecolux® – Rapid Start																		
25W																		
T12	Medium Bi-Pin (G13)	25	36.0	80080	F25T12/SP30/RS/WM/ECO	24	18000	2025	1780	3000	70	☞	\$	➔			101	
		25	36.0	80081	F25T12/SP35/RS/WM/ECO	24	18000	2025	1780	3500	73	☞	\$	➔			101	
		25	36.0	80065	F25T12/CWRSWM/ECO	24	18000	1925	1640	4100	60		\$	➔			101	
		25	36.0	80077	F25T12/WW/RS/WM/ECO	24	18000	1975	1640	3000	52		\$	➔			101	Warm White
30W																		
T12	Medium Bi-Pin (G13)	30	36.0	80087	F30T12/SP35/RS/ECO	24	18000	2350	2120	3500	73	☞					101	
		30	36.0	80088	F30T12/SP41/RS/ECO	24	18000	2350	2120	4100	72	☞					101	
		30	36.0	80089	F30T12/SPX30/RS/ECO	24	18000	2375	2140	3000	82	☞					101	
		30	36.0	80090	F30T12/SPX35/RS/ECO	24	18000	2375	2140	3500	82	☞					101	
		30	36.0	80083	F30T12/C50/RS/ECO	24	18000	1650	1350	5000	90	☞					101	Chroma 50
		30	36.0	80084	F30T12/CW/RS/ECO	24	18000	2200	1910	4100	60						101	