

35" Gard-N-Post™ Bollard Kit



GPBK35B/R

Gard-N-Post with pagoda-style light fixture included. Post is UV rated plastic for long outdoor life. Two non-chipping colors.


FEATURES AND BENEFITS

- Molded-in color is permanent—unlike painted posts where lawn equipment chips the color off
- Openings on both sides of the post for back-to-back power
- Low voltage separator provided for Power use on one side and Low Voltage on the other (phone, security, & cable TV)
- Perfect for wood decks, boat docks, and concrete walkways
- Makes a very low cost bollard
- Kit includes everything needed for installation, except anchor bolts, caulking, and bulb
- Includes Arlington's Large Louvered Pagoda Light Fixture
- (2) combination KOs for a UL Listed enclosure

CATALOG NUMBER	UPC/DCI/NAED MFG #018997	DESCRIPTION	UNIT PKG	STD PKG	DIM A	DIM B	DIM C	DIM D	DIM E
GPBK28B	76090	Black	1	1	6.070	6.070	-	28.500	5.000
GPBK35B	77040	Black	1	1	6.070	6.070	35.000	27.000	3.500
GPBK35BR	77041	Bronze	1	1	6.070	6.070	35.000	27.000	3.500

Add suffix "GC" to Catalog # when ordering in Canada, for example GPBK35BGC.
CSA listed with grounding lug.

PATENTED.



KIT COMES WITH...

Gard-N-Post & metal stabilizer, boot, (pagoda light fixture & decorative spacer or IN-AND-OUT™ cover), (2) blank device plates with gaskets & screws, low voltage separator, and removable KO plate with screws.

RECOMMENDED ANCHORS

(not included)...

Concrete: (4) 3/8" x 2-1/2 Tapcons®

Cast-In-Place Concrete:

(4) 3/8" anchor bolts

Wood Deck: (4) 3/8" bolts with nuts and washers

Tapcons® is a registered trademark of ITW Buildex.

INSTALLATION INSTRUCTIONS



Metal support post attaches easily to surface.



The non-metallic GARD-N-POST slides over the support post.



Both posts are held firmly in place with the supplied screws.



Place decorative curb over GARD-N-POST. Slide it down to cover the installation.



Press fit spacer to base of lamp.



Install pagoda light to post with locknut inside the top of the post. Wire fixture.