

COMPUTER CABLES

Stranded Multi-Conductor
Overall Aluminum Shield
S-R Insulation -300 Volt



CONSTRUCTION	
Conductor	- Stranded tinned copper multi-conductors
Insulation	- S-R PVC insulated with cabled conductors
Shield	- Aluminum polyester shield with stranded tinned copper drain Wire
Jacket	- Gray PVC Jacket

Standards:

- UL 758
- UL 444
- NEC Article 800
- UL Listed CM
- UL Recognized AWM Style 2464 80C 300 Volts
- cUL Listed Type CMG
- California State Fire Marshal Approved

Part #	AWG	Conductors	Stranding	Insulation Thickness	Jacket Thickness	Nom. O.D.	Lbs./M'
D22204	22	4	7/32	.010"	.032"	.188"	26.3
D22206	22	6	7/32	.010"	.032"	.214"	35.3
D22208	22	8	7/32	.010"	.032"	.237"	43
D22210	22	10	7/32	.010"	.032"	.260"	51.1
D22212	22	12	7/32	.010"	.032"	.281"	54.2
D22215	22	15	7/32	.010"	.035"	.303"	69.4
D22220	22	20	7/32	.010"	.035"	.333"	87.5
D22225	22	25	7/32	.010"	.035"	.375"	101

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.

Color Code: Vendor specific, please refer to vendor spec.