

NEW PRODUCT INFORMATION

Hi-Pro LED multi-beam lamps

High lumen, adjustable, multi-directional lamps for industrial and commercial applications

Features

- Replaces HID, CFL, and incandescent
- Direct wire range voltage 100-277V
- Approved for totally enclosed fixtures
- Hi bay or low bay
- Light panels lock into place creating 3 separate beam angle options
- IP65 rated
- 5 Year limited warranty



360° Beam



270° Beam



180° Beam

Available June, 2016

High Lumen Multi-beam Industrial/Commercial LED Lamps

Item Number	Lamp Description	Replaces Inc/CFL/HID	W	V	Base Type	CCT	Lm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack/Mstr.
S9750	25W/LED/HID/MB/5000K/100-277V	150/40/100	25	100-277	E26	5000K	3,250	6 3/8	50K	045923097508	24
S9751	40W/LED/HID/MB/5000K/100-277V	200/55/150	40	100-277	EX39	5000K	5,200	7 7/8	50K	045923097515	16
S9752	60W/LED/HID/MB/5000K/100-277V	300/85/250	60	100-277	EX39	5000K	7,800	8 1/2	50K	045923097522	12

Accessories

92-406	Mog to Med Socket Reducer for S9751, S9752	045923924064
80-929	Hard Wire Surge Protector	045923809293