

PLENUM CONTROL CABLE

Nonshielded Conductors
OMNIPLLEN



CONSTRUCTION

Conductor	- Stranded Bare copper
Insulation	- OMNIPLLEN
Shield	- None
Jacket	- OMNIPLLEN

Applications:

- Power limited control circuits
- Wiring of the following systems:
 - -Intercom
 - -Security
 - -Audio
- Suggested Voltage Rating: 300 Volts

Standards:

- NEC Article 725-CL3P, CMP, MPP

COLOR CODE CHART

Cond. #	Color
1	Black
2	Red
3	White
4	Green

Part #	AWG	Conductors	Insulation Thickness	Jacket Thickness	Nom. O.D.	Lbs./M'
G121402	14	2	.013"	.015"	.216"	38.8
G121402-07	14	2	.013"	.015"	.216"	38.8
G121403	14	3	.006"	.010"	.232"	53.4
G121404	14	4	.006"	.010"	.255"	75
G121202	12	2	.011"	.014"	.252"	56.5

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.

* **Part Number G121402-07 has an orange jacket.**