- UL Listed
- Pressure Cast or Bronze
- Bonding or Grounding
- With Steel, Stainless Steel, Brass or Bronze Screws

Bare ground clamps are used to connect bare copper wire to water pipe, rebar, ground rod or copper water tubing for grounding. Fittings are UL listed and cast from high strength, highly conductive copper alloy with steel, brass or bronze screws.



CAT NO	UPC	WIRE RANGE	DESCRIPTION	TYPE	PIPE SIZE	STD	MSTR	WT/STD	UNIT
20B	10005	8 Sol to 2 Str	Prsr Cast Brs Plated	Steel	1/2 to 1"	25	250	3.83#	С
20M 25	10010 10015	8 Sol to 2 Str 10 Sol to 2 Str	Prsr Cast Mlbl Finish Bronze	Steel Steel	1/2 to 1" 1/2 to 1"	25 25	250 250	4.40# 4.48#	C
DB25 DLI25	67500 28090	10 Sol to 2 Str 10 Sol to 2 Str	Bronze Direct Burial Bronze Direct Burial Lay in Feature	Bronze Stainless Steel	1/2 to 1" s 1/2 to 1"	25 25	250 250	4.79# 4.79#	C
DB25 and	DLI25 Appr	oved For Steel 4/6/8 F	,	Ottool					
DB2538 67503 10 Sol to 2 Str Bronze Direct Burial Bronze 1/2 to 1" 25 250 4.45# C DB2538 Dual Rated Suitable For Pipe or Steel Rebar 3/8 to 1" (#3 - #8). Accommodates Steel Rebar Without Disassembly									
PL25 27 DB27 DLI27	56470 10025 67502 28092	10 Sol to 2 Str 10 Sol to 2 Str 10 Sol to 2 Str 10 Sol to 2 Str	Bronze Bronze Bronze Direct Burial Bronze Direct Burial Lay in Feature	Brass Steel Bronze Stainless Steel	1/2 to 1" 1-1/4 to 2" 1-1/4 to 2" 3 1-1/4 to 2"	25 5 5 5	250 50 50 50	4.85# 2.18# 2.13# 2.13#	CCCC
1001* 1002* * Non UL	10027 10028 Approved	10 Sol to 2 Str 10 Sol to 2 Str	Bronze Bronze	Steel Steel	2-1/2 to 4" 4-1/2 to-6"	5 5	5 5	5.07# 9.12#	C

## Armored Ground Clamps | PC 5560

- UL Listed
- Pressure Cast or Bronze
- Bonding or Grounding
- With Steel or Stainless Steel Screws

Used to connect armored cable to water pipe for grounding. Special pressure bar grips armored cable insulation to decrease chances of grounding conductor being pulled out. Cast from high strength, highly conductive copper alloy.

**SCREW** 



CAT NO	UPC	WIRE RANGE	DESCRIPTION	TYPE	PIPE SIZE	STD	MSTR	WT/STD	UNIT
21B*	10030	8 Sol to 4 Str	Prsr Cast Brs Plated	Steel	1/2 to 1"	25	250	5.09#	С
21M 26 DLI26	10035 10040 28091	8 Sol to 4 Str 8 Sol to 4 Str 8 Sol to 4 Str	Prsr Cast Mlbl Finish Bronze Bronze Lay in Feature	Steel Steel Stainless Steel	1/2 to 1" 1/2 to 1" 3 1/2 to 1"	25 25 25	250 250 250	5.09# 5.83# 5.63#	CCC
26SWV 26SWV Inc	10042 cludes a pre	10 Sol to 6 Str essure bar that swings	Bronze Swivel Type s 360° for easy adjustment	Steel	1/2 to 1"	25	125	9.33#	С
28	10045	8 Sol to 4 Str	Bronze	Steel	1-1/4 to 2"	25	250	11.63#	С
28SWV 28SWV Inc	10046 sludes a pre	10 Sol to 6 Stressure bar that swings	Bronze swivel Type s 360° for easy adjustment	Steel	1-1/4 to 2"	5	5	3.05#	С
1102* 1103* * Non UL	10047 11048 Approved	8 Sol to 4 Str 8 Sol to 4 Str	Bronze Bronze	Steel Steel	2-1/2 to 4" 4-5-6"	5 5	5 5	6.60# 9.92#	C

