Hydraulic Pumps & Miscellaneous

The professional contractor looks to Greenlee for exceptional bolt cutters, hydraulic pumps, accessories and a variety of rope. Each product is designed to make your job faster, safer and easier – get the job done right with Greenlee. To choose the right tool for your job, contact customer service or see your local Greenlee distributor.



BOLT CUTTERS

GREENLEE

Heavy-Duty Bolt Cutters with Fiberglass Handles



SPECIFICATIONS		
CAPACITY	RB85*	RC40*
HDFBC18	5/16" (7.9 mm)	7/32" (5.6 mm)
HDFBC24	3/8" (9.5 mm)	9/32" (7.1 mm)
HDFBC30	1/2" (12.7 mm)	5/16" (7.9 mm)
HDFBC36	5/8" (15.9 mm)	11/32" (8.7 mm)
*Indicates bolt hardness in Rockwell units		

WEIGHT

HDFBC18 - 3.4 lbs. (1.5 kg); HDFBC24 - 10.3 lbs. (4.7 kg) HDFBC30 - 4.9 lbs. (2 kg); HDFBC36 - 7.6 lbs. (3.4 kg)

- · Unique cam bolt blade adjustment for easy cutter alignment.
- Forged steel blades for long life.
- Clevis-mounted blades for greater strength.
- Custom rubber grips for maximum power.
- Fiberglass handles are tough and lightweight.

CAT. NO.	UPC NO.	DESCRIPTION
HDFBC18	11277	Heavy-Duty Bolt Cutter with Fiberglass Handles
		18 in. (457 mm) Long
HDFBC24	11278	Heavy-Duty Bolt Cutter with Fiberglass Handles
		24 in. (610 mm) Long
HDFBC30	11279	Heavy-Duty Bolt Cutter with Fiberglass Handles
		30 in. (762 mm) Long
HDFBC36	11280	Heavy-Duty Bolt Cutter with Fiberglass Handles
		36 in. (914 mm) Long
11367	11367 😗	Blade Unit for HDFBC18
11342	11342 😗	Blade Unit for HDFBC24
11344	11344 😗	Blade Unit for HDFBC30
11346	11346 😗	Blade Unit for HDFBC36

Heavy-Duty Bolt Cutters



SPECIFICATIONS		
CAPACITY	RB85*	RC40*
HDBC24	3/8" (9.5 mm)	9/32" (7.1 mm)
HDBC30	1/2" (12.7 mm)	5/16" (7.9 mm)
HDBC36	5/8" (15.9 mm)	11/32" (8.7 mm)
HDBC42	3/4" (19.1 mm)	3/8" (9.5 mm)

*Indicates bolt hardness in Rockwell units

WEI	CHI
WIL	ulli

HDBC24 - 5.8 lbs. (2.6 kg); HDBC30 - 8.9 lbs. (4 kg); HDBC36 - 13.3 lbs. (6 kg); HDBC42 - 19.8 lbs. (9 kg)

- · Unique cam bolt blade adjustment for easy cutter alignment.
- Forged steel blades for long life.
- Clevis-mounted blades for greater strength.
- Custom rubber grips for maximum power.

CAT. NO.	UPC NO.	DESCRIPTION
HDBC24	11273	Heavy-Duty Bolt Cutter - 24 in. (610 mm) Long
HDBC30	11274	Heavy-Duty Bolt Cutter - 30 in. (762 mm) Long
HDBC36	11275	Heavy-Duty Bolt Cutter - 36 in. (914 mm) Long
HDBC42	11276	Heavy-Duty Bolt Cutter - 42 in. (1067 mm) Long
11342	11342 🔓	Blade Unit for HDBC24
11344	11344 🜀	Blade Unit for HDBC30
11346	11346 🜀	Blade Unit for HDBC36
11348	11348 🜀	Blade Unit for HDBC42

GREENLEE

Bolt Cutters



SPECIFICATIONS		
CAPACITY	RB85*	RC40*
BC14	1/4" (6.4 mm)	3/16" (4.8 mm)
BC18	5/16" (7.9 mm)	1/4" (6.4 mm)
BC24	3/8" (9.5 mm)	5/16" (7.9 mm)
BC30	1/2" (12.7 mm)	11/32" (8.7 mm)
BC36	5/8" (15.9 mm)	3/8" (9.5 mm)
*Indicates holt hardness in	Rockwell units	

WEIGHT	
BC14 - 2.4 lbs. (1.1 kg);	BC18 – 3.4 lbs. (1.5 kg);
BC24 - 5.8 lbs. (2.6 kg);	BC30 - 8.9 lbs. (4 kg);
BC36 - 13 3 lbs (6 kg)	

- Unique cam bolt blade adjustment for easy cutter alignment.
- · Forged steel blades for long life.
- · Clevis-mounted blades for greater strength.
- Custom rubber grips for maximum power.

CAT. NO.	UPC NO.	DESCRIPTION
BC14	11267	Standard Bolt Cutter - 14 in. (356 mm) Long
BC18	11268	Standard Bolt Cutter - 18 in. (457 mm) Long
BC24	11269	Standard Bolt Cutter - 24 in. (610 mm) Long
BC30	11270	Standard Bolt Cutter - 30 in. (762 mm) Long
BC36	11271	Standard Bolt Cutter - 36 in. (914 mm) Long
11281	11281 🚯	Blade Unit for BC14
11301	11301 🚯	Blade Unit for BC18
11306	11306 🚯	Blade Unit for BC24
11316	11316 🚯	Blade Unit for BC30
11321	11321 🚯	Blade Unit for BC36

Threaded Rod Cutter



SPECIFICATIONS	
Capacity	1/4" - 20 soft steel rod (6.4 mm); 3/8" - 16 soft steel rod (9.5 mm)
Weight	14.1 lbs. (6.4 kg)

- One stroke cuts through threaded rod.
- Cuts clean, eliminating the need to grind or file before threading a nut onto cut end.
- Wide base for stable cutting. Includes mounting hole for fast and easy permanent mounting to work surface.
- Strong forged steel cutting head with tool steel cutting die for long life.
- Includes: Threaded Rod Cutter, 1/4"- 20 Cutting Die Set, 3/8"- 16 Cutting Die Set.

CAT. NO.	UPC NO.	DESCRIPTION
36587	36587	Threaded Rod Cutter
37186	37186	1/4" - 20 Cutting Die Set
37187	37187	3/8" - 16 Cutting Die Set

HYDRAULIC PUMPS

GREENLEE

High-Pressure Hydraulic Hand Pump



Manual – Hand
10,000 psi (700 bar), .161 in ₃ (26 mm ₃) per stroke
25-1/2" (648 mm)
7" (178 mm)
6" (152 mm)

NOTE: See page 385 to select the proper hydraulic hose for this pump.

- · Portable and powerful, for use with Greenlee Benders.
- Versatile, operates in any position.
- Steel pump body and handle with rubber grip.
- Wide base for stability.
- Mounting holes for permanent positioning.
- Includes 3/8" (9.5 mm) female hydraulic connector and dust cap.

			WEI	GHT
CAT. NO.	UPC NO.	DESCRIPTION	LBS.	kg
755	15677	High-Pressure Hydraulic Hand Pump	18	8.2
18272	18272 🕧	🕽 Seal Kit- Repair		

Hydraulic Hand Pump



- · Lightweight and portable, for use with Greenlee Punch Drivers.
- Versatile, operates in any position.
- Single speed.
- Rugged steel pump body/reservoir with cast aluminum handle.
- Has mounting holes for easy, permanent mounting.

			WEIGHT	
CAT. NO.	UPC NO.	DESCRIPTION	LBS.	kg
767	13284	Hydraulic Hand Pump	6	2.7
04343	04343 🚯	Seal Kit Repair for Serial Code ABM		
13800	13800 🚯	*Seal Kit Repair for Serial Code 55D 8	k Up	
13801	13801 🚯	*Seal Kit Repair for Serial Code 61BG	thru 67BG	i
30242	30242 🚯	*Seal Kit Repair for Serial Code 68BG	TO BG331	81628
30242	30242	Seal Kit Repair for Serial Code BG331	816 & Up	

*NOTE: Must also purchase 30241 Follower

SPECIFICATIONS

Operation	Manual – Hand
Capacity	6,500 psi (448 bar), .0823 in ₃ (13 mm ₃) per stroke
Length	13" (330 mm)
Width	4" (102 mm)
Height	4" (102 mm)

NOTE: See page 385 to select the proper hydraulic hose for this pump.



Hydraulic Foot Pump



- Free both hands to position and hold the working tool.
- · Foot activated release lever.
- Hold-down pin keeps pedal down for storage and transport.
- Angled base bar keeps the pump upright and stable.
- Includes 1/4" (6.4 mm) female coupler with dust cap.

				WEIG	HT
CAT. NO.	UPC NO.		DESCRIPTION	LBS.	kg
1725	31353		Hydraulic Foot Pump	11	5
24496	24496	(3)	Seal Kit w/ RD Serial Code		
25214	25214	(3)	Seal Kit w/ RU Serial Code		
33336	33336	B	Seal Kit w/ VK Serial Code		

SPECIFICATIONS

Operation	Manual – Foot	
Capacity	6,500 psi (448 bar), .117 in ₃ (19 mm ₃) per stroke	
Length	16" (406 mm)	
Height	Pedal down 6" (152 mm), Pedal up 12" (305 mm)	
Width	8" (203 mm)	

NOTE: See page 385 to select the proper hydraulic hose for this pump.

Hand-Operated Hydraulic Pump



- Two-speed hydraulic pump. Ideal for use with remote cutting and crimping tools.
- Compact and lightweight easy to move around jobsites.
- Solid base with wide legs provides for good stability during operation.
- Built-in carrying handle.
- · Large, easy-to-grasp, retraction wheel.
- Equipped with 3/8" female screw-type hydraulic coupler.

				WEIGHT		
	CAT. NO.	UPC NO.	DESCRIPTION	LBS.	kg	
	7475H	07475	Hand-Operated Hydraulic Pump	18	8.2	
	07829	07829	Seal Kit			

SPECIFICATIONS

Max output pressure	10,000 psi (700 bar)
Useable oil capacity	0.75 quart (0.74 liter)
1st stage oil volume (200 psi)	0.82 cu in/stroke
2nd stage oil volume (10,000 psi)	0.16 cu in/stroke
Length (including coupler)	25" (635 mm)
Width	5-5/8" (143 mm)
Height	5-1/2" (140 mm)

NOTE: See page 385 to select the proper hydraulic hose for this pump.

Electric Hydraulic Pump



- Useable oil volume: 3 quarts (2.8 liters).
- For use with Greenlee 2" capacity benders.
- Automatic or manual ram-return selector valve provides more control from the pendant switch.
- Molded enclosure protects pump, motor and circuitry in tough working environments.
- Use with single-hose hydraulic systems with spring-return rams.

			WEIG	HT
CAT. NO.	UPC NO.	DESCRIPTION	LBS.	kg
975	33516	Electric Hydraulic Pump	51	23
34369	34369	R Seal Kit		

SPECIFICATIONS

Operation	120 VAC 1/2 HP (.375 kW)
Capacity	10,000 psi (700 bar); 250 inch, (4 L) per minute rapid advance; 18 inch, (.32 L) per minute at full pressure
Length	12" (305 mm)
Width	10" (254 mm)
Height	15-1/2" (394 mm)

NOTE: See page 385 to select the proper hydraulic hose for this pump.

GREENLEE

Electric Hydraulic Pump



- Useable oil volume: 6-1/4 guarts (5.9 liters)
- · For use with all Greenlee benders.
- Solid state controls for added reliability.
- · Low pressure for fast ram advance, automatically changes to low volume high pressure.
- Pendant control for advance, valve on pump for release.
- Use with single-hose hydraulic systems with spring-return rams.
- Equipped with four swivel casters.
- Cast aluminum reservoir for long life.

			WEIGHT	
CAT. NO.	UPC NO.	DESCRIPTION	LBS.	kg
960 SAPS	18297	Electric Hydraulic Pump	92	42
18416	18416	⊕ Seal Kit		

SPECIFICATIONS	S		
Operation 120 VAC 1-1/2 HP (1.12 kW)			
Capacity 10,000 psi (700 bar); 300 inch, (4.8 L) per minute rapid adva 54 inch, (.9 L) per minute at full pressure			
Length	12" (305 mm)		
Width	10-3/4" (223 mm)		
Height	22-5/16" (567 mm)		

NOTE: See page 385 to select the proper hydraulic hose for this pump.

Electric Hydraulic Pump



- Useable oil volume: 6 quarts (5.7 liters).
- · For use with all Greenlee benders.
- Handy pendant advance control on 980 and 980-22PS. The 980-22FS has a foot-control switch.
- Low voltage pendant coupled to solid state motor controls eliminates contact arcing for greater reliability and longer life.
- · Automatic or manual ram return selector valve provides more control from the pendant switch.
- · Molded enclosure protects pump, motor and circuitry in tough working environments.
- Use with single-hose hydraulic systems with spring-return rams.

			WEI	
CAT. NO.	UPC NO.	DESCRIPTION	LBS.	kg
980	33515	Electric Hydraulic Pump with Pendant	71	32
980-22	36314	Electric Hydraulic Pump	71	32
980-22PS	36313	Electric Hydraulic Pump with Pendant Switch	71	32
980-22FS	36315	Electric Hydraulic Pump with Foot Switch	71	32
34369	34369 🚯	Seal Kit		

Note: 980-22 is 220V pump only, no control switch

SPECIFICATIONS

Operation	980 – 120 VAC 1-1/2 Hp (1.12 kW) 980-22PS – 220 VAC 50Hz 1-1/2 Hp (1.12 kW)
Capacity	10,000 psi (700 bar); 250 inch, (4 L) per minute rapid advance; 54 inch, (.9 L) per minute at full pressure
Length	12" (305 mm)
Width	12" (305 mm)
Height	17-1/2" (445 mm)

NOTE: See page 385 to select the proper hydraulic hose for this pump.



ACCESSORIES

Hydraulic Hose Selection Guide

TOOL CAT. NO./DESCRIPTION	TOOL COUPLER	PUMP CAT. NO.	HOSE CAT./UPC NO.
750 Cable Cutter	1/4" Female Coupler	767	38316
750 Cable Cutter	1/4" Female Coupler	1725	37729
750 Cable Cutter	1/4" Female Coupler	975	17707
777 Bender	3/8" Female Coupler	755, 975, 980 or 960SAPS	11289
782 Bender	3/8" Female Coupler	755 or 975	11289
800 Cable Bender	1/4" Female Coupler	1725	37729
880 Bender	3/8" Female Coupler	755 or 975	11289
881 Bender	3/8" Female Coupler	980 or 960SAPS	11289
882 Bender	3/8" Female Coupler	755 or 975	11289
884 Bender	3/8" Female Coupler	980 or 960SAPS	11289
885 Bender	3/8" Female Coupler	980 or 960SAPS	11289
1731 C-Frame Punch Driver	1/4" Female Coupler	767	38316
1731 C-Frame Punch Driver	1/4" Female Coupler	1725	37729
1731 C-Frame Punch Driver	1/4" Female Coupler	755 or 975	11289
SDK202GL Cable Cutter	3/8" Male Coupler	7475H, 975 or 980	05850, 05851, 05852
RK06AT, RK06FT	3/8" Male Coupler	7475H, 975 or 980	05850, 05851, 05852
RK1230, RK1240, RK1240K	3/8" Male Coupler	7475H, 975 or 980	05850, 05851, 05852
RCCX	3/8" Male Coupler	7475H, 975 or 980	05850, 05851, 05852
RK1550	3/8" Male Coupler	7475H, 975 or 980	05850, 05851, 05852

Hydraulic Hose Units



- High pressure hydraulic hose units for use with Greenlee hydraulic numps
- Equipped with couplers and dust caps.

CAT. NO.	UPC NO.	DESCRIPTION
05850*	05850	10' X 1/4" Hose With (1) 3/8" Male Coupler and (1) 3/8" Female Coupler
05851*	05851	10' X 1/4" Non-Conductive Hose with (1) 3/8" Male Coupler and
		(1) 3/8" Female Coupler
05852*	05852	25' X 1/4" Non-Conductive Hose with (1) 3/8" Male Coupler and
		(1) 3/8" Female Coupler
11289*	11289	6' X 3/8" Hose with (2) 3/8" Male Couplers
17707*	17707	10' X 1/4" Hose with (1) 3/8" Male Coupler and
		(1) 1/4" Male Coupler
37728	37728	6' X 1/4" Hose with (1) 1/4" Male Coupler and
		(1) 1/4" NPT Thread
37729*	37729	10' X 1/4" Hose with (2) 1/4" Male Couplers
38316	38316	3' X 1/4" Hose with (1) 1/4" Male Coupler and
		(1) 1/4" NPT Swivel Threaded Fitting
06302	06302	3' X 1/4" Hose with (1) 1/4" NPT Male Threaded Fitting
		and (1) 1/4" NPT Swivel Threaded Fitting
A F 11 1 11 1 1 1 1	,	

^{*} Filled with hydraulic oil.

			HOSE UNIT CAT./UPC NO.					COUPL CAT./U				
CAT. NO.	UPC NO.	DESCRIPTION	05850	05851					37729	38316	37614	3548GB/
50386	50386	3' x 1/4" (.9 m x 6.4 mm) Hydraulic Hose								1		
3687GB	50760	6' x 3/8" (1.8 m x 9.5 mm) Hydraulic Hose				1						
51688	51688	6' x 1/4" (1.8 m x 6.4 mm) Hydraulic Hose						1				
52515	52515	10' x 1/4" (3 m x 6.4 mm) Hydraulic Hose	1				1		1			
48844	48844	10' x 1/4" (3 m x 6.4 mm) Hydraulic Hose		1								
48845	48845	25' x 1/4" (6.5 m x 6.4 mm) Hydraulic Hose			1							
54167	54167	1/4" (6.4 mm) Female Coupler without Dust Cap									1	
54168	54168	1/4" (6.4mm) Dust Cap for Female Coupler									1	
54169	54169	1/4" (6.4 mm) Male Coupler without Dust Cap					1	1	2	1	1	
54170	54170	1/4" (6.4 mm) Dust Cap for Male Coupler					1	1	2	1	1	
4018GB	50807	3/8" (9.6 mm) Female Coupler with Dust Cap										1
4033GB	50823	3/8" (9.6 mm) Male Coupler with Dust Cap				2	1					1
41877	41877	3/8" (9.6 mm) Female Coupler without Dust Cap	1	1	1							
41941	41941	3/8" (9.6 mm) Male Coupler without Dust Cap	1	1	1							
41834	41834	3/8" (9.6 mm) Dust Cap for 41941/41877 Couplers	2	2	2							

Greenlee Green Spray Touch-up Paint



· Closely matches Greenlee painted products.

			WEIG	HT
CAT. NO.	UPC NO.	DESCRIPTION	LBS.	kg
22618	22618	13 oz. (384 ml) Aerosol Can of Greenlee Green Spray Paint	1.2	.5
10378	10378	13 oz. (384 ml) Aerosol Can of Greenlee Flat Green Spray Paint*	1.2	.5

NOTE: The color green is a registered trademark for Test Instruments, Job Boxes, Benders and Pulling Equipment.

Hydraulic Oil

GREENLEE





- Greenlee-approved hydraulic oil.
- Specially compounded for use with Greenlee hydraulic equipment.
- Refinery-filtered to give you the finest oil available.

			WEIG	HT
CAT. NO.	UPC NO.	DESCRIPTION	LBS.	kg
4016 GB	51059	Hydraulic Oil – 1 Gallon (3.8 l)	8.5	3.9
4017 GB	50806	Hydraulic Oil - 1 Quart (.9 I)	2.25	1.02

NOTE: For best operation of your Greenlee hydraulic-powered equipment, use Greenlee hydraulic oil only. (Do not use hydraulic brake fluid, shock absorber fluid, alcohol, glycerine, caster oil or other non-specified fluid—as they reduce performance and can cause damage to pumps and equipment.) Use of improper fluids waives the guarantee on Greenlee hydraulic equipment.

GREENLEE

Polypro General Purpose Rope



405 Rope Stand sold separately. See page 170.

- **Not for cable pulling**. See the ropes listed with cable pullers for recommended cable pulling ropes.
- Highly-visible, bright yellow with green tracer, excellent for roping off areas on construction sites.
- Rot and mildew resistant.
- · Weather resistant.
- · Economical general purpose rope.



	ROPE L	ENGTH	CAT. NO.	UPC NO.	BREAKING S	STRENGTH	AVERAGE LBS.	WEIGHT kg.
3/16"	250'	76 m	408	21467	720 lbs.	3.2 kN	3	1.4
(4.8 mm)	600'	182 m	409	21468	720 lbs.	3.2 kN	6	2.7
` '	250'	76 m	412	21471	1130 lbs.	5.0 kN	4	1.8
1/4"	600'	182 m	413	21472	1130 lbs.	5.0 kN	9	4.1
(6.4 mm)	1,000'	304 m	414	21474	1130 lbs.	5.0 kN	13	5.9
3/8"	250'	76 m	417	21477	2430 lbs.	10.8 kN	9	4.1
(9.5 mm)	600'	182 m	418	21520	2430 lbs.	10.8 kN	19	8.6
1/2"	250'	76 m	421	21480	3780 lbs.	16.8 kN	15	6.8
(12.7 mm)	600'	182 m	422	21521	3780 lbs.	16.8 kN	35	15.9
5/8" (15.9 mm)	600'	182 m	424	21524	5580 lbs.	24.8 kN	55	24.9

Chain-Type Pipe Vise

GREENLEE



- Use with a wide range of sizes of pipe or conduit.
- Built-in pipe rest.
- To prevent marring of plastic or plastic coated pipe, vise jaws can be rotated with smooth side up. Use serrated side for harder materials.
- Chain design holds pipe securely to prevent it from twisting or turning during threading.

CAT. NO.	UPC NO.	DESCRIPTION
467	27318	Chain-Type Pipe Vise

SPECIFICATIONS

Capacity	1/8" - 5" (3.2 mm x 127 mm) pipe
Weight	17 lbs. (7.7 kg)

Cutting/Threading Oil



- Premium quality, high lubricity for easier cutting and long tool life.
- · Choice of light or dark.

CAT. NO.	UPC NO.	DESCRIPTION
462B	11412	Dark Cutting/Threading Oil - 1 Pt.
462-Q	28237	Dark Cutting/Threading Oil - 1 Qt.
462-1	26096	Dark Cutting/Threading Oil - 1Gal
463-Q	28238	Light Cutting/Threading Oil - 1 Qt
463-1	28239	Light Cutting/Threading Oil - 1 Gal

SPECIFICATIONS

CAT. NO.	SIZE	WEIGHT
462-Q, 463-Q	1 Qt. (.9 I)	2.3 lbs. (1 kg)
462-1, 463-1	1 Gal. (3.8 I)	8.7 lbs. (4 kg)