


Dimensions/Data

24"x 36"PD Style Polymer Concrete (Stackable) Assembly



	DESCRIPTION	TIER	DESIGN / TEST LOAD #	WEIGHT#	PALLET QTY	PART NO.			
U	W/ 2 Bolts	8	8,000 / 12,000	100	10	PG2436CA00**			
	2 piece w/2 Bolts	8	8,000 / 12,000	122	10	PG2436CS00**			
(II)	W/ 2 Bolts	15	15,000 / 22,500	115	10	PG2436HA00**			
(II)	2 piece w/2 Bolts	15	15,000 / 22,500	122	10	PG2436HS00**			
(II)	W/ 2 Bolts	22	22,500 / 33,750	122	10	PG2436HH00**			
(II)	No Bolts	8	8,000 / 12,000	100	10	PG2436WA00**			

To order gasketed covers, replace the letter "A" with the letter "G". Replace ** with a logo code found on page 18.

NOTE: Gasketed covers and bolt grommets must be used with a gasketed box. Gaskets reduce the inflow of fluids but do not make the enclosure water tight.

Boxes

	DESCRIPTION	DEPTH	TIER	DESIGN / TEST LOAD #	WEIGHT#	PALLET QTY	PART NO.
(H)	Standard Open Bottom	18"	22	22,500 / 33,750	159	2	PD2436BA18
		26"	22	22,500 / 33,750	199	2	PD2436BA26
		48"	22	22,500 / 33,750	313	1	PD2436BA48

To order boxes with 2 standard mouseholes, replace the letter "A" with the letter "B".

To order gasketed boxes, replace the letter "A" with the letter "G".

NOTE: Gasketed covers and bolt grommets must be used with a gasketed box. Gaskets reduce the inflow of fluids but do not make the enclosure water tight.





Most commonly used cover logos are shown below. Custom Logos are available. Contact your Quazite/Hubbell Representative.

PENCELL COVER OPTIONS

LOGOS

PENCELL LOGO CODES	DESCRIPTION
009 010 012 014	BLANK CATV COMMUNICATIONS CONTROLS
017 021 022 023	ELECTRIC FIBER OPTICS FIRE ALARM GAS
024 026 029 036 038 040 041 042 043 044 045 046 048 050 057	GROUND HIGH VOLTAGE LIGHTING SECURITY SIGNAL STATE TRAFFIC SIGNAL STREET LIGHTING TELECOM TELEPHONE TRAFFIC TRAFFIC TRAFFIC CONTROL TRAFFIC SIGNAL TV WATER EMERGENCY ILLUMINATION DANGER HIGH VOLTAGE
084 092 03A 06B 0ZA K91 KH1 5P3	POWER TELECOMMUNICTIONS DOT INSTRUMENTATION IRRIGATION RECLAIMED WATER FIBEROPTIC ELECTRIC WARNING DO NOT OPEN

