

HALOGEN Lamps

WAC LIGHTING
Responsible Lighting®



JC-50-G635

Fixture Type:

Catalog Number:

Project: _____

Location: _____



JC-10, JC, 20



J-150-S

Low Voltage JC Bi-pin – Quick Connect™ Pendants, Sconces

Model	Power	Color Temp	Volt	Lumens	Average Life	Base	Length
JC-50-G635	50W	2900K	12V	950	2,000 Hours	GY6.35	1 ³ / ₁₆ "

Low Voltage JC Bi-pin – Button Lights and Miniature Recessed Fixtures

JC-10	10W	2900K	12V	140	2,000 Hours	G4	1 ³ / ₁₆ "
JC-20	20W	2900K	12V	350	2,000 Hours	G4	1 ³ / ₁₆ "

Line Voltage J Type Double Ended

J-150-S	150W	2900K	110-130V	2600	2,000 Hours	R7S	3 ¹ / ₈ "
---------	------	-------	----------	------	-------------	-----	---------------------------------

ORDER NUMBER

-

Example: JC-50-G635

WAC Lighting
www.waclighting.com
Phone (800) 526.2588 • Fax (800) 526.2585

Headquarters/Eastern Distribution Center
44 Harbor Park Drive • Port Washington, NY 11050
Phone (516) 515.5000 • Fax (516) 515.5050

Western Distribution Center
1750 Archibald Avenue • Ontario, CA 91760
Phone (800) 526.2588 • Fax (800) 526.2585