



Job Name:

Job Type:

Comments:

Quantity:

9830-15: LX Linear Lampholder White

Dimensions:

Length:	2"
Width:	3/4"
Height:	13/16"

Bulbs:

1 - festoon xenon T3 10w Max. 12v - Not included

Material List:

- 1 Body - Polycarbonate - White
- 1 Reflector - Aluminum - Satin Aluminum

Safety Listing:

UL Listed for Damp Locations
cUL Listed for Damp Locations
cETL Listed

Instruction Sheets:

English (HC-662)



Single Light Aluminum/Polycarbonate Accent Socket White Finish.

Anodized aluminum reflector. Heat resistant polycarbonate with white finish.

UPC #:785652983054

Finish: White (15)

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97118-32	Clear	Xenon	T-3	Festoon	5	4.2	12v	16000	33	2550	
97118-33	Frosted	Xenon	T-3	Festoon	5	4.2	12v	16000	33	2550	
97119-32	Clear	Xenon	T-3	Festoon	10	8.4	12v	12000	83	2650	
97119-33	Frosted	Xenon	T-3	Festoon	10	8.4	12v	12000	83	2650	
97120-32	Clear	Xenon	T-3	Festoon	5	4.2	24v	16000	33	2550	

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	9830-15	1	785652983054	3.18	3.18	1	0.006	0.01	Yes
Master Pack		50	10785652983051	5.25	5.25	6.63	0.106	0.5	Yes
Shipping Master		1000	20785652983058	30.58	13.25	13.38	3.137	27.05	Yes
NJ Pallet		20000		48	40	71.5	79.444	541	No
NV Pallet		21000		48	40	52	57.778	420	No