

ET Series - Line Voltage



Features

- Single pole and double pole
- Heat only, cool only, & heat or cool
- DP models include positive off
- Celsius and Fahrenheit temperature scale
- Optional Thermometer
- 22 Amps, 277 Volts AC

UPC # 686334	MODEL	DESCRIPTION	LIST
538725	AET5DWS	Double Pole 22 Amp, 120-277V with leads, Anticipator	41.65
538732	AET5SWS	Single Pole 22 Amp, 120-277V with leads, Anticipator	37.40
538886	ET5DS	Double Pole 22 Amp, 120-277V, Heat Only	32.90
538749	ET5D4S	Double Pole 22 Amp, 120-277V, 35-75°F Temp Range	33.60
538756	ET5DTS	Double Pole 22 Amp, 120-277V, with Thermometer, Heat Only	34.30
538763	ET5DWS	Double Pole 22 Amp, 120-277V, Heat Only with Leads	33.60
538770	ET5MS	Heat Only, 2 Stage	35.70
538787	ET5SS	Single Pole 22 Amp, 120-277V, Heat Only	27.30
538794	ET5S4S	Single Pole 22 Amp, 120-277V, 35-75°F Temp Range	30.80
538800	ET5SRS	Single Pole 22 Amp, Cooling Only	27.30
538893	ET5SRTS	Single Pole Cool with Thermometer	30.80
538817	ET5STS	Single Pole 22 Amp, Heat Only with Thermometer	30.80
538824	ET5SWS	Single Pole 22 Amp, Heat Only with Leads	32.20
538831	ETD5MS	Double Throw, 2 Stage Heat, 1 Stage Cool	35.70
538848	ETD5MTS	2 Heat, 1 Cool with Thermometer	37.10
538855	ETD5SS	Single Pole Double Throw Heat/Cool	30.80
538862	ETD5STS	Single Pole Double Throw Heat/Cool with Thermometer	32.20

EPET Series and HLT Series Hazardous Location



Features

- SPDT & DPDT Models
- Heat or cool compatible
- Celsius and Fahrenheit temperature scale
- Bi-Metal or capillary sensor
- Snap action switch
- Casting tapered top and bottom for 3/4" conduit
- 1/2" thick cast Aluminum housing
- Dimension 5-3/4" x 6-3/8" x 5.57"

Motor Rating (full load): 3/4 HP @ 125V, 1-1/2 HP @250V
Pilot Duty Rating 125VA @ 24VAC
NEMA Class Seven Div. 1 Approved
Class I Group C & D, Class II Group E, F, & G
Not rated for Group B

UPC# 686334	MODEL	DESCRIPTION	LOAD RATINGS	RANGE	LIST
538077	EPETD8D	DPDT - Bi-Metal	22A @120-277VAC	50-90°F	453
538107	EPETD8S	SPDT - Bi-Metal	22A @120-277VAC	50-90°F	429
528078	EPETP8D	DPDT - Bi-Metal	22A @120-480VAC	50-90°F	467
528061	EPETP8S	SPDT - Bi-Metal	22A @120-480VAC	50-90°F	442
523158	HLT-1	SPDT - Capillary	22A @120-277VAC	40-110°F	476
523165	HLT-2	DPDT - Capillary	22A @120-277VAC	40-110°F	502
Master ctn: 4 pcs, 24 lbs (varies slightly by model), 16" x 14.5" x 6"					
EPET Series incorporate plastic knob & Bi-Metal Sensor housing.					
HLT Series incorporates screwdriver temperature adjustment slot and all metal housing. External bulb and capillary sensor.					

2000 Series - Line Voltage



Features

- White or Ivory
- Single pole and double pole
- Heat Only
- DP models include positive off
- 22 Amps, 277 Volts AC

UPC# 686334	MODEL	COLOR	DESCRIPTION	LIST
502849	S2022H10AA	White	Single Pole with leads, 22 Amp	34
502436	S2022H10AB	Ivory		
502856	D2022H10BA	White	Double pole with leads, 22 Amp	45
502443	D2022H10BB	Ivory		
502917	S2025H10AA	White	Single Pole with leads, 25 Amp	51
502924	D2025H10DA	White	Double pole with leads, 25 Amp	60