



Metallics

Distributor Catalogue 2014-2015

**Anchors, Fasteners,
Tools, and Specialty Products
for the Electrical,
Plumbing, Heating and
Air Conditioning Industries**



**THE METALLICS QUICK
REFERENCE GUIDE**



**Screws &
Screw Kits**

A



**Nuts &
Nut Kits**

B



**Washers &
Washer Kits**

C



**Hexagon
Bolts**

D



**Anchoring
Devices**

E



**Telecom Access.
Cable Ties
Plastic Fasteners**

F



**Fixture Hanging
Accessories**

G



**Special Purpose
Electrical
Fasteners**

H



**Tools • Drills
and Accessories**

I



**Chemicals • Tape
Hand Cleaner
DAP Products**

J



**Accessories
Pro. Eyewear
First Aid Kits**

K



**Point of
Purchase
Displays**

L

SCREWS



"COMBO" TAPPING SCREWS

Pan Head (Slotted and Phillips)

STEEL ZINC CHROMATE

STOCK NO.	UPC NO.	DIAMETER	LENGTH	WT. PER PKG.	STD. PKG./ MSTR. SLEEVE	SUGGESTED TRADE LIST PRICE PER	
JTS1	82553	4	1/4	.14	100/500	2.65/c	NEW
JTS2	82554	4	3/8	.17	100/500	2.85/c	NEW
JTS10	80159	4	1/2	.20	100/500	3.23/c	
JTS4	80160	4	3/4	.23	100/500	3.75/c	
JTS11	80161	4	1	.28	100/500	3.98/c	
JTS6	80162	6	1/4	.19	100/500	2.75/c	
JTS7	80163	6	3/8	.23	100/500	2.78/c	
JTS12	80164	6	1/2	.26	100/500	3.20/c	
JTS13	80165	6	5/8	.28	100/500	3.28/c	
JTS14	80166	6	3/4	.33	100/500	3.45/c	
JTS15	80167	6	1	.39	100/500	3.20/c	
JTS9	80168	6	1 1/4	.47	100/500	3.55/c	
JTS38	80169	6	1 1/2	.53	100/500	4.50/c	
JTS39	82558	6	2	.66	100/500	6.05/c	NEW
JTS40	80170	7	1/2	.31	100/500	3.98/c	
JTS42	82570	7	3/4	.44	100/500	4.05/c	NEW
JTS44	82572	7	1	.52	100/500	4.28/c	NEW
JTS17	80171	8	3/8	.32	100/500	2.90/c	
JTS18	80172	8	1/2	.39	100/500	3.33/c	
JTS19	80173	8	5/8	.41	100/500	3.53/c	
JTS20	80174	8	3/4	.46	100/500	3.85/c	
JTS21	80175	8	1	.56	100/500	4.28/c	
JTS22	80176	8	1 1/4	.66	100/500	4.63/c	
JTS23	80177	8	1 1/2	.73	100/500	5.03/c	
JTS48	80178	8	1 3/4	.86	100/500	7.70/c	
JTS24	80179	8	2	.96	100/500	7.75/c	
JTS49	80180	10	3/8	.44	100/500	3.28/c	
JTS25	80181	10	1/2	.45	100/500	3.55/c	
JTS26	80182	10	5/8	.57	100/500	3.98/c	
JTS27	80183	10	3/4	.63	100/500	4.70/c	
JTS28	80184	10	1	.75	100/500	5.55/c	
JTS29	80185	10	1 1/4	.86	100/500	5.70/c	
JTS30	80186	10	1 1/2	.94	100/500	7.55/c	
JTS51	80187	10	1 3/4	1.14	100/500	7.68/c	
JTS31	80188	10	2	1.18	100/500	10.93/c	
JTS80	80189	10	2 1/2	1.54	100	13.18/c	
JTS81	80190	10	3	1.82	100	14.28/c	
JTS32	80191	12	1/2	.65	100/500	5.40/c	
JTS52	82577	12	5/8	.74	100/500	10.75/c	NEW
JTS33	80192	12	3/4	.79	100/500	5.70/c	
JTS34	80193	12	1	1.00	100/500	6.43/c	
JTS35	80194	12	1 1/4	1.15	100/500	7.48/c	
JTS36	80195	12	1 1/2	1.33	100/500	8.68/c	
JTS54	80196	12	1 3/4	1.53	100/500	11.05/c	

OTHER SIZES AND QUANTITIES AVAILABLE BY REQUEST

CONTINUED ON NEXT PAGE

Metallics was the first in America to offer the Combo Head — 1985