

1101 Rectangular Boxes—Covers & Flanges

CATALOG #	DESCRIPTION
6304-BE	Brass, hinged 2 7/8" x 3 7/8" cover (1/4" thick) for data or twist lock receptacle (Up to 30 amp)
6304-DFB-1	Brass, hinged 2 7/8" x 3 7/8" cover (1/4" thick) for duplex
6304-DFB-1-A	Aluminum, hinged 2 7/8" x 3 7/8" cover (1/4" thick) for duplex
6304-DFB-1-TEL	Brass, same as above but for Comm./Data
6304-DFB-1-TEL-A	Aluminum, same as above but for Comm./Data
6304-DFB-1-GFI	Brass, same as above but for decora receptacle
6304-DFB-1-GFI-A	Aluminum, same as above but for decora receptacle
6304-DFB-LR	Brass, dual hinged 2 7/8" x 3 7/8" cover (1/4" thick) for duplex
6304-DFB-LR-A	Aluminum, dual hinged 2 7/8" x 3 7/8" cover (1/4" thick) for duplex
6304-DP	Brass, 2 7/8" x 3 7/8" cover (1/8" thick) with (2) 1 1/2" screw plugs for duplex
6304-DP-NS	Nickel silver, 2 7/8" x 3 7/8" cover (1/8" thick) with (2) 1 1/2" screw plugs for duplex
6304-S	Brass, 2 7/8" x 3 7/8" cover (1/8" thick) with 2" – 1/2" combo plug for Comm./Data
6304-S-NS	Nickel silver, 2 7/8" x 3 7/8" cover (1/8" thick) with 2" – 1/2" combo plug for Comm./Data
CF-1101-DFB	Single gang brass carpet flange, 5 1/2" x 6 1/2"
CF-1101-DFB-A	Single gang aluminum carpet flange, 5 1/2" x 6 1/2"
CF-1102-DFB	Two gang brass carpet flange, 6 1/2" x 8 1/2"
CF-1102-DFB-A	Two gang aluminum carpet flange, 6 1/2" x 8 1/2"
CF-1103-DFB	Three gang brass carpet flange, 6 1/2" x 11 1/2"
CF-1103-DFB-A	Three gang aluminum carpet flange, 6 1/2" x 11 1/2"

»»»» For Replacement Plugs, see page 30

6304-BE	6304-DFB-1	6304-DFB-1-A	6304-DFB-LR
			
6304-DFB-LR-A	6304-DP	6304-DP-NS	6304-S
			
6304-S-NS	CF-1102-DFB	CF-1102-DFB-A	
			
	Available in 1, 2, & 3 Gang variations		Available in 1, 2, & 3 Gang variations