



Duplex Receptacle Wallplates

Description	Color	Nylon Standard	Nylon Mid-Size	Nylon Jumbo	Material	Metal Catalog Number
 1-Gang, 1-Duplex	Almond	NP8AL	NPJ8AL	—	Aluminum	SA8
	Black	NP8BK	NPJ8BK	—	Brass	SB8
	Blue	—	NPJ8BL	—	Brass Plated	SBP8
	Brown	NP8	NPJ8	—	Chrome	SCH8
	Gray	NP8GY	NPJ8GY	—	S/S 302/304	SS8
	Ivory	NP8I	NPJ8I	NPJJ8I	S/S 430	SS8L
	Light Almond	NP8LA	NPJ8LA	NPJJ8LA	Steel, Almond	SP8AL*
	Office White	NP8OW	NPJ8OW	—	Steel, Gray	SP8G*
	Orange	NP8OR	—	—		
	Red	NP8R	NPJ8R	—		
	White	NP8W	NPJ8W	NPJJ8W		
 2-Gang, 2-Duplex	Black	NP82BK	NPJ82BK	—	Aluminum	SA82
	Brown	NP82	NPJ82	—	Brass	SB82
	Gray	NP82GY	NPJ82GY	—	Brass Plated	SBP82
	Ivory	NP82I	NPJ82I	—	Chrome	SCH82
	Light Almond	NP82LA	NPJ82LA	—	S/S 302/304	SS82
	Office White	NP82OW	NPJ82OW	—	S/S 430	SS82L
	Orange	NP82OR	—	—	Steel, Almond	SP82AL*
	Red	NP82R	NPJ82R	—	Steel, Gray	SP82G*
	White	NP82W	NPJ82W	—		
 3-Gang, 3-Duplex	Brown	NP83	—	—	Aluminum	①
	Ivory	NP83I	—	—	Brass	①
	White	NP83W	—	—	Brass Plated	①
					Chrome	①
					S/S 302/304	SS83
					S/S 430	—
 4-Gang, 4-Duplex	Brown	NP84	—	—	Aluminum	①
	Ivory	NP84I	—	—	Brass	①
	White	NP84W	—	—	Brass Plated	①
					Chrome	①
					S/S 302/304	SS84
					S/S 430	—
 2-Gang, 1-Duplex	Brown	—	—	—	Brass	—
	Ivory	—	—	—	Brass Plated	—
	White	—	—	—	Chrome	—
					S/S 302/304	SS748
					S/S 430	—

Single 15/20A Straight Blade or 15A Twist-Lock® Receptacle Wallplates

Description	Color	Nylon Standard	Nylon Mid-Size	Nylon Jumbo	Material	Metal Catalog Number
 1-Gang, 1-Single 1.40 in. (35.6) Dia. Hole	Black	NP7BK	NPJ7BK	—	Aluminum	SA7
	Brown	NP7	NPJ7	—	Brass	SB7
	Gray	NP7GY	NPJ7GY	—	Brass Plated	SBP7
	Ivory	NP7I	NPJ7I	—	Chrome	SCH7
	Light Almond	NP7LA	NPJ7LA	—	S/S 302/304	SS7
	Office White	NP7OW	NPJ7OW	—	S/S 430	SS7L
	Red	NP7R	NPJ7R	—	Steel, Almond	SP7AL*
	White	NP7W	NPJ7W	—	Steel, Gray	SP7G*
 2-Gang, 1-Single 1.40 in. (35.6) Dia. Hole	Brown	—	—	—	Aluminum	—
	Ivory	—	—	—	Brass	—
	White	—	—	—	Brass Plated	—
					Chrome	—
					S/S 302/304	SS747
					S/S 430	—
 2-Gang, 2-Single 1.40 in. (35.6) Dia. Hole	Brown	—	—	—	Aluminum	①
	Ivory	—	—	—	Brass	①
	White	—	—	—	Brass Plated	①
					Chrome	①
					S/S 302/304	SS72
					S/S 430	—

Note: All nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.

① Available as a custom wallplate, see pages O-31 to O-34. Consult custom wallplates section for additional openings and combinations.

*Powder coat paint finish.

Dimensions in Inches (mm)