

STEEL STRAIGHT CORD GRIP STRAIN RELIEF CONNECTORS

COLOR CODED - STRAIGHT

APPLICATION

To secure and seal cords or cables entering enclosures or raceways.

FEATURES

- Neoprene Grommet for a moisture proof seal
- Simple installation, cord can be installed without disassembly of the fitting
- Liquidtight/Oiltight/Raintight
- Suitable for NEMA 4 enclosures and other wet locations
- Male tapered thread NPT
- Colored gripper allows for easy identification

STANDARD MATERIALS

Steel Body / Steel Gland Nut Neoprene Grommet

STANDARD FINISH

Zinc Plated



TYPE CG50-250

| CATALOG NUMBER | TRADE SIZE | COLOR | CABLE RANGE | | UNIT PACK | MASTER PACK | LBS. / 100 PCS. | UPC # |
|----------------|------------|--------|-------------|------|-----------|-------------|-----------------|-------|
| | | | MIN | MAX | | | | |
| 1/2" | | | | | | | | |
| CG50-250 | 1/2" | Red | 0.15 | 0.25 | 25 | 100 | 10 | 85001 |
| CG50-350 | 1/2" | White | 0.25 | 0.35 | 25 | 100 | 10 | 85002 |
| CG50-450 | 1/2" | Blue | 0.34 | 0.45 | 25 | 100 | 10 | 85003 |
| CG50-560 | 1/2" | Green | 0.45 | 0.56 | 25 | 100 | 10 | 85004 |
| CG50-650 | 1/2" | Brown | 0.55 | 0.65 | 25 | 100 | 10 | 85005 |
| 3/4" | | | | | | | | |
| CG75-250 | 3/4" | Red | 0.15 | 0.25 | 10 | 50 | 14 | 85101 |
| CG75-350 | 3/4" | White | 0.25 | 0.35 | 10 | 50 | 14 | 85102 |
| CG75-450 | 3/4" | Blue | 0.35 | 0.45 | 10 | 50 | 14 | 85103 |
| CG75-560 | 3/4" | Green | 0.45 | 0.56 | 10 | 50 | 14 | 85104 |
| CG75-650 | 3/4" | Brown | 0.55 | 0.65 | 10 | 50 | 14 | 85105 |
| CG75-750 | 3/4" | Yellow | 0.65 | 0.75 | 10 | 50 | 14 | 85106 |
| CG75-850 | 3/4" | Purple | 0.75 | 0.85 | 10 | 50 | 14 | 85107 |
| 1" | | | | | | | | |
| CG100-560 | 1" | Green | 0.45 | 0.56 | 5 | 25 | 20 | 85201 |
| CG100-650 | 1" | Brown | 0.50 | 0.65 | 5 | 25 | 20 | 85202 |
| CG100-750 | 1" | Yellow | 0.65 | 0.75 | 5 | 25 | 20 | 85203 |
| CG100-850 | 1" | Purple | 0.75 | 0.85 | 5 | 25 | 20 | 85204 |
| CG100-950 | 1" | Grey | 0.85 | 0.95 | 5 | 25 | 20 | 85205 |
| CG100-1050 | 1" | Black | 0.95 | 1.05 | 5 | 25 | 20 | 85206 |
| 1-1/4" | | | | | | | | |
| CG125-850 | 1-1/4" | Purple | 0.75 | 0.85 | 5 | 25 | 40 | 85301 |
| CG125-950 | 1-1/4" | Grey | 0.85 | 0.95 | 5 | 25 | 40 | 85302 |
| CG125-1050 | 1-1/4" | Black | 0.95 | 1.05 | 5 | 25 | 40 | 85303 |
| CG125-1150 | 1-1/4" | Orange | 1.05 | 1.15 | 5 | 25 | 40 | 85304 |
| CG125-1250 | 1-1/4" | Red | 1.15 | 1.25 | 5 | 25 | 40 | 85305 |
| CG125-1375 | 1-1/4" | White | 1.25 | 1.38 | 5 | 25 | 40 | 85306 |
| 1-1/2" | | | | | | | | |
| CG150-1050 | 1-1/2" | Black | 0.95 | 1.05 | 2 | 10 | 70 | 85401 |
| CG150-1150 | 1-1/2" | Orange | 1.05 | 1.15 | 2 | 10 | 70 | 85402 |
| CG150-1250 | 1-1/2" | Red | 1.15 | 1.25 | 2 | 10 | 70 | 85403 |
| CG150-1375 | 1-1/2" | White | 1.25 | 1.38 | 2 | 10 | 70 | 85404 |

Suitable for use in Hazardous Locations under NEC 501-4(b), 502- 4(a), and 503-3(a). For Class I, Div. 2, Class II, Div. 1, 2, and Class III, Div. 1, 2.



Steel Electric
PRODUCTS

Ph: 718.259.6100 / 800.626.1223 Fax: 718.331.1874

www.sepco-usa.com