

EASY-TWIST™

Wire Connectors

Winged Twist-On

WWC Series



SPECIFICATIONS

- UL 486C Listed wire connector E155027.
- WWC-GR is UL 467 Listed Grounding and Bonding.
- Temperature Rating: 105 °C (221 °F).
- Voltage: 600V max., 1,000V max. in fixtures and signs.
- Wire Type: For Copper wire only.
- **Example: (100) (10x100) = 100 in standard package, 1000 in standard carton.**

FEATURES

- Deep surface ridges provide better grip.
- Ergonomic, swept-back wing design provides handling comfort and increased torque ability.
- Flame retardant UL 94V-2 thermoplastic shell provides excellent electrical insulation.
- Fixed, precise square wire spring provides secure gripping of conductors.
- Deep skirt entry provides protection from flashover and shorts.
- Compact design ensures proper installation, especially in tight spaces.
- Threaded funnel entry guides the wires into the connector easily.
- Pre-twisting of wires is not necessary.
- Zinc-plated springs for low contact resistance.
- **Installation:** Socket installation tools are included in each bag of Easy-Twist™ Connectors (Cat.No. with "B" suffix). Made to fit any pneumatic or electrical tool with a 1/4" chuck or drive socket.



COLOR/TYPE	CARTON	SMALL JAR	LARGE JAR	LARGE BAG	BUCKET	BULK	DRUM
Yellow (WWC)	WWC-Y-C (100) (10x100)	WWC-Y-CJ (100) (50x100)	WWC-Y-J (550) (12x550)	WWC-Y-B (500) (13x500)	WWC-Y-BT (3,000)	WWC-Y (5000)	WWC-Y-D (35000)
Tan (WWC)	WWC-T-C (100) (10x100)	WWC-T-CJ (100) (50x100) WWC-T-SJ (100) (50x100)	WWC-T-J (450) (12x450)	WWC-T-B (500) (12x500)	WWC-T-BT (3,000)	WWC-T (5000)	WWC-T-D (30000)
Red (WWC)	WWC-R-C (100) (10x100)	WWC-R-SJ (100) (20x100)	WWC-R-J (300) (12x300)	WWC-R-B (500) (7x500)	WWC-R-BT (3,000)	WWC-R (5000)	WWC-R-D (20000)
Grey (WWC)	WWC-G-C (50) (10x50)	WWC-G-SJ (50) (32x50)	—	WWC-G-B (250) (11x250)	—	WWC-G (5000)	WWC-G-D (20000)
Blue (WWC)	WWC-B-C (50) (10x50)	WWC-B-SJ (50) (20x50)	WWC-B-J (125) (12x125)	WWC-B-B (100) (16x100)	—	WWC-B (2500)	WWC-B-D (9500)
Green GND (WWC)	WWC-GR-C (100) (10x100)	WWC-GR-SJ (100) (20x100)	WWC-GR-J (300) (12x350)	WWC-GR-B (500) (9x500)	WWC-GR-BT (3,000)	WWC-GR (5500)	WWC-GR-D (25000)
Yellow N1 (WWC)	WWC-N1-C (100) (10x100)	WWC-N1-CJ (100) (50x100)	—	WWC-N1-B (500) (13x500)	—	WWC-N1 (10000)	—
Red N2 (WWC)	WWC-N2-C (100) (10x100)	—	—	WWC-N2-B (500) (9x500)	—	WWC-N2 (10000)	—

Scan QR code
for mobile access
to wire combinations.

