## T5 12W HE 3FT. DIR TITANIUM LED SERIES









- Compatible with Instant Start & Programmed Start ballasts
- Exceptional efficacy 129 LPW
- Suitable for use in totally enclosed fixtures
- Dowerful light output 1550 lumens
- Dimmable



























### HIGH LUMEN EFFICIENCY - SUPERIOR PERFORMANCE



# T5 12W HE 3FT. DIR TITANIUM LED SERIES



### SPECIFICATIONS\*\*

Product	57954	57955	57956
Model	12T5HE/3F/830/DIR	12T5HE/3F/835/DIR	12T5HE/3F/840/DIR
Туре	T5	T5	T5
Base	Mini Bi-Pin G5	Mini Bi-Pin G5	Mini Bi-Pin G5
Power (W)	12	12	12
Voltage - Frequency	120-277V 50-60Hz	120-277V 50-60Hz	120-277V 50-60Hz
Color Temp. (ANSI)	Warm White 3000K	Neutral White 3500K	Cool White 4000K
CRI (Ra)	80	80	80
Typical lumens (lm)	1420	1420	1550
Efficacy (LPW)	118	118	129
Light Emitting Area	270°	270°	270°
Beam Angle	120°	120°	120°
Dimmable	Yes	Yes	Yes
Power Factor	0.9	0.9	0.9
THD	<20%	<20%	<20%
Rated Lifetime - L70 (hrs.)	50,000	50,000	50,000
Dia. x MOL	0.67"x33.98" (17x863mm)	0.67"x33.98" (17x863mm)	0.67"x33.98" (17x863mm)
Weight (lb. / g)	0.27lb. / 124g	0.27lb. / 124g	0.27lb. / 124g

## PROGRAM START BALLAST PERFORMANCE

Bare Lamp (W)	System (W)	Lumens 1420	Lumens 1420	Lumens 1550
		3000K	3500K	4000K