

# RATIO



P5015-20

A sleek metal frame supports a low-slung shade to create Ratio's casual modern style. The frame's proportion to the white linen drum shade evokes a perfect ratio for lighting. All fixtures include a polished glass diffuser that offers an elegant appeal.

## FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

## PAIR WITH

Cherish  
Harmony



P3604-09



P5015-09



P3604-20



P3604-09



P5021-09



P5021-20

## SEMI-FLUSH CONVERTIBLE

**P3604-09** Brushed Nickel  
**P3604-20** Antique Bronze  
Hanging and ceiling mount hardware included.  
16" dia., 11-1/2" ht.  
Overall ht. w/stem 77-1/2", wire 10'.  
Three medium base lamps, each 75w max.

## FOUR-LIGHT PENDANT

**P5015-09** Brushed Nickel  
**P5015-20** Antique Bronze  
Hanging and ceiling mount hardware included.  
24" dia., 15-7/8" ht.  
Overall ht. w/stem 82", wire 10'.  
Four medium base lamps, each 75w max.

## SIX-LIGHT PENDANT

**P5021-09** Brushed Nickel  
**P5021-20** Antique Bronze  
Hanging and ceiling mount hardware included.  
30" dia., 19-1/8" ht.  
Overall ht. w/stem 85", wire 10'.  
Six medium base lamps, each 75w max.

# RATIO

---

White linen shade with polished glass diffuser.

## SEMI-FLUSH CONVERTIBLE

**P3604-09** Brushed Nickel

**P3604-20** Antique Bronze

Hanging and ceiling mount hardware included.

16" dia., 11-1/2" ht.

Overall ht. w/stem 77-1/2", wire 10'.

Three medium base lamps, each 75w max.



P3604-20



P3604-09