Aluminum Service Poles

- Poles with three service capability ideal for delivering power, fiber, and data cabling from the ceiling to the floor
- Available in three standard lengths to accommodate a variety of applications
- Available in five attractive durable paint colors and clear anodized aluminum finish to suit every need
- Factory ordered custom pole lengths and configurations available for special applications

Hubbell offers a line of attractive and durable Aluminum Service Poles which distribute power and telecommunications wiring from above the ceiling to workstations below.

They are offered in lengths of 10' 2", 12' 2", and 15' 2" with a variety of electrical wiring devices. Poles with three service capability have a divider to separate power and low voltage wiring.

These customizable power poles effectively distribute power, fiber, and data cabling from the ceiling to the floor. Available in varying lengths and colors, custom options maximize space and allow workstations, retail checkout areas, collaboration areas, digital signage, vending machines, appliances, and kiosks to be pulled away from the wall.



FEATURES

- Available in gray, ivory, black, white and office white painted and clear anodized aluminum finishes
- Style Line® decorator duplex receptacles and two Style Line® knockouts for communications
- Includes ceiling trim mounting plate and bottom scuff boot

SPECIFICATIONS

- **UL** listed
- Suitable for retail checkout areas application



Ivory

Gray







Aluminum Service Poles


ORDERING INFORMATION

Three Service Aluminun	n Service Poles	Height Feet (m)		
Description	Color	10' 2" (3.10m)	12' 2" (3.71m)	15' 2" (4.62m)
(2) 20A 125V Style Line® duplex	Black	HBLPP10BK	HBLPP12BK	HBLPP15BK
receptacles; one circuit	Gray	HBLPP10A	HBLPP12A	HBLPP15A
	lvory	HBLPP10AI	HBLPP12AI	HBLPP15AI
	Office White	HBLPP100W	HBLPP12OW	HBLPP15OW
	White	HBLPP10W	HBLPP12W	HBLPP15W
	Clear Anodized Aluminum	HBLPP10AAL	HBLPP12AAL	HBLPP15AAL
(1) Orange isolated ground	Black	HBLPP10IGBK	_	_
20A 125V Style Line® duplex	Gray	HBLPP10IGA	_	_
receptacle; (1) 20A 125V Style	lvory	HBLPP10IGAI	_	_
Line® duplex receptacle; two	Office White	HBLPP10IGOW	_	_
circuits	White	HBLPP10IGW	_	_
	Clear Anodized Aluminum	HBLPP10IGAL	_	_
(2) Orange isolated ground	Black	HBLPP10SBK	_	_
20A 125V Style Line® duplex	Gray	HBLPP10SA	_	_
receptacles; (1) isolated ground	Ivory	HBLPP10SAI	_	_
surge suppression 20A 125V	Office White	HBLPP10SOW	_	-
duplex receptacle; one circuit	White	HBLPP10SW	-	-
	Clear Anodized Aluminum	HBLPP10SAL	_	_
(1) 20A 125V GFCI Self Test	Black	HBLPP10GFBK	HBLPP12GFBK	HBLPP15GFBK
duplex receptacle with (2)	Gray	HBLPP10GF	HBLPP12GF	HBLPP15GF
ground fault protected 20A 125V	Ivory	HBLPP10GFI	HBLPP12GFI	HBLPP15GFI
Style Line® duplex receptacles;	Office White	HBLPP10GFOW	HBLPP12GFOW	HBLPP15GFOW
one circuit.	White	HBLPP10GFW	HBLPP12GFW	HBLPP15GFW
	Clear Anodized Aluminum	HBLPP10GFAL	HBLPP12GFAL	HBLPP15GFAL
Blank pole; divider;	Black	HBLPPOBK	HBLPPO12BK	HBLPPO15BK
(4) Style Line® device	Gray	HBLPPOA	HBLPPO12A	HBLPPO15A
knockouts	Ivory	HBLPPOAI	HBLPPO12AI	HBLPPO15AI
	Office White	HBLPPOOW	HBLPPO12OW	HBLPPO15OW
	White	HBLPPOW	HBLPPO12W	HBLPPO15W
	Clear Anodized Aluminum	HBLPPOAAL	HBLPPO12AAL	HBLPPO15AAL



See catalog section for custom pole configurations.

Accessories	
Description	
Adjustable T-bar assembly for mounting poles in the middle of ceiling tile.	ATB*
Replacement service pole trim kit (office white).	PPTRIM1*
Note: *Not UL listed.	





www.hubbell-wiring.com

