SSHO COMMERCIAL SMARTSERIES®

HIGH-OUTPUT WALL HEATER



IDEAL SPACES

- Lobbies
- Vestibules
- Waiting Rooms
- Restaurants
- Stairwells
- Bedrooms
- Living/Family Rooms
- Basements
- Offices
- Conference Rooms
- Entrance Ways

COLORS

- Northern White
- Navaho White
- Statuary Bronze
- Custom Colors Available*

DIMENSIONS

- Grille: 19-1/8"H x 15-3/4"W x 1-3/8"D
- Back Box: 18-1/4"H x 14-3/8"W x 4"D

TEMP RANGE

■ 40°- 99°F

CFM

100









- BMS compatible Connects to Building Management Systems for optimum control
- Energy efficiency with proportional heating that automatically adjusts wattage output
- Maintains heat within 1.5 degree of set temperature (as compared to five degrees with conventional bi-metal thermostats)
- Hold function maintains constant set temperature. Use for freeze protection or vacation setting when away
- Lockout Feature Securely maintain comfort levels
- No ducting or plumbing needed means no heat loss before the heat enters the room
- SmartSeries® Digital Thermostat: 5/2-day programmability with four program periods per day
- 'Right out of the box' three-piece construction Includes back box, Element/Fan Deck and Grille
- Fits recessed between standard stud walls or use with optional surface mounting frame (ideal for block or plaster walls)
- Power on/off switch for added safety during maintenance



SSHO COMMERCIAL SMARTSERIES®

HIGH-OUTPUT WALL HEATER

MODELS & SPECIFICATIONS							
CATALOG NO.	UPC	VOLTS	WATTS	AMPS	PHASES	BTU/HR.	SHIP WT. (LBS.)
SSHO4008	6 85360 15670 5	208	1800/4000	8.7/19.2	1	13,650	26
SSHO4004	6 85360 15672 9	240	1800/4000	7.5/16.7	1	13,650	26
SSHO4007	6 85360 15673 6	277	1800/4000	6.5/14.4	1	13,650	26

SURFACE MOUNTING FRAME ACCESSORIES								
CATALOG NO.	UPC	DESCRIPTION	SHIP WT. (LBS)					
HTWHSM	6 85360 15545 6	Surface Mounting Frame 15-3/8"W x 19-3/16"H x 3-3/4"D	4					
HTWHS1	6 85360 15548 7	1 in. Semi-Recess Mounting Frame 15-3/8"W x 19-3/16"H x 1"D	4					
HTWHS2	6 85360 15551 7	2 in. Semi-Recess Mounting Frame 15-3/8"W x 19-3/16"H x 2"D	4					

NOTE: *See page 157 for information on custom paint colors. Add NV (Navajo White) or SB (Stat Bronze) suffix to catalog number (ex. SSHO4008NV). Mounting Limitations: Do not install heater closer than 12 in. to the floor, 12 in. to an adjacent wall, 36 in. to the ceiling. Do not install heater behind towel rack or door, upside down or sideways, in the floor, in the ceiling, or in closets.

