



Kellems® Wire Management Products
I-Grips
Plastic-Coated, Galvanized Steel Mesh for Insulated Cables

WARNING!
It is important that you read all breaking strength, safety and technical data relating to this product on pages T-71 through T-76.



Application
Kellems® I-Grips will fit 2, 3, 4 and 5 wire Hubbell Insulgrip® plugs and connector bodies. The eye tabs fit under the nylon cord clamp and the screws slide through the eyelets, securing the grip in place. These grips are for indoor use only.

- Benefits**
- Easily attached to Insulgrip plugs and connector bodies.
 - Controls cable arc-of-bend.
 - Provides heavy-duty strain relief.
 - Fits all sizes.

I-Grips

Cable Diameter Range Inches (cm)	E Inches (cm)	M Inches (cm)	Catalog Number
.32"-.43" (.81-1.09)	1.25" (3.17)	4" (10.16)	07310001
.43"-.56" (1.09-1.42)	1.25" (3.17)	4.75" (12.06)	07310002
.56"-.73" (1.42-1.85)	1.50" (3.81)	6" (15.24)	07310003
.73"-.85" (1.85-2.16)	1.50" (3.81)	6.5" (16.51)	07310004
.85"-1.00" (2.16-2.54)	1.50" (3.81)	8" (20.32)	07310005
1.00"-1.25" (2.54-3.17)	1.50" (3.81)	10" (25.40)	07310006

*Note: E-Eye length.
M-Mesh length at nominal diameter.
Eyelet hole diameter .203" (.52cm).
I-Grips should not be used on Insulgrip devices when "Seal-Tite®" weatherproof covers are to be installed.*

