



07309

ECONO-LITE STREAMER®

Our most economical lighting system! Features 14 gauge (open conductors) and our easy-open, snap-on plastic guards. Accommodates A-23 type bulbs up to 150 watts. Does not include caps or connectors.

CAT NO	LENGTH IN FT	DESCRIPTION	GUARD	NEMA PLUG	NEMA RECEPTACLE	COMPLIANCE	MASTER PACK	MASTER WT	MASTER PCK CUBE
15 Amp									
07308	50	14g TW 300v	Plastic	—	—	—	1	3	.97
07309	100	14g TW 300v	Plastic	—	—	—	1	5	.97



07200



07300

Replacement Guards

CAT NO	DESCRIPTION	MASTER PACK	MASTER WT	MASTER PACK CUBE
07200-20	Coated METAL	20	6	1.13
07300	Plastic	20	2	1.05
07500-00-00	Plastic	20	3	1.05



07603

Metal Halide Temporary Light



CAT NO	WATTS	GUARD TYPE	BULB TYPE	CORD LENGTH IN FT	MASTER PACK	MASTER WT	MASTER PACK CUBE
07603*	400	10" Wire Guard	Type "O"	6	1	26	1.74

* NEC 2005

Metal Halide Replacement Bulb



CAT NO	WATTS	DESCRIPTION	CORD LENGTH IN FT	MASTER PACK	MASTER WT	MASTER PACK CUBE
07620*	400	Type "O" Replacement Bulb	—	4	4.41	0.4

* NEC 2005

