Straps for Service Entrance Cable and EMT						
	CAT. NO.	MAXIMUM CABLE OR PIPE SIZE	COLOR	PACKAGE AND QUANTITY	STD. Carton Quantity	APPROX. Shipping WT. Per Carton
C UNIS LISTED	RA-1710	.718" Dia.	For #6 SER (4 Gray	Conductor) and 1/2" EA Box of 50	1 <i>T</i> 1000	16 lbs.
	RA-1720	.937" Dia.	For #2 SER (4 Gray	Conductor) and 3/4" EN Box of 25	1 <i>T</i> 500	13 lbs.
	RA-1724	1.062″ Dia.	For #1/C Gray	SER (4 Conductor) Box of 25	500	15 lbs.
	RA-1730	1.160" Dia.	For #2/0 SER Gray	(4 Conductor) and 1" EN Box of 25	1 <i>T</i> 500	16 lbs.
	RA-1740	1.438" Dia.	For #4/0 Gray	SER (4 Conductor) Box of 10	200	9 lbs.
	<ul> <li>The standard color is gray with a UV stabilizer.</li> <li>For prolonged outdoor exposure, black colored straps with a UV stabilizer are also available.</li> </ul>					
C. U.S. TED	RA-1750	.437" x .750"	For #6 S Gray	SEU (3 Conductor) Box of 100	2000	21 lbs.
	RA-1760	.550" x .972"	For #2 S Gray	SEU (3 Conductor) Box of 50	1000	17 lbs.
	RA-1765	.775" x 1.265"	For #2/0 Gray	SEU (3 Conductor) Box of 25	500	16 lbs.
	RA-1770	.855" x 1.500"	For #4/0 Gray	SEU (3 Conductor) Box of 25	500	18 lbs.
2-Hole Straps for Plastic Pipe and Conduit						
C. U. U.S. TED	PC-1210	1/2" .840" Dia.	Gray	Box of 50	1000	10 lbs.
	PC-1220	3/4" 1.050" Dia.	Gray	Box of 50	1000	11 lbs.
	PC-1230	1" 1.312" Dia.	Gray	Box of 25	500	11 lbs.
	PC-1240	1-1/4" 1.670" Dia.	Gray	Box of 25	500	12 lbs.
Protective Handy Plates						
7	Protect electrical cables passing through wood framing members.     Conform to requirements of the National Electrical Code.					
	SA-10015	3" x 1-1/2" x 16 ga.	-	Box of 100	500	38 lbs.