

Description

Suttle's 66M Block system is used in equipment rooms or in remote and intermediate wiring closets to connect voice or data wiring to customer premise equipment.


Blocks are molded of flame retardant thermoplastic with quick-connect 66-type clips for ease of installation and proven termination reliability.


Features

- Molded from flame retardant thermoplastic
- Standard 66-type connector clips, 4 clips x 50 rows
- A66M1-25 contains 50 rows with four connected clips in each, for a total of 25 pairs capacity
- A66M1-25 includes one 25-pair designation strip
- A66M1-50 contains 50 rows, but two separate pairs of clips in each, for a total of 50 pairs capacity
- A66M1-50 includes two 25-pair designation strips
- Requires industry-standard 66 block termination tool for punchdown

Dimensions

Model	Number of Pairs	Type of Terminal	Dimensions H x W x D
A66M1-25	25	4 Clip	10.0" x 3.40" x 1.20"
A66M1-50	50	2 Clip	10.0" x 3.40" x 1.20"
031709-97			10.0" x 2.26" x 0.5"
	c(UL)us		





4 Clip

2 Clip

Product Information	Description			
Suttle Part Number				
A66M1-25	4 x 50, 66M connecting block, 25 pair, includes 1 designation strip			
A66M1-50	4 x 50, 66M connecting block, 50 pair, includes 2 designation strips			
66M1-50-C5	4 x 50, 66M connecting block, 50 pair, with translucent clear cover marked "CAT 5"			
031709-97	Hinged cover for 66M block, self-extinguishing plastic (sold separately)			

