

# **LED A-Lamps**

75w Equivalent • Omni-Directional

High efficiency A-Lamps. Light output in all directions to suit many applications.

## Limitless options for the following applications:

- General Lighting
- Floor Lamps
- Ceiling Fixtures

- Table Lamps
- Sconces

## Great features and benefits:

- Energy efficient: up to 85% more efficient than incandescent alternatives
- Smooth, uniform dimming where applicable
- Long life: 15,000/25,000 hour options
- Similar look and feel as incandescent alternative
- Excellent color consistency
- Available in 2700K, 3000K, 4100K and 5000K
- Fits any installation where a standard A-lamp is used

## Choices to meet your markets:

- 15,000 hour high value series
- 25,000 hour elite series











## 75w • Omni-Directional


## **Applications:**

Ideal for applications where uniform multi-directional light output is required.

- + Table Lamps
- **+** Sconces
- **◆** Decorative Fixtures
- **★** Floor Lamps
- + Ceiling Fixtures
- **◆** Any general service lighting application

Features	Benefits
Up to 85% less energy than halogen alternatives	Instant energy savings
Long life	Minimizes replacement and maintenance costs
Very low heat generation	Perfect for sensitive display lighting such as art galleries
Excellent color consistency and CRI	Enhances colors of focal point while maintaining uniformity throughout lighting installation from lamp to lamp
UL approved for damp location	Can be used outdoors when protected from elements — withstands humidity indoors/outdoors
Shatter resistant	Lower the risk of injury and breakage
ANSI construction compliant	Fits all A-lamp installations

Dims to  $\leq 5\%$  of full light level where applicable



Specifications	· ·
Input Line Voltage:	120 VAC
Input Line Frequency	
Lamp Life (Rated)	
Minimum Starting Temp	30℃
Maximum Operating Temp	40°C
CRI	80
Vapor tight or jelly jar applications may reduce life	

Warranty	Item#	Description	Case Pack	Rated Life (hrs)	Wattage	Incandescent Wattage Comparison	Lumens	LPW	ССТ	CRI	M.O.L. (inches)	Diameter (inches)	Enclosed/ Recessed Luminaire	ENERGY STAR Rated
	Non-Dimmable													
$3^{\frac{\text{YEAR}}{\text{WARRANTY}}}$	L11A19N1527K	LED 11W A19 ND 2700K	12	15,000	11	75	1100	100.0	2700K	80	4.5	2.4	γ	*
	L11A19N1530K	LED 11W A19 ND 3000K	12	15,000	11	75	1150	104.5	3000K	80	4.5	2.4	Υ	*
	L11A19N1541K	LED 11W A19 ND 4100K	12	15,000	11	75	1200	109.1	4100K	80	4.5	2.4	Υ	*
	L11A19N1550K	LED 11W A19 ND 5000K	12	15,000	11	75	1225	111.4	5000K	80	4.5	2.4	Υ	*
5 YEAR WARRANTY	Dimmable L11A19D2527K L11A19D2530K L11A19D2541K L11A19D2550K	LED 11W A19 DIM 2700K LED 11W A19 DIM 3000K LED 11W A19 DIM 4100K LED 11W A19 DIM 5000K	12 12 12 12	25,000 25,000 25,000 25,000	11 11 11 11	75 75 75 75	1150 1175 1200 1225	104.5 106.8 109.1 111.4	2700K 3000K 4100K 5000K	80 80 80 80	4.5 4.5 4.5 4.5	2.4 2.4 2.4 2.4	ү ү ү ү	* * * *
	For the most up-to-date specs, please visit www.tcpi.com													

