

30A NEMA | Black & White®

30A NEMA Locking Devices

Industrial Grade Black & White® Locking Devices

30A-125V, 250V and 277VAC

2-Pole, 3-Wire Grounding Ⓛ Ⓢ

Rating	30A-125V		30A-250V		30A-277VAC	
NEMA						
	L5-30P	L5-30R	L6-30P	L6-30R	L7-30P	L7-30R
Description	Cat. No.	Cat. No.	Cat. No.	Cat. No.	Cat. No.	Cat. No.
Plugs and Connectors	Plug	Connector	Plug	Connector	Plug	Connector
Black & White®	2611	2613	2621	C2623	2631	2633
Nylon Body						
All Black	2611-B	2613-B	2621-B	C2623-B	—	—
Nylon Body						
Yellow Nylon Body	2611-CY	2613-CY	2621-CY	C2623-CY	—	—
Power Indication™	2611-PLC	2613-PLC	2621-PLC	C2623-PLC	2631-PLC	2633-PLC
Black & White®						
Nylon Body						
Power Indication™	2611-PLB	2613-PLB	—	—	—	—
All Black Nylon Body						
Inlets and Outlets	Inlet	Outlet	Inlet	Outlet	Inlet	Outlet
Flanged Device	2615	2616	2625F	2626F	2635	2636
Receptacles						
V-O-Max® Single	—	2610	—	2620	—	2630
Flush Receptacle						
V-O-Max® Single Flush	—	2610-IG	—	2620-IG	—	2630-IG
Receptacle, Isolated Ground						



2620



2621-B



2625F



2650

30A-480VAC and 600VAC

2-Pole, 3-Wire Grounding Ⓛ Ⓢ

Rating	30A-480VAC		30A-600VAC	
NEMA				
	L8-30P	L8-30R	L9-30P	L9-30R
Description	Cat. No.	Cat. No.	Cat. No.	Cat. No.
Plugs and Connectors	Plug	Connector	Plug	Connector
Black & White Nylon Body	2641	2643	C2651	C2653
Inlets and Outlets	Inlet	Outlet	Inlet	Outlet
Flanged Device	2645	2646	2655	2656
Receptacles				
V-O-MAX® Single Flush	—	2640	—	2650
Receptacle				