

Round Speaker Wire



94722

Soundsational™ Speaker Cables (high-strand, pressure-extruded, round)

Part Number	Description	AWG	Cond	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
94762	16/2 stranded BC (65/34) 99.97% OFC	16	2	CL3	31 lbs	0.192"	500' Box (45)	White (01) Yellow (02)
94764	16/4 stranded BC (65/34) 99.97% OFC	16	4	CL3	47 lbs	0.224"	500' Box (45)	Blue (06)
94742	14/2 stranded BC (105/34) 99.97% OFC	14	2	CL3	44 lbs	0.222"	500' Box (45)	White (01) Yellow (02)
94744	14/4 stranded BC (105/34) 99.97% OFC	14	4	CL3	69 lbs	0.260"	500' Box (45)	
94722	12/2 stranded BC (168/34) 99.97% OFC	12	2	CL3	73 lbs	0.278"	500' Reel (05)	White (01) Purple (13)



94542 94564

Signet™ Speaker Cables (direct burial, high-strand, tubed construction)

Part Number	Description	AWG	Cond	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
94562	16/2 stranded BC (65/34) 99.97% OFC	16	2	CL3	24 lbs	0.188"	1000' Box (46)	White (01) Blue (06)
94564	16/4 stranded BC (65/34) 99.97% OFC	16	4	CL3	43 lbs	0.220"	500' Box (45)	
94542	14/2 stranded BC (105/34) 99.97% OFC	14	2	CL3	35 lbs	0.218"	1000' Box (46)	White (01) Yellow (02)
94544	14/4 stranded BC (105/34) 99.97% OFC	14	4	CL3	64 lbs	0.256"	1000' Box (46)	



94642 94664

ClearSignal™ Speaker Cables (contractor grade, tubed construction)

Part Number	Description	AWG	Cond	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
94662	16/2 stranded BC (26/30) 99.97% OFC	16	2	CL3	23 lbs	0.188"	500' Box (45)	White (01) Blue (06)
94664	16/4 stranded BC (26/30) 99.97% OFC	16	4	CL3	42 lbs	0.220"	500' Box (45)	
94642	14/2 stranded BC (41/30) 99.97% OFC	14	2	CL3	34 lbs	0.218"	500' Box (45)	White (01) Yellow (02)
94644	14/4 stranded BC (41/30) 99.97% OFC	14	4	CL3	63 lbs	0.256"	500' Box (45)	

Zip Speaker Wire



94616

Premium Parallel Zip Speaker Cables

Part Number	Description	AWG	Cond	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
94616	16/2 stranded BC (65/34) 99.97% OFC	16	2	CL2	36 lbs	0.126" x 0.266"	250' Reel (04) 500' Reel (05)	Clear (18)
94614	14/2 stranded BC (105/34) 99.97% OFC	14	2	CL2	53 lbs	0.157" x 0.360"	500' Reel (05)	Clear (18)
94612	12/2 stranded BC (168/34) 99.97% OFC	12	2	CL2	76 lbs	0.193" x 0.410"	500' Reel (05) 1,000' Reel (06)	Clear (18)



94605

Basic Zip Speaker Cables

Part Number	Description	AWG	Cond	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
94600	22/2 stranded BC (7/30) 99.97% OFC	22	2	CL2	8 lbs	0.073" x 0.156"	1,000' Reel (06) 1,000' Reel (46)	White (01) Clear (18)
94603	18/2 stranded BC (16/30) 99.97% OFC	18	2	CL2	17 lbs	0.090" x 0.200"	1,000' Reel (06) 1,000' Reel (46)	White (01) Clear (18)
94605	16/2 stranded BC (26/30) 99.97% OFC	16	2	CL2	25 lbs	0.105" x 0.230"	500' Reel (05) 500' Reel (45)	Clear (18)
94607	14/2 stranded BC (41/30) 99.97% OFC	14	2	CL2	36 lbs	0.122" x 0.264"	500' Reel (05)	Clear (18)
94608	12/2 stranded BC (65/30) 99.97% OFC	12	2	CL2	60 lbs	0.142" x 0.304"	500' Reel (05)	Clear (18)



55266

Direct Burial Zip Speaker / Lighting Cable

Part Number	Description	AWG	Cond	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
55266	16/2 stranded BC (26/30) 99.97% OFC	16	2	n/a	43 lbs	0.156" x 0.307"	500' Reel (05)	Black (08)
55267	14/2 stranded BC (41/30) 99.97% OFC	14	2	n/a	53 lbs	0.166" x 0.341"	500' Reel (05)	Black (08)
55269	12/2 stranded BC (65/30) 99.97% OFC	12	2	n/a	71 lbs	0.186" x 0.417"	500' Reel (05)	Black (08)
55272	10/2 stranded BC (104/30) 99.97% OFC	10	2	n/a	102 lbs	0.209" x 0.405"	500' Reel (05)	Black (08)
55271	8/2 stranded BC (168/30) 99.97% OFC	8	2	n/a	162 lbs	0.287" x 0.574"	250' Reel (04)	Black (08)