

Decora® Standard

Specifications and Features

- Accent any wall covering with a wide selection of colors and finishes
- Smooth face and rounded edges resist dust accumulation
- Color-matched mounting screws supplied
- Mounting screws on one-gang Thermoplastic (Nylon) are preinstalled and captive

DECORA STANDARD SIZE

	Description	Color	Thermoset	Thermoplastic (Nylon)	Metal				
			P26	N26	Industry Standard				
			Cat. No.	Cat. No.			Cat. No.		
	1-Gang	White	80401-W	80401-NW	Aluminum	A26	83401		
		Ivory	80401-I	80401-NI	Brass	B26	81401		
		Almond	80401-A	80401-NA	Polished Brass		81401-PB		
		Lt. Almond	80401-T	80401-NT	Non-Magnetic S/S	SN26-N	84401-40		
		Grey	80401-GY	80401-NGY					
		Black	80401-E	80401-NE					
		Brown	80401	80401-N					
		Red	—	80401-NR					
		Blue	—	80401-NB					
			2-Gang	White	80409-W	80409-NW	Aluminum	A262	83409
Ivory	80409-I			80409-NI	Brass	B262	81409		
Almond	80409-A			80409-NA	Polished Brass		81409-PB		
Lt. Almond	80409-T			80409-NT	Non-Magnetic S/S	S262-N	84409-40		
Grey	80409-GY			80409-NGY					
Black	80409-E			80409-NE					
Brown	80409			80409-N					
Red	—			80409-NR					
	3-Gang			White	80411-W	80411-NW	Aluminum	A263	83411
				Ivory	80411-I	80411-NI	Brass	B263	81411
		Almond	80411-A	80411-NA	Polished Brass		81411-PB		
		Lt. Almond	80411-T	80411-NT	Non-Magnetic S/S	S263-N	84411-40		
		Grey	80411-GY	80411-NGY					
		Black	80411-E	—					
		Brown	80411	80411-N					
	4-Gang	White	80412-W	80412-NW	Brass	B264	81412		
		Ivory	80412-I	80412-NI	Non-Magnetic S/S	S264-N	84412-40		
		Almond	80412-A	80412-NA					
		Lt. Almond	80412-T	80412-NT					
		Grey	80412-GY	—					
		Black	80412-E	—					
		Brown	80412	80412-N					