

### **COMPRESSION**

## **REDUCING ADAPTERS**

Use to reduce barrel size for smaller wire in lug or splice

Versatile adapters fit into copper compression splice or lug to reduce barrel size Install with compression die appropriate for barrel size

High conductivity copper, tin-plated

Some sizes are corrugated, some smooth with open seam


#### **CRA SERIES**

			ONA OLIVILO									
NAED	CATALOG NUMBER	FROM	ES SIZE TO	LENGTH	U-TYPE COLOR	INDEX						
41616	CRA10-6	FROW	#6	LENGIH	COLOR	INDEX						
41614	CRA10-4	1/0	#4	15/16	PINK	12/348						
41646	CRA40-6		#6									
41644	CRA40-4		#4									
41645	CRA40-2		#2									
41640	CRA40-1	4/0	#1	13/4	PURPLE	15						
41641	CRA40-10		1/0	1 /4	TORTEL	13						
41642	CRA40-20		2/0									
41643	CRA40-30		3/0									
41625	CRA250-2		#2									
41620	CRA250-1		#1									
41621	CRA250-10		1/0									
41622	CRA250-20	250	2/0	2	YELLOW	16						
41623	CRA250-30		3/0									
41624	CRA250-40		4/0									
41635	CRA300-2		#2									
41631	CRA300-10		1/0									
41632	CRA300-20	300	2/0	2	WHITE	17/298						
41633	CRA300-30		3/0									
41634	CRA300-40		4/0									
41636	CRA350-20		2/0									
41637	CRA350-40	350	4/0	2	DED	40/004						
41638	CRA350-250	330	250	2	RED	18/324						
41639	CRA350-300		300									
41656	CRA500-6		#6									
41654	CRA500-4		#4									
41655	CRA500-2	500	#2	21/4	BROWN	20/299						
41650	CRA500-1	300	#1	2 /4	BROWN	20/299						
41651	CRA500-10		1/0									
41652	CRA500-20		2/0									
41653	CRA500-30		3/0									
41670	CRA500-40		4/0									
41671	CRA500-250	500	250	21/4	BROWN	20/299						
41672	CRA500-300		300	- / -	DICOVII	20/200						
41673	CRA500-350		350									
41674	CRA500-400		400									
41665	CRA600-500	600	500	21/4	GREEN	22/472						
41675	CRA750-500	750	500	21/4	BLACK	24						
41676	CRA750-600	100-	600									
41607	CRA1000-750	1000	750	3	WHITE	27						





Copper wire only



Copper wire only



# COMPRESSION COMPRESSION REDUCER KITS - COPPER

Splice two sizes of Class B copper cable; installer to supply all cable

Join a new system to an existing system where oversized cable is used to reduce voltage drop on long runs Reduce an oversized wire to fit a lug supplied on the equipment

CRK kit includes CRA adapter(s) to reduce the barrel to fit the cable sizes.

Each kit contains: Long barrel compression splice (C Series)

Adapter(s) for reduction/tip end (CRA Series)

Adapter(s) for cable/run end, if needed (CRA Series)

All components are high conductivity copper, tin-plated

Can be insulated with high heat-shrink tubing

CRK kits are designed for copper cable only. To splice an aluminum cable to a smaller copper cable, consult the factory for an ACK-R Kit (ASC-T splice with CRA insert), or use a AC-R Aluminum Reducing Splice or PT Bi-Metallic Adapter.

# **CRK SERIES**

NAED CATALOG		REDUCES SIZE		KIT INCLUDES			U-TYPE DIE	
NUMBER	NUMBER	FROM	то	CRA	С	CRA	COLOR	INDEX
41729	CRK2-6	#2	#6	-	C2	2-6	BROWN	10
41716	CRK10-6	1/0	#6	- C10	10-6	DINIK	40/040	
41714	CRK10-4	1/0	#4	_	C10	10-4	PINK	12/348
41721	CRK20-1	2/0	#1	_	C20	20-1	BLACK	13
41734	CRK30-4		#4	40-30		40-4		
41732	CRK30-2	3/0	#2	40-30	C40	40-2	PURPLE	15
41735	CRK30-10	3/0	1/0	40-30	040	40-10		
41730	CRK30-20		2/0	40-30		40-20		
41746	CRK40-6		#6			40-6		
41745	CRK40-2		#2			40-2	PURPLE	15
41741	CRK40-10	4/0	1/0	-	C40	40-10		
41742	CRK40-20		2/0			40-20		
41743	CRK40-30		3/0			40-30		
41786	CRK250-6		#6			250-10 + 10-6		
41785	CRK250-2		#2	- (	C250	250-2	YELLOW	16
41781	CRK250-10	250	1/0			250-10		
41782	CRK250-20	230	2/0			250-20		
41783	CRK250-30		3/0			250-30		
41784	CRK250-40		4/0			250-40		
41796	CRK350-20	350	2/0	_	C350	350-20	RED	18/324
41797	CRK350-40		4/0			350-40		
41749	CRK400-250	400	250	500-400	C500	500-250	BROWN	20/299
41756	CRK500-6		#6			500-6		
41752	CRK500-20		2/0			500-20		
41753	CRK500-30		3/0	-	C500	500-30	BROWN	20/299
41770	CRK500-40	500	4/0			500-40		
41771	CRK500-250		250			500-250		
41773	CRK500-350		350			500-350		
41774	CRK500-400		400			500-400		
41762	CRK600-300	600	300	_		600-500 + 500-300	GREEN	
41763	CRK600-350		350		C600	600-500 + 500-350		22/472
41764	CRK600-400		400			600-500 + 500-400		
41765	CRK600-500		500			600-500		
41775	CRK750-500	750	500	_	C750	750-500	BLACK	24
41776	CRK750-600		600			750-600	BLACK	
41707	CRK1000-750	1000	750	_	C1000	1000-750	WHITE	27

Other kit combinations available, consult factory.

For aluminum main, ACK Series also available. Consult factory.

**Example:** CRK 500-350 configuration with single adapter

**Example:** CRK 400-250 configuration with two adapters to fit wires

Assembled, user provides wires

Assembled, user provides wires



# COMPRESSION NECK-DOWN™ REDUCING SPLICES - COPPER

**GREAVES EXCLUSIVE** 

Long barrel reducers to join copper wires of different sizes Produced from high-conductivity seamless copper tubing Marked with die index and die color code on each end Can be insulated with high heat-shrink tubing Also see CRK Series compression Reducer Kits

For copper cable only 600V\*

#### ND-R SERIES

NAED CATALOG NUMBER NUMBER		WIRE SIZE		U-TYPE DIE A		U-TYPE DIE B	
		Α	В	INDEX	COLOR	INDEX	COLOR
52012	ND 10R2	1/0	#2	12/348	PINK	10	BROWN
52011	ND 10R1	1/0	#1	12/540	PIINK	11/375	GREEN
52021	ND 20R10	2/0	1/0	13	BLACK	12/348	PINK
52032	ND 30R20	3/0	2/0	14	ORANGE	13	BLACK
52042	ND 40R20	4/0	2/0	45 DUDDU	DUDDLE	13	BLACK
52043	ND 40R30	4/0	3/0	15	PURPLE	14	ORANGE
52252	ND 250R20	250	2/0	16	YELLOW	13	BLACK
52254	ND 250R40	250	4/0	16		15	PURPLE
52302	ND 300R250	300	250	17/298	WHITE	16	YELLOW
52354	ND 350R40	350	4/0	18/324	RED	15	PURPLE
52352	ND 350R250	350	250	81/324	RED	16	YELLOW
52403	ND 400R350	400	350	91/470	BLUE	18/324	RED
52502	ND 500R250		250			16	YELLOW
52503	ND 500R350	500	350	20/299	BROWN	18/324	RED
52504	ND 500R400		400			19/470	BLUE
52635	ND 600R350	000	350	22/472	22/472 GREEN	18/324	RED
52650	ND 600R500	600	500	22/4/2		20/299	BROWN
52755	ND 750R500		500	0.4/470		20/299	BROWN
52756	ND 750R600	750	600	24/4/3	24/473 BLACK		GREEN
52107	ND 1000R750	1000	750	27	WHITE	24/473	BLACK
52121	ND 1250R1000	1250	1000	29	YELLOW	27	WHITE
52151	ND 1500R1000	1500	1000	31	GREEN	27	WHITE
52162	ND 1500R1250	1500	1250	31	GREEN	29	YELLOW



Manufactured to order in 3-4 days. \*Minimum order 3 pieces of same size.

For tin plating add suffix "P" to Catalog No; adds approx. 1 week production time. Consult factory for combinations not listed.


# **ALUMINUM REDUCING SPLICES**Made of high conductivity wrought aluminum

Made of high conductivity wrought aluminum
Long barrel with positive center stop to assure proper cable insertion
Can be insulated with high heat-shrink tubing
Connector bores are coated with oxide-inhibitor and capped

### **AC-R SERIES**

NAED	CATALOG	WIRE SIZE		DIE A & B	EST. SHIPPING	
NUMBER	NUMBER	Α	В	INDEX	WEIGHT (lbs)	UNIT
53012	AC 10R2	1/0	#2	BG, 8A, 5/8		EA
53021	AC 20R1	2/0	#1	60, 245	.15	EA
53031	AC 30R10	3/0	1/0	TU, 781, 56		EA
53042	AC 40R20	4/0	2/0	298, 840		EA
53253	AC 250R30	250	3/0	11A, 249, 840		EA
53304	AC 300R40	300	4/0	96, 299	.21	EA
53354	AC 350R40	350	4/0	96, 299		EA
53402	AC 400R250	400	250	22, 472	1	EA
53530	AC 500R300	500	300	106, 300	.77	EA
53535	AC 500R350	500	350	106, 300	.80	EA
53635	AC 600R350	600	350	24, 473	1.15	EA
53750	AC 750R500	750	500	140, 301	1.32	EA
53107	AC 1000R750	1000	750	161, 302	1.90	EA

Dual-Rated CUAL 600 V\*



<sup>\*</sup>May be used for applications up to 35 KV when proper installation and insulation procedures are employed.

<sup>\*</sup>May be used for applications up to 35KV when proper installation and insulation procedures are employed. Other sizes available, consult factory.