

Features & Benefits

- Assembled in USA
- No rewiring needed
- Works with fluorescent electronic ballast (Instant Start, Programmed Start, and Dimming)*
- Long life
- High CRI
- Instant on, no delay
- Convenient and quick installation
- Utilizes existing instant start or rapid start sockets
- Compatible with controls and sensors
- Dimmable
- Works in cold temperature applications
- Super wide view angle
- 5 Year Warranty
- High performance plastic series
- Buy American Compliant



* EMERGENCY BALLAST RESTRICTIONS




RetroFlex™
LED T8 LAMP • Simplicity.
Commercial Grade LED T8 Lamp

Specification Data


Order Code	Length	Lamp Wattage	System Wattage	CCT	Initial Lumens	CRI	Beam Angle	Lamp Efficacy	System Efficacy	Life	DLC
L36T8/835/12P-EB	36	12	14	3500K	1700	83	325	135	120	50000	No
L36T8/840/12P-EB	36	12	14	4000K	1700	83	325	135	120	50000	No
L36T8/850/12P-EB	36	12	14	5000K	1700	83	325	135	120	50000	No

Wiring diagram


1-LAMP Instant Start Electronic Ballast




2-LAMP Instant Start Electronic Ballast




3-LAMP Instant Start Electronic Ballast




4-LAMP Instant Start Electronic Ballast



1-LAMP Programmed Start Electronic Ballast



2-LAMP Programmed Start Electronic Ballast



* Not compatible with products equipped with battery backup and/or emergency ballasts.

* Please refer to "Ballast Compatibility List" on Related Downloads.

Specification data is based on tests performed in a controlled environment and represents relative performance. Actual performance can vary depending on operating conditions. Application and performance data subject to change without notice. All specifications are nominal unless noted otherwise.