

# Decora Plus™ Duplex Receptacles

## Heavy-Duty Industrial Specification and Hospital Grades

### Isolated Ground

### 15 A & 20 A, 125 V

Brass self-grounding clip is permanently staked on for secure and reliable performance

Wide receptacle face shelf provides exceptional support to the wallplate or box cover

Body and face made of impact-resistant advanced engineering polymer for extreme durability

“Universal” strap design provides ample support for electrical box installations, and includes multiple “break-off” tabs to eliminate interference with virtually any cover or wallplate

Ground and contact terminal isolated from mounting strap to prevent system noise interference

Oversized brass terminal screw heads provide superior clamping force and electrical conductivity

External wiring clamps allow for back or side wiring, and provide visual verification of termination and a faster, easier installation

Molded in ribs prevent terminal screws from making contact with wall box

### Ordering Information

		Specification Grade		Hospital Grade	
Ratings		15 A/ 125 V	20A/ 125 V	15 A/ 125 V	20 A/ 125 V
NEMA Config.		5-15R	5-20R	5-15R	5-20R
Order ID	Orange	16262-OIG	16362-OIG	D8200-IG	D8300-IG
	Ivory	16262-IIG	16362-IIG	D8200-IGI	D8300-IGI
	White	16262-WIG	16362-WIG	D8200-IGW	D8300-IGW
	Gray	16262-GIG	16362-GIG	D8200-IGG	D8300-IGG
	Red	16262-RIG	16362-RIG	D8200-IGR	D8300-IGR
	Brown	16262-BIG	16362-BIG	D8200-IGB	D8300-IGB
	Black	16262-EIG	16362-EIG	D8200-IGE	D8300-IGE
	Lt. Almond	16262-TIG	16362-TIG	D8200-IGT	D8300-IGT

### Common Applications:

- Educational Facilities
- Office Environments
- Hospitals/Medical Buildings
- Hospitality
- Day Care Centers


## Specifications

Series	16262-IG/D8200-IG	16362-IG/D8300-IG
<b>AC Horsepower Rating</b>		
At Rated Voltage	½ HP	1 HP
<b>Electrical Specifications</b>		
Amperage	15 A	20 A
NEMA	5-15R	5-20R
Voltage	125 V	
Grounding	Self-Grounding*	
Pole	2	
Wire	3	
Dielectric Voltage	Withstands 3000 V min	
Temperature Rise	Max 30 °C temperature rise at full rated current	
<b>Environmental Specifications</b>		
Flammability	UL94 V0	
Operating Temperature	Maximum Continuous 75 °C, minimum -40 °C (w/o impact)	
<b>Material Specifications</b>		
Face	PBT Polyester Blend	
Body	PBT Polyester Blend	
Strap	Steel (Galvanized G60)	
Ground Contact	0.030" Brass	
Ground Screw	#8 Hex Head, Triple-Drive Brass	
Ground Clamp	Brass	
Ground Clip	Brass	
Mounting Screw	Triple-Drive Plated Steel	
Line Contacts	0.030" Phosphor Bronze	
Terminal Clamp	Brass	
Terminal Screws	#8 Triple-Drive Brass	
Shutter Mechanism	Acetal	
<b>Mechanical Specifications</b>		
Product ID	Ratings are permanent part of devices	
Terminal ID	Brass - Hot, Silver - Neutral, Green - Ground	
Terminal Accommodation	#14 - #10 AWG	
Wire Types	Stranded or Solid	
Termination	Back and Side Wire	
<b>Standards &amp; Certifications</b>		
NEMA	WD 1 & WD 6	
ANSI	C-73	
Certification/Listing	cULus, NOM-ANCE	
Applicable Standards	UL498, Fed Spec W-C-596, CSA C22.2 No.42	
RoHS	RoHS Compliant	
<b>Warranty</b>		
Product Warranty	10 Years	


\* Self-grounding when installed in a properly grounded metallic box

## Dimensions

Front View



Side View



Visit our Website at:  
[www.leviton.com/commercial](http://www.leviton.com/commercial)  
 email: [commercial@leviton.com](mailto:commercial@leviton.com)

Q-1111

110817

### Leviton Manufacturing Co., Inc.

201 N Service Rd, Melville, NY 11747  
 Telephone: 1-800-323-8920 • FAX: 1-800-832-9538  
 Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

© 2017 Leviton Manufacturing Co., Inc. All rights reserved.

