

GROUNDING

GREAVES EXCLUSIVE

Ground-Lok™ CLAMP SYSTEM SERRATED HEAD - COMPONENTS

Copper wire only

BRONZE WATER PIPE GROUND CLAMPS

Interchangeable clamps and adapters provide versatility

Matching serrations assure positive lock of adapter to clamp

Heavy duty construction - cast bronze body and plated steel screws





G1 SERIES

NAED NUMBER	CATALOG NUMBER	WATER PIPE SIZE (IPS)	TUBING SIZE	GROUND WIRE RANGE	CTN QTY	EST. SHIPP WEIGHT (lbs)	ING UNIT
CLAMPS							
30102	G 1	1/2 - 1	3/4 - 11/2	#2 - 10 STR	50	12.0	CTN
30160	G 2	11/4 - 2	11/2 - 2		25	10.8	CTN
30440	G 12	21/2 - 4	3 - 4		4	4.46	CTN
30460	G 13	41/2 - 6	5 - 6		4	6.11	CTN
WIRE ADAPTERS							
30680	G 40	CABLE		4/0 - #10 STR		4.56	CTN
		ARMORED		#2 - 10 STR	20	4.56	CTN
CONDUIT HUBS							
NAED NUMBER	CATALOG NUMBER	THREAD SIZE	GROUND WIRE RANGE		CTN QTY	EST. SHIPPING WEIGHT(lbs) UNIT	

2/0 - #10 STR

3/0 - #10 STR

3/0 - #10 STR







CTN

CTN

CTN

5.00

5.72

6.81



PLATING: For tin-plating add suffix letter "P" to CATALOG NUMBERS.

1/2

3/4

UL listed to #4 AWG. CSA certified as shown.

G 41

G 42

G 43

30700

30720

30740



20

20

20

4 CLAMPS + 4 ADAPTERS = 20 COMBINATIONS

Available with brass screws.

All adapters fit all clamps